

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P827667

Luminaire Tested: **OHBL-15HE-A-UNV-L930-CD-UPL15**

Issue Date: 5/3/2024



Test Information

Test Method: LM-79-08
Report Number: P827667
REPORT IS A COMBINATION OF REPORTS P826107 AND G3-2310-221-10
Test Lab: INNOVATION CENTER
Issue Date: 5/3/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: OHBL-15HE-A-UNV-L930-CD-UPL15
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1228.0 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.17')
CIE Type: Indirect

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P827667

CATALOG NUMBER: OHBL-15HE-A-UNV-L930-CD-UPL15

Luminous Intensity Polar Plot





TEST NUMBER: P827667

CATALOG NUMBER: OHBL-15HE-A-UNV-L930-CD-UPL15

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0																			
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	0																			
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0																			
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0																			
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0																			
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0																			
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	0																			
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0																			
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0																			
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	0																			
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P827667

CATALOG NUMBER: OHBL-15HE-A-UNV-L930-CD-UPL15

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.1	0.3
90°-100°	117.7	9.6
100°-110°	407.9	33.2
110°-120°	350.5	28.5
120°-130°	168.2	13.7
130°-140°	84.1	6.8
140°-150°	48.8	4.0
150°-160°	28.5	2.3
160°-170°	14.8	1.2
170°-180°	4.5	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.1	0.3
90°-120°	876.1	71.3
90°-150°	1177.2	95.9
90°-180°	1225.0	99.8
0°-180°	1228.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	18	23	31	35	2
95°	23	58	86	115	133	81
105°	512	504	430	304	279	484
115°	352	352	356	354	347	356
125°	171	180	185	184	183	161
135°	101	104	107	108	109	80
145°	74	75	77	78	78	47
155°	59	60	61	61	62	28
165°	51	51	52	52	52	15
175°	46	46	46	47	47	4
180°	46	46	46	46	46	



TEST NUMBER: P827667

CATALOG NUMBER: OHBL-15HE-A-UNV-L930-CD-UPL15

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.4	17.8	23.4	30.7	34.8
92.5°	8.1	22.6	37.2	51.7	59.8
95°	22.6	58.2	86.5	114.8	133.4
97.5°	134.2	151.2	164.9	190.0	204.5
100°	272.4	294.2	241.7	253.8	259.5
102.5°	438.1	423.6	312.8	281.3	276.4
105°	511.7	504.4	430.0	303.9	278.9



TEST NUMBER: P827667

CATALOG NUMBER: OHBL-15HE-A-UNV-L930-CD-UPL15

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	411.4	417.1	409.8	395.3	380.7
115°	352.4	352.4	355.7	354.0	346.8
117.5°	302.3	300.7	303.9	302.3	300.7
120°	252.2	255.4	256.2	254.6	253.8
122.5°	208.6	215.0	219.1	216.6	215.8
125°	170.6	180.3	185.1	183.5	182.7
127.5°	145.5	151.2	157.6	157.6	156.0
130°	126.1	130.1	135.0	135.8	135.8
132.5°	112.4	115.6	119.6	120.4	121.2
135°	101.0	104.3	106.7	108.3	109.1
137.5°	93.0	94.6	97.8	98.6	99.4
140°	84.9	87.3	89.7	90.5	91.3
142.5°	79.2	80.8	82.4	84.1	84.1
145°	73.6	75.2	76.8	78.4	78.4
147.5°	69.5	71.1	72.8	72.8	73.6
150°	65.5	67.1	67.9	68.7	68.7
152.5°	62.2	63.0	64.7	64.7	65.5
155°	59.0	59.8	61.4	61.4	62.2
157.5°	56.6	57.4	58.2	59.0	59.0
160°	54.2	55.0	55.8	55.8	56.6
162.5°	52.5	53.4	53.4	54.2	54.2
165°	50.9	50.9	51.7	51.7	51.7
167.5°	49.3	49.3	50.1	50.1	50.9
170°	47.7	48.5	48.5	48.5	49.3
172.5°	46.9	46.9	47.7	47.7	47.7
175°	46.1	46.1	46.1	46.9	46.9
177.5°	45.3	46.1	46.1	46.1	46.1
180°	46.1	46.1	46.1	46.1	46.1



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	511.7	512.5	474.5	365.4	306.4
110°	472.1	476.1	455.1	413.9	363.8



(END OF REPORT)