

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P827968

Luminaire Tested: **OHBL-15HE-A-UNV-L935-CD-UPL24**

Issue Date: 5/3/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P827968  
REPORT IS A COMBINATION OF REPORTS P826215 AND G3-2310-221-6  
Test Lab: INNOVATION CENTER  
Issue Date: 5/3/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: OHBL-15HE-A-UNV-L935-CD-UPL24  
Description:  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2016.9 lumens  
Efficiency: N/A  
Efficacy: 115.9 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.17')  
CIE Type: Indirect

Input Watts (W): 17.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P827968

CATALOG NUMBER: OHBL-15HE-A-UNV-L935-CD-UPL24

### Luminous Intensity Polar Plot





TEST NUMBER: P827968

CATALOG NUMBER: OHBL-15HE-A-UNV-L935-CD-UPL24

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	9	9	9	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	2	2	2	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P827968

CATALOG NUMBER: OHBL-15HE-A-UNV-L935-CD-UPL24

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	5.1	0.3
90°-100°	193.2	9.6
100°-110°	670.8	33.3
110°-120°	575.4	28.5
120°-130°	276.0	13.7
130°-140°	138.1	6.8
140°-150°	80.1	4.0
150°-160°	46.7	2.3
160°-170°	24.2	1.2
170°-180°	7.4	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	5.1	0.3
90°-120°	1439.3	71.4
90°-150°	1933.5	95.9
90°-180°	2012.0	99.8
0°-180°	2016.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	28	39	52	58	3
95°	44	92	143	190	215	137
105°	836	827	703	501	460	793
115°	577	582	582	581	576	582
125°	282	297	302	302	299	264
135°	167	170	176	178	179	132
145°	121	124	127	128	128	77
155°	97	98	100	101	101	45
165°	83	84	85	85	85	24
175°	75	76	76	77	77	7
180°	75	75	75	75	75	



TEST NUMBER: P827968

CATALOG NUMBER: OHBL-15HE-A-UNV-L935-CD-UPL24

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	4.2	28.3	39.2	51.7	57.5
92.5°	14.2	37.5	60.0	85.0	95.8
95°	44.2	92.5	143.3	190.0	215.0
97.5°	224.2	242.5	260.8	315.8	343.3
100°	460.0	488.3	394.2	416.7	424.2
102.5°	710.8	706.7	515.0	461.7	455.0
105°	835.8	826.7	703.3	500.8	460.0



TEST NUMBER: P827968

CATALOG NUMBER: OHBL-15HE-A-UNV-L935-CD-UPL24

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	673.3	683.3	670.0	650.8	624.2
115°	576.7	582.5	582.5	580.8	575.8
117.5°	493.3	494.2	497.5	496.7	497.5
120°	408.3	417.5	425.0	420.8	415.8
122.5°	342.5	352.5	357.5	355.8	350.8
125°	281.7	296.7	302.5	301.7	299.2
127.5°	238.3	249.2	257.5	258.3	257.5
130°	207.5	214.2	222.5	223.3	224.2
132.5°	184.2	190.0	195.8	199.2	198.3
135°	166.7	170.0	175.8	177.5	179.2
137.5°	152.5	155.0	160.0	162.5	162.5
140°	140.0	143.3	147.5	149.2	150.0
142.5°	129.2	132.5	135.8	137.5	137.5
145°	120.8	124.2	126.7	127.5	128.3
147.5°	113.3	116.7	118.3	120.0	120.0
150°	107.5	109.2	111.7	112.5	113.3
152.5°	101.7	103.3	105.8	106.7	106.7
155°	96.7	98.3	100.0	100.8	100.8
157.5°	92.5	94.2	95.8	96.7	96.7
160°	89.2	90.0	91.7	92.5	92.5
162.5°	85.8	86.7	87.5	88.3	88.3
165°	83.3	84.2	85.0	85.0	85.0
167.5°	80.8	80.8	81.7	82.5	82.5
170°	78.3	79.2	79.2	80.0	80.0
172.5°	76.7	77.5	77.5	77.5	78.3
175°	75.0	75.8	75.8	76.7	76.7
177.5°	75.0	75.0	75.0	75.0	75.0
180°	75.0	75.0	75.0	75.0	75.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	839.2	842.5	777.5	607.5	505.8
110°	774.2	781.7	744.2	680.0	598.3



(END OF REPORT)