

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P826469

Luminaire Tested: **OHBL-15HE-MCL-UNV-L830-CD-UPL15**

Issue Date: 5/3/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P826469  
REPORT IS A COMBINATION OF REPORTS P826108 AND G3-2310-221-10  
Test Lab: INNOVATION CENTER  
Issue Date: 5/3/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: OHBL-15HE-MCL-UNV-L830-CD-UPL15  
Description:  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1413.7 lumens  
Efficiency: N/A  
Efficacy: 137.3 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.17')  
CIE Type: Indirect

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P826469

CATALOG NUMBER: OHBL-15HE-MCL-UNV-L830-CD-UPL15

### Luminous Intensity Polar Plot





TEST NUMBER: P826469

CATALOG NUMBER: OHBL-15HE-MCL-UNV-L830-CD-UPL15

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	9	9	9	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	2	2	2	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P826469

CATALOG NUMBER: OHBL-15HE-MCL-UNV-L830-CD-UPL15

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.6	0.3
90°-100°	135.5	9.6
100°-110°	469.5	33.2
110°-120°	403.5	28.5
120°-130°	193.6	13.7
130°-140°	96.8	6.8
140°-150°	56.2	4.0
150°-160°	32.8	2.3
160°-170°	17.0	1.2
170°-180°	5.2	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.6	0.3
90°-120°	1008.5	71.3
90°-150°	1355.2	95.9
90°-180°	1410.0	99.7
0°-180°	1413.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	20	27	35	40	2
95°	26	67	100	132	154	93
105°	589	581	495	350	321	558
115°	406	406	409	408	399	410
125°	196	208	213	211	210	186
135°	116	120	123	125	126	92
145°	85	86	88	90	90	54
155°	68	69	71	71	72	32
165°	59	59	60	60	60	17
175°	53	53	53	54	54	5
180°	53	53	53	53	53	



TEST NUMBER: P826469

CATALOG NUMBER: OHBL-15HE-MCL-UNV-L830-CD-UPL15

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.8	20.5	27.0	35.4	40.0
92.5°	9.3	26.1	42.8	59.6	68.9
95°	26.1	67.0	99.6	132.1	153.5
97.5°	154.5	174.0	189.8	218.7	235.4
100°	313.6	338.7	278.2	292.2	298.7
102.5°	504.4	487.6	360.1	323.8	318.2
105°	589.0	580.7	495.1	349.9	321.0



TEST NUMBER: P826469

CATALOG NUMBER: OHBL-15HE-MCL-UNV-L830-CD-UPL15

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	473.7	480.2	471.8	455.0	438.3
115°	405.7	405.7	409.4	407.6	399.2
117.5°	348.0	346.2	349.9	348.0	346.2
120°	290.3	294.1	295.0	293.1	292.2
122.5°	240.1	247.5	252.2	249.4	248.5
125°	196.3	207.5	213.1	211.2	210.3
127.5°	167.5	174.0	181.5	181.5	179.6
130°	145.2	149.8	155.4	156.3	156.3
132.5°	129.3	133.1	137.7	138.7	139.6
135°	116.3	120.0	122.8	124.7	125.6
137.5°	107.0	108.9	112.6	113.5	114.5
140°	97.7	100.5	103.3	104.2	105.2
142.5°	91.2	93.1	94.9	96.8	96.8
145°	84.7	86.5	88.4	90.3	90.3
147.5°	80.0	81.9	83.8	83.8	84.7
150°	75.4	77.2	78.2	79.1	79.1
152.5°	71.7	72.6	74.4	74.4	75.4
155°	67.9	68.9	70.7	70.7	71.7
157.5°	65.1	66.1	67.0	67.9	67.9
160°	62.3	63.3	64.2	64.2	65.1
162.5°	60.5	61.4	61.4	62.3	62.3
165°	58.6	58.6	59.6	59.6	59.6
167.5°	56.8	56.8	57.7	57.7	58.6
170°	54.9	55.8	55.8	55.8	56.8
172.5°	54.0	54.0	54.9	54.9	54.9
175°	53.0	53.0	53.0	54.0	54.0
177.5°	52.1	53.0	53.0	53.0	53.0
180°	53.0	53.0	53.0	53.0	53.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	589.0	590.0	546.2	420.6	352.7
110°	543.4	548.1	523.9	476.4	418.8



(END OF REPORT)