

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P828570

Luminaire Tested: **OHBL-15HE-MCL-UNV-L950-CD-UPL24**

Issue Date: 5/3/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P828570  
REPORT IS A COMBINATION OF REPORTS P826216 AND G3-2310-221-6  
Test Lab: INNOVATION CENTER  
Issue Date: 5/3/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: OHBL-15HE-MCL-UNV-L950-CD-UPL24  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2104.3 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.17')  
CIE Type: Indirect  
  
Input Watts (W): 17.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P828570

CATALOG NUMBER: OHBL-15HE-MCL-UNV-L950-CD-UPL24

### Luminous Intensity Polar Plot





TEST NUMBER: P828570

CATALOG NUMBER: OHBL-15HE-MCL-UNV-L950-CD-UPL24

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	9	9	9	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	2	2	2	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P828570

CATALOG NUMBER: OHBL-15HE-MCL-UNV-L950-CD-UPL24

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	5.4	0.3
90°-100°	201.6	9.6
100°-110°	699.8	33.3
110°-120°	600.3	28.5
120°-130°	288.0	13.7
130°-140°	144.1	6.8
140°-150°	83.5	4.0
150°-160°	48.7	2.3
160°-170°	25.2	1.2
170°-180°	7.7	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	5.4	0.3
90°-120°	1501.7	71.4
90°-150°	2017.3	95.9
90°-180°	2099.0	99.7
0°-180°	2104.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	30	41	54	60	3
95°	46	96	150	198	224	143
105°	872	862	734	522	480	827
115°	602	608	608	606	601	607
125°	294	310	316	315	312	276
135°	174	177	184	185	187	137
145°	126	130	132	133	134	80
155°	101	103	104	105	105	47
165°	87	88	89	89	89	25
175°	78	79	79	80	80	8
180°	78	78	78	78	78	



TEST NUMBER: P828570

CATALOG NUMBER: OHBL-15HE-MCL-UNV-L950-CD-UPL24

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	4.3	29.6	40.9	53.9	60.0
92.5°	14.8	39.1	62.6	88.7	100.0
95°	46.1	96.5	149.5	198.2	224.3
97.5°	233.9	253.0	272.1	329.5	358.2
100°	479.9	509.5	411.2	434.7	442.5
102.5°	741.6	737.3	537.3	481.7	474.7
105°	872.1	862.5	733.8	522.5	479.9



TEST NUMBER: P828570

CATALOG NUMBER: OHBL-15HE-MCL-UNV-L950-CD-UPL24

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	702.5	712.9	699.0	679.0	651.2
115°	601.7	607.7	607.7	606.0	600.8
117.5°	514.7	515.6	519.1	518.2	519.1
120°	426.0	435.6	443.4	439.1	433.9
122.5°	357.3	367.8	373.0	371.3	366.0
125°	293.9	309.5	315.6	314.7	312.1
127.5°	248.7	260.0	268.7	269.5	268.7
130°	216.5	223.4	232.1	233.0	233.9
132.5°	192.1	198.2	204.3	207.8	206.9
135°	173.9	177.4	183.5	185.2	186.9
137.5°	159.1	161.7	166.9	169.5	169.5
140°	146.1	149.5	153.9	155.6	156.5
142.5°	134.8	138.2	141.7	143.5	143.5
145°	126.1	129.5	132.2	133.0	133.9
147.5°	118.2	121.7	123.5	125.2	125.2
150°	112.2	113.9	116.5	117.4	118.2
152.5°	106.1	107.8	110.4	111.3	111.3
155°	100.9	102.6	104.3	105.2	105.2
157.5°	96.5	98.2	100.0	100.9	100.9
160°	93.0	93.9	95.6	96.5	96.5
162.5°	89.6	90.4	91.3	92.2	92.2
165°	86.9	87.8	88.7	88.7	88.7
167.5°	84.3	84.3	85.2	86.1	86.1
170°	81.7	82.6	82.6	83.5	83.5
172.5°	80.0	80.9	80.9	80.9	81.7
175°	78.2	79.1	79.1	80.0	80.0
177.5°	78.2	78.2	78.2	78.2	78.2
180°	78.2	78.2	78.2	78.2	78.2



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	875.5	879.0	811.2	633.8	527.8
110°	807.7	815.5	776.4	709.5	624.3



(END OF REPORT)