

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P236391

Luminaire Tested: **SKB4-LD5-18-N-UNV-L835-CD2-U**

Issue Date: 3/3/2020



Test Information

Test Method: LM-79-08
Report Number: P236391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1710-365-8)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SKB4-LD5-18-N-UNV-L835-CD2-U
Description: METALUX SKYBAR LED WAVESTREAM LUMINAIRE
4 BLADES WITH NARROW DISTRIBUTION LENS, ALL BLADES VERTICAL
Light Source: (952) 3500K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19516.0 lumens
Efficiency: N/A
Efficacy: 136.1 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.56 / 1.53
Luminous Opening: Rectangular w/ Sides (W: 1.88' x L: 4' x H: 0.21')
CIE Type: Direct

Input Watts (W): 143.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P236391

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L835-CD2-U

Luminous Intensity Polar Plot





TEST NUMBER: P236391

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L835-CD2-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	93
1	107	103	99	95	104	100	96	93	94	91	89	89	87	85	85	83	81	78
2	98	90	84	78	95	88	82	77	83	78	74	79	75	71	75	72	69	66
3	90	80	72	66	87	78	71	65	74	68	63	70	65	61	67	63	59	57
4	83	71	63	57	80	70	62	56	66	60	54	63	57	53	60	55	51	49
5	76	64	55	49	74	63	55	49	60	53	47	57	51	46	55	49	45	43
6	71	58	49	43	68	57	49	43	54	47	42	52	46	41	50	44	40	38
7	66	53	44	38	64	51	44	38	49	42	37	47	41	36	45	40	36	34
8	61	48	40	34	59	47	39	34	45	38	33	44	37	33	42	36	32	30
9	57	44	36	31	55	43	36	31	42	35	30	40	34	30	39	33	29	27
10	54	41	33	28	52	40	33	28	39	32	27	37	31	27	36	30	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7579	7579	7579
5°	7590	8069	8583
10°	7508	9312	10538
15°	7373	10472	11842
20°	7207	11141	12365
25°	6962	11321	12234
30°	6645	11066	11368
35°	6259	10362	9924
40°	5813	9400	8422
45°	5281	8455	7266
50°	4669	7464	6430
55°	4012	6646	5732
60°	3428	5965	4955
65°	2813	5393	4317
70°	2325	4809	3787
75°	1917	4358	3416
80°	1655	4064	2962
85°	1517	3663	2585



TEST NUMBER: P236391

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L835-CD2-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	563.2	2.9
10°-20°	1959.0	10.0
20°-30°	3196.5	16.4
30°-40°	3575.9	18.3
40°-50°	3164.2	16.2
50°-60°	2450.6	12.6
60°-70°	1691.9	8.7
70°-80°	1052.0	5.4
80°-90°	522.4	2.7
90°-100°	217.4	1.1
100°-110°	182.0	0.9
110°-120°	200.1	1.0
120°-130°	207.7	1.1
130°-140°	203.4	1.0
140°-150°	175.6	0.9
150°-160°	111.1	0.6
160°-170°	39.0	0.2
170°-180°	4.1	0.0
0°-30°	5718.6	29.3
0°-40°	9294.5	47.6
0°-60°	14909.3	76.4
0°-90°	18175.6	93.1
90°-120°	599.4	3.1
90°-150°	1186.1	6.1
90°-180°	1340.0	6.9
0°-180°	19516.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5281	5281	5281	5281	5281	
5°	5292	5412	5658	5876	6015	502
15°	5032	5913	7266	7983	8208	1418
25°	4503	6085	7534	8072	8126	2069
35°	3703	5376	6392	6274	6105	2314
45°	2737	4087	4646	4266	3978	2103
55°	1722	2773	3094	2827	2654	1553
65°	921	1797	1981	1728	1574	929
75°	413	1180	1124	991	872	449
85°	147	652	516	412	356	143
90°	59	376	283	228	193	38
95°	64	268	210	164	146	53
105°	66	250	161	141	132	71
115°	59	337	210	159	143	59
125°	52	350	256	190	173	47
135°	42	314	354	244	212	33
145°	38	244	362	349	333	24
155°	38	109	312	346	346	18
165°	39	44	126	211	240	11
175°	38	38	39	40	34	4
180°	38	38	38	38	38	



TEST NUMBER: P236391

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L835-CD2-U

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6
2.5°	5308.5	5297.5	5298.2	5313.7	5321.7	5318.1	5329.8	5346.7	5367.3	5391.6	5400.4
5°	5292.3	5287.2	5310.0	5357.0	5396.0	5412.1	5435.6	5488.6	5545.9	5590.7	5657.6
7.5°	5257.8	5263.0	5316.6	5393.8	5473.1	5509.1	5551.7	5648.0	5787.6	5912.6	6062.5
10°	5199.0	5220.3	5311.5	5422.4	5546.6	5619.4	5702.4	5897.1	6124.9	6321.9	6519.5
12.5°	5131.4	5168.2	5282.1	5434.9	5642.1	5759.0	5894.9	6172.0	6444.6	6687.8	6927.4
15°	5031.5	5098.3	5240.9	5446.7	5749.4	5912.6	6077.2	6396.1	6720.1	7025.8	7266.1
17.5°	4920.5	5010.2	5179.9	5463.6	5838.3	6022.8	6205.0	6568.8	6941.3	7233.8	7486.6
20°	4808.1	4899.2	5099.1	5463.6	5885.4	6091.1	6292.5	6698.8	7056.0	7358.0	7601.2
22.5°	4657.4	4783.8	5007.2	5435.6	5892.7	6113.9	6334.4	6729.7	7091.2	7372.0	7610.0
25°	4503.1	4624.4	4902.9	5366.6	5847.9	6085.2	6296.1	6690.8	7034.7	7307.3	7533.6
27.5°	4326.0	4454.6	4767.7	5262.2	5755.3	5983.1	6191.8	6568.8	6911.2	7172.8	7378.6
30°	4130.6	4273.1	4614.1	5108.6	5599.5	5820.0	6025.7	6384.3	6709.9	6940.6	7122.1
32.5°	3941.7	4067.4	4424.5	4923.5	5401.8	5612.7	5804.5	6153.6	6440.2	6645.9	6789.2
35°	3702.9	3836.6	4212.9	4706.7	5163.0	5376.1	5534.1	5858.2	6121.3	6282.9	6392.4
37.5°	3475.8	3596.3	3974.8	4464.9	4888.9	5072.6	5241.6	5536.3	5766.3	5912.6	5967.7
40°	3238.5	3347.9	3719.8	4182.0	4582.5	4753.0	4911.7	5181.4	5383.5	5487.8	5503.2
42.5°	2987.1	3082.7	3453.0	3881.4	4259.9	4425.2	4582.5	4811.0	4984.4	5080.7	5063.8
45°	2737.3	2813.0	3176.0	3578.7	3931.4	4087.2	4213.6	4431.1	4589.1	4642.0	4646.4
47.5°	2466.1	2549.9	2892.3	3281.8	3611.8	3744.0	3856.5	4065.9	4193.0	4226.8	4207.0
50°	2220.7	2294.9	2609.4	2968.8	3282.5	3392.8	3513.3	3707.3	3798.4	3833.7	3802.8
52.5°	1968.6	2047.3	2341.9	2674.1	2951.1	3089.3	3179.7	3354.6	3429.5	3448.6	3436.9
55°	1722.5	1814.3	2092.1	2392.7	2663.8	2773.3	2885.0	3030.5	3095.2	3092.2	3093.7
57.5°	1505.0	1580.6	1849.6	2139.9	2397.8	2491.1	2591.1	2713.0	2774.0	2788.7	2787.3
60°	1302.1	1377.1	1637.2	1895.2	2145.0	2244.9	2323.6	2425.0	2478.6	2489.7	2493.3
62.5°	1104.5	1188.2	1434.4	1688.7	1922.4	2017.1	2086.2	2183.2	2217.0	2224.4	2246.4
65°	920.8	1018.5	1254.4	1506.4	1715.9	1796.7	1857.7	1939.3	1976.7	1999.5	1981.1
67.5°	766.4	871.5	1103.0	1349.9	1541.0	1615.2	1671.0	1734.2	1766.6	1770.2	1729.1
70°	633.4	745.9	969.3	1200.7	1384.4	1452.1	1502.8	1553.5	1547.6	1525.5	1509.4
72.5°	515.1	633.4	863.4	1078.8	1248.5	1308.8	1349.9	1380.0	1347.7	1333.0	1308.8
75°	413.0	538.6	772.3	975.1	1128.7	1180.2	1200.0	1194.9	1173.5	1151.5	1124.3
77.5°	327.7	458.5	684.9	880.3	1015.6	1047.9	1057.4	1038.3	1008.9	988.4	961.9
80°	259.4	393.9	612.1	793.6	889.2	911.9	917.8	891.4	859.8	842.1	813.5
82.5°	197.7	336.6	542.3	693.7	769.4	783.3	779.7	750.3	724.6	692.2	663.6
85°	147.0	282.2	467.4	588.6	643.0	652.5	643.7	612.9	585.7	553.3	515.9
87.5°	102.9	231.5	382.9	475.4	518.1	517.3	507.0	479.9	447.5	418.9	389.5
90°	58.8	164.6	281.4	343.2	373.3	375.5	367.4	343.9	324.8	307.9	282.9
92.5°	60.3	125.7	213.1	280.7	314.5	318.2	317.5	302.0	281.4	260.9	242.5
95°	63.9	104.3	166.1	220.5	257.9	268.2	272.6	263.8	248.4	230.0	210.2
97.5°	66.1	109.5	163.1	201.3	223.4	230.0	236.6	232.2	220.5	205.0	188.9
100°	68.3	120.5	175.6	208.0	222.7	222.7	219.0	210.2	202.8	191.1	176.4
102.5°	68.3	125.7	193.3	221.9	235.2	233.7	230.7	209.4	188.9	181.5	170.5
105°	66.1	127.9	210.2	246.2	249.1	249.8	244.0	226.3	201.3	180.0	160.9
107.5°	66.1	125.7	216.8	261.6	267.5	263.1	258.7	240.3	216.0	195.5	172.7
110°	64.7	123.5	219.7	282.2	297.6	282.2	272.6	254.3	230.0	206.5	188.9



TEST NUMBER: P236391

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L835-CD2-U

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	61.7	115.4	217.5	288.1	316.0	310.1	292.5	266.7	242.5	219.0	199.1
115°	58.8	103.6	210.9	288.8	328.5	336.6	332.1	283.6	254.3	230.7	210.2
117.5°	57.3	94.1	208.0	288.8	337.3	346.1	350.5	308.6	268.2	241.0	221.2
120°	55.8	82.3	201.3	285.9	338.0	352.7	358.6	354.2	288.1	253.5	230.0
122.5°	54.4	71.3	194.0	280.7	335.8	352.7	363.7	363.7	327.0	269.7	241.0
125°	52.2	63.9	174.9	271.2	331.4	349.8	363.0	370.4	357.9	297.6	256.5
127.5°	50.0	56.6	160.2	263.1	324.8	344.6	358.6	371.1	367.4	346.8	280.0
130°	47.8	50.0	141.8	256.5	315.2	336.6	352.7	369.6	368.2	362.3	338.0
132.5°	44.8	46.3	120.5	241.8	302.0	327.0	344.6	365.2	370.4	360.1	360.1
135°	41.9	42.6	97.7	210.9	290.3	314.5	335.8	359.3	368.9	365.2	354.2
137.5°	40.4	41.2	76.4	186.7	287.3	301.3	322.6	352.7	366.0	367.4	360.8
140°	39.7	39.7	61.0	165.3	270.4	296.1	308.6	342.4	360.1	366.0	363.7
142.5°	38.9	38.9	50.7	141.8	229.3	284.4	302.0	329.2	352.7	363.0	364.5
145°	38.2	38.9	44.8	113.9	199.9	244.0	294.7	313.8	341.0	356.4	362.3
147.5°	38.2	38.9	43.4	84.5	172.7	205.8	249.1	308.6	324.8	346.1	357.1
150°	38.2	38.2	42.6	60.3	142.6	179.3	210.9	290.3	310.8	330.7	345.4
152.5°	38.2	38.2	41.9	50.0	108.8	147.7	180.0	235.9	305.0	313.0	327.0
155°	38.2	38.2	41.2	45.6	73.5	108.8	146.2	196.9	247.6	305.7	312.3
157.5°	38.9	38.9	40.4	44.1	54.4	72.0	103.6	162.4	202.8	249.8	296.1
160°	38.9	38.9	39.7	43.4	47.0	52.2	63.9	113.9	163.1	195.5	229.3
162.5°	38.9	38.9	39.7	41.9	44.8	46.3	49.2	69.1	113.9	158.0	183.7
165°	38.9	38.9	38.9	40.4	43.4	44.1	45.6	50.0	63.2	92.6	126.4
167.5°	38.9	38.9	38.9	39.7	41.2	42.6	43.4	45.6	47.8	51.4	63.2
170°	38.9	38.9	38.9	38.9	39.7	40.4	41.2	42.6	44.1	44.8	46.3
172.5°	38.2	38.9	38.2	38.2	38.2	38.9	38.9	39.7	40.4	41.2	41.9
175°	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.9
177.5°	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2	37.5	37.5
180°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5



TEST NUMBER: P236391

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L835-CD2-U

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6	5280.6
2.5°	5415.1	5420.2	5422.4	5446.7	5448.9	5445.9	5449.6	5474.6	5475.3	5475.3
5°	5697.2	5750.9	5814.1	5858.9	5876.5	5883.2	5936.1	5961.8	5968.4	6015.4
7.5°	6205.0	6280.7	6374.0	6455.6	6502.6	6529.8	6579.1	6640.1	6665.8	6717.9
10°	6690.0	6840.7	6963.4	7068.5	7139.0	7166.2	7233.1	7312.4	7369.8	7372.7
12.5°	7129.5	7311.0	7453.5	7584.3	7625.5	7674.0	7753.3	7808.5	7859.9	7873.1
15°	7484.4	7651.2	7800.4	7931.9	7983.3	8018.6	8098.7	8158.2	8188.4	8207.5
17.5°	7707.0	7868.7	8007.6	8125.2	8165.6	8206.7	8274.3	8325.8	8359.6	8371.3
20°	7796.7	7951.7	8079.6	8190.6	8230.3	8265.5	8330.2	8381.6	8414.0	8423.5
22.5°	7795.2	7938.5	8067.9	8172.2	8213.4	8253.0	8317.7	8363.3	8394.9	8408.8
25°	7707.8	7852.5	7968.6	8050.2	8072.3	8095.8	8127.4	8132.5	8150.9	8125.9
27.5°	7532.9	7657.8	7715.1	7735.7	7732.8	7726.9	7705.6	7685.7	7682.8	7657.1
30°	7241.2	7313.9	7339.6	7322.0	7328.6	7284.5	7276.4	7264.7	7285.2	7299.9
32.5°	6865.6	6900.2	6864.2	6842.9	6828.2	6820.1	6825.2	6827.4	6820.8	6812.0
35°	6424.0	6391.7	6350.5	6286.6	6274.1	6249.1	6205.8	6174.2	6148.4	6105.1
37.5°	5947.8	5896.4	5853.0	5775.1	5723.7	5700.2	5609.1	5544.4	5479.7	5459.2
40°	5470.9	5409.2	5355.5	5268.1	5226.2	5179.2	5057.9	5005.8	4950.6	4914.6
42.5°	5025.6	4979.3	4897.0	4802.9	4725.8	4667.7	4572.2	4503.1	4463.4	4437.7
45°	4590.6	4531.0	4427.4	4326.0	4265.8	4207.0	4118.1	4056.3	3999.0	3977.7
47.5°	4179.8	4098.2	4015.2	3909.4	3844.0	3797.7	3738.2	3665.4	3619.8	3597.8
50°	3761.7	3699.9	3611.0	3510.4	3472.9	3424.4	3354.6	3302.4	3267.1	3261.2
52.5°	3393.5	3338.4	3259.0	3167.2	3120.9	3096.6	3029.8	2983.5	2963.6	2949.7
55°	3062.1	3013.6	2933.5	2863.0	2826.9	2800.5	2741.0	2697.6	2682.2	2654.3
57.5°	2750.5	2716.0	2658.7	2584.4	2560.2	2521.3	2453.6	2408.1	2364.7	2344.9
60°	2477.9	2436.7	2369.9	2304.5	2258.2	2217.0	2150.2	2104.6	2059.8	2058.3
62.5°	2217.8	2162.6	2084.8	2006.9	1975.3	1948.1	1877.5	1830.5	1804.8	1802.6
65°	1937.0	1885.6	1820.9	1765.1	1728.4	1703.4	1665.2	1615.9	1585.1	1574.0
67.5°	1687.2	1648.3	1596.8	1548.3	1522.6	1499.8	1443.2	1404.3	1373.4	1365.3
70°	1475.6	1440.3	1399.1	1344.0	1321.2	1295.5	1248.5	1206.6	1177.2	1178.0
72.5°	1280.1	1248.5	1210.3	1161.8	1138.3	1122.1	1078.8	1048.6	1022.2	1014.1
75°	1099.3	1072.1	1048.6	1007.5	990.6	970.0	929.6	901.7	881.1	871.5
77.5°	943.5	923.7	889.9	850.2	837.0	810.5	774.5	748.1	727.5	726.8
80°	785.5	755.4	727.5	691.5	675.3	657.7	622.4	599.6	584.9	584.2
82.5°	632.7	607.0	579.8	546.0	535.0	521.7	500.4	478.4	468.1	457.8
85°	495.3	471.0	448.3	426.2	412.2	404.9	382.9	374.0	357.9	356.4
87.5°	368.9	351.3	340.2	320.4	313.8	308.6	294.7	281.4	276.3	269.7
90°	264.5	249.8	241.8	229.3	227.8	220.5	214.6	205.0	196.9	193.3
92.5°	224.9	209.4	200.6	191.1	186.7	184.4	176.4	169.7	166.8	163.1
95°	194.0	181.5	173.4	166.8	163.9	160.9	155.8	152.1	147.7	145.5
97.5°	173.4	163.9	157.3	151.4	149.2	147.7	143.3	139.6	136.7	134.5
100°	163.1	153.6	147.7	143.3	140.4	138.9	135.2	132.3	130.1	128.6
102.5°	158.7	149.9	144.8	141.1	139.6	137.4	134.5	132.3	130.1	128.6
105°	155.8	149.9	144.8	141.8	141.1	139.6	136.7	135.2	133.7	131.5
107.5°	155.8	141.8	138.9	141.8	141.8	140.4	138.2	136.7	135.2	133.7
110°	169.7	155.1	145.5	137.4	133.7	131.5	129.3	130.8	132.3	130.1



TEST NUMBER: P236391

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L835-CD2-U

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
112.5°	183.0	169.0	157.3	147.7	144.8	141.8	140.4	138.9	135.9	135.2
115°	192.5	177.1	168.3	161.7	158.7	156.5	152.1	148.4	146.2	143.3
117.5°	202.8	186.7	174.9	166.8	164.6	163.1	160.9	158.7	156.5	155.1
120°	212.4	196.2	183.7	175.6	172.7	169.7	166.8	163.1	160.2	158.0
122.5°	220.5	205.8	193.3	183.7	181.5	178.6	174.2	170.5	166.8	165.3
125°	232.9	215.3	202.1	193.3	190.3	188.1	183.0	179.3	174.9	172.7
127.5°	246.9	227.8	213.8	202.8	199.1	195.5	190.3	185.9	182.2	180.8
130°	272.6	244.0	227.1	214.6	210.2	206.5	200.6	194.7	190.3	188.9
132.5°	332.9	277.8	245.4	229.3	224.1	217.5	210.9	205.0	199.9	198.4
135°	358.6	331.4	313.0	255.0	244.0	237.4	224.9	218.2	211.6	211.6
137.5°	349.8	352.7	345.4	322.6	316.7	309.4	265.3	242.5	233.7	231.5
140°	357.9	347.6	339.5	352.7	349.8	344.6	319.7	311.6	306.4	303.5
142.5°	361.5	356.4	348.3	340.2	338.0	335.1	340.2	345.4	345.4	343.2
145°	363.0	360.1	356.4	351.3	349.1	346.1	342.4	338.0	334.4	332.9
147.5°	360.8	360.8	358.6	356.4	354.2	352.7	349.1	346.1	342.4	341.0
150°	354.9	358.6	358.6	358.6	357.9	357.1	353.5	349.8	347.6	346.1
152.5°	341.7	349.8	354.2	355.7	356.4	357.9	357.9	357.1	354.9	353.5
155°	321.9	332.9	340.2	344.6	346.1	346.8	349.1	348.3	347.6	346.1
157.5°	311.6	311.6	321.9	330.7	332.1	334.4	336.6	336.6	334.4	333.6
160°	271.2	302.8	311.6	308.6	309.4	311.6	315.2	318.2	320.4	318.2
162.5°	205.0	227.1	255.0	282.2	291.0	297.6	308.6	307.9	305.7	305.0
165°	155.1	179.3	191.8	202.8	210.9	216.8	227.1	235.9	238.8	239.6
167.5°	88.2	108.0	128.6	144.8	151.4	160.2	163.9	172.0	174.2	170.5
170°	48.5	52.9	58.1	66.1	67.6	73.5	80.1	92.6	94.8	88.9
172.5°	43.4	44.1	44.8	45.6	45.6	45.6	45.6	45.6	43.4	41.2
175°	38.9	39.7	39.7	40.4	40.4	40.4	39.7	38.2	36.0	34.5
177.5°	37.5	37.5	37.5	37.5	37.5	37.5	36.7	34.5	32.3	30.9
180°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5

(END OF REPORT)