

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P219334

Luminaire Tested: **SSLED-LD5-12-N-UNV-L840-CD1-SA23-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P219334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27261)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SSLED-LD5-12-N-UNV-L840-CD1-SA23-U
Description: METALUX ROUND HIGH BAY STEELER LED WITH NARROW DISTRIBUTION LENS WITH Rev.G BOARD. LENS DIFFUSE 2407, 7.5% BLEND. SHROUD ACCESSORY INSTALLED. FIXTURE CENTERED TO LEDS
Light Source: (240) 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11713.8 lumens
Efficiency: N/A
Efficacy: 137.3 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Circular (Dia: 1.41' x H: 0')
CIE Type: Direct


Input Watts (W): 85.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219334

CATALOG NUMBER: SSLED-LD5-12-N-UNV-L840-CD1-SA23-U

Luminous Intensity Polar Plot





TEST NUMBER: P219334

CATALOG NUMBER: SSLED-LD5-12-N-UNV-L840-CD1-SA23-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78
4	95	87	81	77	94	86	81	76	84	79	76	82	78	75	80	77	74	72
5	90	81	75	70	89	80	74	70	78	73	69	77	72	69	75	71	68	67
6	85	76	69	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	49	56	52	48	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86877
5°	85518
10°	82111
15°	76229
20°	67543
25°	56046
30°	43769
35°	32547
40°	21685
45°	14037
50°	9059
55°	6163
60°	4280
65°	2735
70°	752
75°	490
80°	488
85°	688



TEST NUMBER: P219334

CATALOG NUMBER: SSLED-LD5-12-N-UNV-L840-CD1-SA23-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1159.9	9.9
10°-20°	2968.8	25.3
20°-30°	3358.9	28.7
30°-40°	2399.3	20.5
40°-50°	1153.1	9.8
50°-60°	477.2	4.1
60°-70°	166.1	1.4
70°-80°	21.5	0.2
80°-90°	8.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7487.6	63.9
0°-40°	9886.9	84.4
0°-60°	11517.2	98.3
0°-90°	11713.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11713.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12603	
5°	12358	###
15°	10681	2969
25°	7368	3359
35°	3868	2399
45°	1440	1153
55°	513	477
65°	168	166
75°	18	21
85°	9	9
90°	0	



TEST NUMBER: P219334

CATALOG NUMBER: SSLED-LD5-12-N-UNV-L840-CD1-SA23-U

CANDELA DISTRIBUTION (FULL):

	0°
0°	12602.7
2.5°	12540.8
5°	12358.3
7.5°	12088.9
10°	11730.4
12.5°	11258.5
15°	10681.2
17.5°	9998.1
20°	9207.1
22.5°	8326.6
25°	7368.5
27.5°	6418.4
30°	5498.6
32.5°	4647.8
35°	3867.5
37.5°	3052.0
40°	2409.8
42.5°	1872.9
45°	1439.8
47.5°	1100.8
50°	844.7
52.5°	656.0
55°	512.8
57.5°	401.4
60°	310.4
62.5°	234.7
65°	167.7
67.5°	100.2
70°	37.3
72.5°	23.5
75°	18.4
77.5°	14.8
80°	12.3
82.5°	10.7
85°	8.7
87.5°	7.2
90°	0.0

(END OF REPORT)