

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P219359

Luminaire Tested: **SSLED-LD5-15-M-UNV-L850-CD1-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P219359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27367)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SSLED-LD5-15-M-UNV-L850-CD1-U
Description: METALUX ROUND HIGH BAY STEELER LED WITH MEDIUM DISTRIBUTION LENS WITH Rev.G BOARD. LENS DIFFUSE 2407, 7.5% BLEND.
Light Source: (240) 5000K CCT, 80 CRI LEDs
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16105.9 lumens
Efficiency: N/A
Efficacy: 145.4 lumens/watt
Spacing Criteria (0/90/45): 1.3 / 1.3 / 1.2
Luminous Opening: Circular (Dia: 1.41' x H: 0')
CIE Type: Direct


Input Watts (W): 110.74
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219359

CATALOG NUMBER: SSLED-LD5-15-M-UNV-L850-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P219359

CATALOG NUMBER: SSLED-LD5-15-M-UNV-L850-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	91	89
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86	84	81	79
3	97	88	82	77	95	87	81	76	84	79	75		82	77	74		79	76	73	71
4	90	81	73	68	88	79	73	68	77	71	67		75	70	66		73	69	65	63
5	84	74	66	61	82	73	66	60	71	64	60		69	63	59		67	62	59	57
6	79	67	60	55	77	67	60	54	65	59	54		63	58	54		62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49		59	53	49		57	52	48	47
8	69	57	50	45	68	57	50	45	56	49	45		54	49	44		53	48	44	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	44	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57376
5°	58102
10°	60266
15°	63148
20°	65803
25°	66307
30°	62484
35°	53937
40°	42725
45°	31407
50°	22404
55°	16385
60°	12694
65°	10431
70°	9001
75°	8100
80°	7527
85°	7087



TEST NUMBER: P219359

CATALOG NUMBER: SSLED-LD5-15-M-UNV-L850-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	808.3	5.0
10°-20°	2507.7	15.6
20°-30°	3966.0	24.6
30°-40°	3962.2	24.6
40°-50°	2526.2	15.7
50°-60°	1261.0	7.8
60°-70°	648.1	4.0
70°-80°	326.5	2.0
80°-90°	100.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7282.0	45.2
0°-40°	11244.2	69.8
0°-60°	15031.3	93.3
0°-90°	16105.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	16105.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8323	
5°	8396	808
15°	8848	2508
25°	8718	3966
35°	6409	3962
45°	3222	2526
55°	1363	1261
65°	640	648
75°	304	326
85°	90	100
90°	0	



TEST NUMBER: P219359

CATALOG NUMBER: SSLED-LD5-15-M-UNV-L850-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°
0°	8323.2
2.5°	8346.7
5°	8396.4
7.5°	8485.4
10°	8609.6
12.5°	8732.5
15°	8848.3
17.5°	8937.8
20°	8969.9
22.5°	8909.7
25°	8717.5
27.5°	8365.7
30°	7849.8
32.5°	7190.0
35°	6409.3
37.5°	5576.3
40°	4747.8
42.5°	3951.4
45°	3221.6
47.5°	2602.4
50°	2089.1
52.5°	1681.8
55°	1363.3
57.5°	1116.2
60°	920.7
62.5°	765.0
65°	639.5
67.5°	535.5
70°	446.6
72.5°	370.1
75°	304.1
77.5°	245.9
80°	189.6
82.5°	138.6
85°	89.6
87.5°	44.5
90°	0.0

(END OF REPORT)