

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: METALUX

Report Number: P219462

Luminaire Tested: **SSLED-LD5-15-W-UNV-L835-CD1-SA23-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P219462  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27263)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: SSLED-LD5-15-W-UNV-L835-CD1-SA23-U  
Description: METALUX ROUND HIGH BAY STEELER LED WITH WIDE DISTRIBUTION LENS WITH Rev.G BOARD. LENS DIFFUSE 2407, 7.5% BLEND. SHROUD ACCESSORY INSTALLED. FIXTURE CENTERED TO LEDS  
Light Source: (240) 3500K CCT, 80 CRI LEDS  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13560.8 lumens  
Efficiency: N/A  
Efficacy: 122.5 lumens/watt  
Spacing Criteria (0/90/45): 1.7 / 1.7 / 1.49  
Luminous Opening: Circular (Dia: 1.41' x H: 0')  
CIE Type: Direct


Input Watts (W): 110.74  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219462

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L835-CD1-SA23-U

### Luminous Intensity Polar Plot





TEST NUMBER: P219462

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L835-CD1-SA23-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	80	72	67	88	78	72	67	76	70	66	74	69	65	72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	50	45	41	39
9	62	50	43	38	61	50	42	38	49	42	37	48	42	37	47	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	34571
5°	34609
10°	35150
15°	37187
20°	41303
25°	46430
30°	51166
35°	54483
40°	51673
45°	42662
50°	27215
55°	14944
60°	8089
65°	3799
70°	1195
75°	932
80°	965
85°	1028



TEST NUMBER: P219462

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L835-CD1-SA23-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	477.9	3.5
10°-20°	1498.3	11.0
20°-30°	2822.5	20.8
30°-40°	3955.4	29.2
40°-50°	3282.5	24.2
50°-60°	1208.9	8.9
60°-70°	262.3	1.9
70°-80°	39.0	0.3
80°-90°	13.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4798.8	35.4
0°-40°	8754.1	64.6
0°-60°	13245.6	97.7
0°-90°	13560.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13560.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5015	
5°	5001	478
15°	5211	1498
25°	6104	2823
35°	6474	3955
45°	4376	3283
55°	1243	1209
65°	233	262
75°	35	39
85°	13	14
90°	0	



TEST NUMBER: P219462

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L835-CD1-SA23-U

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5015.0
2.5°	5013.2
5°	5001.4
7.5°	4998.4
10°	5021.5
12.5°	5083.8
15°	5210.6
17.5°	5397.3
20°	5630.2
22.5°	5874.4
25°	6104.3
27.5°	6289.2
30°	6427.9
32.5°	6499.6
35°	6474.1
37.5°	6178.4
40°	5742.2
42.5°	5173.8
45°	4376.1
47.5°	3444.5
50°	2537.7
52.5°	1786.8
55°	1243.4
57.5°	870.6
60°	586.7
62.5°	387.6
65°	232.9
67.5°	126.8
70°	59.3
72.5°	42.1
75°	35.0
77.5°	29.0
80°	24.3
82.5°	19.6
85°	13.0
87.5°	6.5
90°	0.0

(END OF REPORT)