

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P219422

Luminaire Tested: **SSLED-LD5-15-W-UNV-L850-CD1-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P219422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27368)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SSLED-LD5-15-W-UNV-L850-CD1-U
Description: METALUX ROUND HIGH BAY STEELER LED WITH WIDE DISTRIBUTION LENS WITH Rev.G BOARD. LENS DIFFUSE 2407, 7.5% BLEND.
Light Source: (240) 5000K CCT, 80 CRI LEDs
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15935.2 lumens
Efficiency: N/A
Efficacy: 143.9 lumens/watt
Spacing Criteria (0/90/45): 1.9 / 1.9 / 1.7
Luminous Opening: Circular (Dia: 1.41' x H: 0')
CIE Type: Direct


Input Watts (W): 110.74
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219422

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L850-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P219422

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L850-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	81		87	83	80		84	81	78	76
3	94	85	77	72	92	83	76	71	80	74	70		77	73	69		75	71	67	65
4	86	75	67	61	84	74	67	61	72	65	60		69	64	59		67	63	59	57
5	79	67	59	53	77	66	59	53	64	57	52		62	56	52		61	55	51	49
6	73	61	52	46	71	60	52	46	58	51	46		56	50	45		55	49	45	43
7	68	55	46	41	66	54	46	40	52	45	40		51	45	40		50	44	40	38
8	63	50	41	36	61	49	41	36	48	41	36		46	40	35		45	39	35	33
9	58	45	37	32	57	45	37	32	44	37	32		43	36	32		42	36	31	30
10	54	42	34	29	53	41	34	29	40	33	28		39	33	28		38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31427
5°	31248
10°	31285
15°	32694
20°	36480
25°	41683
30°	47302
35°	52282
40°	56171
45°	56333
50°	47475
55°	32473
60°	18327
65°	9514
70°	6234
75°	5764
80°	5971
85°	5948



TEST NUMBER: P219422

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L850-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.4	2.7
10°-20°	1321.4	8.3
20°-30°	2545.9	16.0
30°-40°	3878.1	24.3
40°-50°	4322.7	27.1
50°-60°	2460.6	15.4
60°-70°	661.4	4.2
70°-80°	233.8	1.5
80°-90°	81.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4296.8	27.0
0°-40°	8174.8	51.3
0°-60°	14958.1	93.9
0°-90°	15935.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15935.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4559	
5°	4516	429
15°	4581	1321
25°	5480	2546
35°	6213	3878
45°	5778	4323
55°	2702	2461
65°	583	661
75°	216	234
85°	75	82
90°	0	



TEST NUMBER: P219422

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L850-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°
0°	4558.9
2.5°	4549.1
5°	4515.7
7.5°	4482.4
10°	4469.3
12.5°	4490.9
15°	4581.1
17.5°	4749.8
20°	4972.8
22.5°	5223.9
25°	5480.2
27.5°	5724.8
30°	5942.5
32.5°	6106.6
35°	6212.6
37.5°	6258.3
40°	6242.0
42.5°	6106.0
45°	5778.4
47.5°	5206.2
50°	4426.8
52.5°	3560.4
55°	2701.9
57.5°	1950.5
60°	1329.3
62.5°	881.4
65°	583.3
67.5°	406.7
70°	309.3
72.5°	253.7
75°	216.4
77.5°	186.4
80°	150.4
82.5°	111.2
85°	75.2
87.5°	39.2
90°	0.0

(END OF REPORT)