

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P219366

Luminaire Tested: **SSLED-LD5-30-M-UNV-L835-CD2-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P219366
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27367)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SSLED-LD5-30-M-UNV-L835-CD2-U
Description: METALUX ROUND HIGH BAY STEELER LED WITH MEDIUM DISTRIBUTION LENS WITH Rev.G BOARD. LENS DIFFUSE 2407, 7.5% BLEND.
Light Source: (240) 3500K CCT, 80 CRI LEDs
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 29076.7 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.3 / 1.3 / 1.2
Luminous Opening: Circular (Dia: 1.41' x H: 0')
CIE Type: Direct


Input Watts (W): 266.35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219366

CATALOG NUMBER: SSLED-LD5-30-M-UNV-L835-CD2-U

Luminous Intensity Polar Plot





TEST NUMBER: P219366

CATALOG NUMBER: SSLED-LD5-30-M-UNV-L835-CD2-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	91	89
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86	84	81	79
3	97	88	82	77	95	87	81	76	84	79	75		82	77	74		79	76	73	71
4	90	81	73	68	88	79	73	68	77	71	67		75	70	66		73	69	65	63
5	84	74	66	61	82	73	66	60	71	64	60		69	63	59		67	62	59	57
6	79	67	60	55	77	67	60	54	65	59	54		63	58	54		62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49		59	53	49		57	52	48	47
8	69	57	50	45	68	57	50	45	56	49	45		54	49	44		53	48	44	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	44	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103584
5°	104895
10°	108801
15°	114003
20°	118796
25°	119707
30°	112806
35°	97375
40°	77133
45°	56702
50°	40448
55°	29581
60°	22915
65°	18832
70°	16251
75°	14620
80°	13589
85°	12790



TEST NUMBER: P219366

CATALOG NUMBER: SSLED-LD5-30-M-UNV-L835-CD2-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1459.3	5.0
10°-20°	4527.2	15.6
20°-30°	7160.0	24.6
30°-40°	7153.1	24.6
40°-50°	4560.7	15.7
50°-60°	2276.5	7.8
60°-70°	1170.1	4.0
70°-80°	589.4	2.0
80°-90°	180.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	13146.5	45.2
0°-40°	20299.6	69.8
0°-60°	27136.7	93.3
0°-90°	29076.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	29076.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15026	
5°	15158	###
15°	15974	4527
25°	15738	7160
35°	11571	7153
45°	5816	4561
55°	2461	2276
65°	1154	1170
75°	549	589
85°	162	181
90°	0	



TEST NUMBER: P219366

CATALOG NUMBER: SSLED-LD5-30-M-UNV-L835-CD2-U

CANDELA DISTRIBUTION (FULL):

	0°
0°	15026.3
2.5°	15068.8
5°	15158.5
7.5°	15319.0
10°	15543.3
12.5°	15765.2
15°	15974.2
17.5°	16135.9
20°	16193.7
22.5°	16085.1
25°	15738.1
27.5°	15103.0
30°	14171.6
32.5°	12980.5
35°	11571.0
37.5°	10067.1
40°	8571.4
42.5°	7133.6
45°	5816.2
47.5°	4698.3
50°	3771.6
52.5°	3036.2
55°	2461.3
57.5°	2015.1
60°	1662.1
62.5°	1381.2
65°	1154.5
67.5°	966.8
70°	806.3
72.5°	668.1
75°	548.9
77.5°	443.9
80°	342.3
82.5°	250.3
85°	161.7
87.5°	80.3
90°	0.0

(END OF REPORT)