

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P826448

Luminaire Tested: **OHBL-12HE-MFL-UNV-L830-CD-UPL18**

Issue Date: 5/3/2024



Test Information

Test Method: LM-79-08
Report Number: P826448
REPORT IS A COMBINATION OF REPORTS P826145 AND G3-2310-221-8
Test Lab: INNOVATION CENTER
Issue Date: 5/3/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: OHBL-12HE-MFL-UNV-L830-CD-UPL18
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1665.6 lumens
Efficiency: N/A
Efficacy: 135.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.17')
CIE Type: Indirect

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P826448

CATALOG NUMBER: OHBL-12HE-MFL-UNV-L830-CD-UPL18

Luminous Intensity Polar Plot





TEST NUMBER: P826448

CATALOG NUMBER: OHBL-12HE-MFL-UNV-L830-CD-UPL18

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	9	9	9	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	2	2	2	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P826448

CATALOG NUMBER: OHBL-12HE-MFL-UNV-L830-CD-UPL18

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	4.2	0.3
90°-100°	159.3	9.6
100°-110°	553.3	33.2
110°-120°	475.4	28.5
120°-130°	228.3	13.7
130°-140°	114.0	6.8
140°-150°	66.2	4.0
150°-160°	38.6	2.3
160°-170°	20.0	1.2
170°-180°	6.1	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	4.2	0.3
90°-120°	1188.1	71.3
90°-150°	1596.6	95.9
90°-180°	1661.0	99.7
0°-180°	1665.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	23	32	42	46	3
95°	35	76	120	155	178	111
105°	690	683	582	410	379	654
115°	477	483	482	476	476	482
125°	233	244	250	249	248	219
135°	138	140	145	147	148	109
145°	100	102	105	106	106	64
155°	80	82	83	84	84	38
165°	69	70	70	71	71	20
175°	62	62	63	63	63	6
180°	62	62	62	62	62	



TEST NUMBER: P826448

CATALOG NUMBER: OHBL-12HE-MFL-UNV-L830-CD-UPL18

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.7	23.3	31.6	41.9	46.5
92.5°	12.1	30.7	51.2	70.7	78.2
95°	35.4	76.3	120.0	155.4	177.7
97.5°	181.5	198.2	221.5	262.4	277.3
100°	374.1	392.7	329.4	345.2	350.8
102.5°	585.3	584.4	422.5	381.5	375.9
105°	689.5	683.0	582.5	410.4	378.7



TEST NUMBER: P826448

CATALOG NUMBER: OHBL-12HE-MFL-UNV-L830-CD-UPL18

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	560.2	563.9	552.8	537.9	514.6
115°	477.4	483.0	482.0	476.4	475.5
117.5°	406.7	409.4	411.3	409.4	410.4
120°	339.7	346.2	349.9	347.1	345.2
122.5°	283.8	292.2	296.8	294.1	292.2
125°	232.6	243.8	250.3	249.4	247.5
127.5°	197.3	205.7	214.0	213.1	211.2
130°	171.2	177.7	183.3	184.2	185.2
132.5°	153.5	156.3	161.9	162.8	164.7
135°	137.7	140.5	145.2	147.0	148.0
137.5°	125.6	128.4	132.1	134.0	134.9
140°	115.4	118.2	121.0	122.8	123.8
142.5°	107.0	109.8	112.6	113.5	114.5
145°	100.5	102.4	105.2	106.1	106.1
147.5°	94.0	95.8	97.7	99.6	99.6
150°	88.4	90.3	92.1	93.1	94.0
152.5°	84.7	85.6	87.5	88.4	88.4
155°	80.0	81.9	82.8	83.8	83.8
157.5°	77.2	78.2	79.1	80.0	80.0
160°	74.4	74.4	75.4	76.3	76.3
162.5°	71.7	71.7	72.6	73.5	73.5
165°	68.9	69.8	69.8	70.7	70.7
167.5°	67.0	67.0	67.9	67.9	68.9
170°	65.1	65.1	66.1	66.1	66.1
172.5°	63.3	64.2	64.2	64.2	64.2
175°	62.3	62.3	63.3	63.3	63.3
177.5°	61.4	62.3	62.3	62.3	62.3
180°	62.3	62.3	62.3	62.3	62.3



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	696.1	696.1	642.1	498.8	417.8
110°	637.4	644.9	617.0	561.1	496.9



(END OF REPORT)