

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P828549

Luminaire Tested: **OHBL-12HE-N-UNV-L950-CD-UPL12**

Issue Date: 5/3/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P828549  
REPORT IS A COMBINATION OF REPORTS P826050 AND G3-2310-221-12  
Test Lab: INNOVATION CENTER  
Issue Date: 5/3/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: OHBL-12HE-N-UNV-L950-CD-UPL12  
Description:  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1082.7 lumens  
Efficiency: N/A  
Efficacy: 128.9 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.17')  
CIE Type: Indirect

Input Watts (W): 8.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P828549

CATALOG NUMBER: OHBL-12HE-N-UNV-L950-CD-UPL12

### Luminous Intensity Polar Plot





TEST NUMBER: P828549

CATALOG NUMBER: OHBL-12HE-N-UNV-L950-CD-UPL12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	9	9	9	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	2	2	2	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P828549

CATALOG NUMBER: OHBL-12HE-N-UNV-L950-CD-UPL12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.7	0.3
90°-100°	103.4	9.6
100°-110°	359.9	33.2
110°-120°	309.1	28.5
120°-130°	148.1	13.7
130°-140°	74.1	6.8
140°-150°	43.1	4.0
150°-160°	25.2	2.3
160°-170°	13.1	1.2
170°-180°	4.0	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.7	0.3
90°-120°	772.4	71.3
90°-150°	1037.8	95.9
90°-180°	1080.0	99.7
0°-180°	1082.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	16	21	27	30	2
95°	22	50	75	101	116	71
105°	450	444	379	269	247	425
115°	313	313	314	311	306	313
125°	153	159	163	161	162	143
135°	89	91	95	96	96	71
145°	65	67	68	69	70	41
155°	52	53	54	55	55	24
165°	45	45	46	46	46	13
175°	41	41	41	41	41	4
180°	40	40	40	40	40	



TEST NUMBER: P828549

CATALOG NUMBER: OHBL-12HE-N-UNV-L950-CD-UPL12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.6	15.6	20.9	27.0	30.4
92.5°	7.8	20.0	33.0	47.0	51.3
95°	21.7	50.4	74.8	100.9	116.5
97.5°	117.4	127.8	144.3	170.4	179.1
100°	240.0	258.2	214.8	224.3	228.7
102.5°	381.7	376.5	274.7	248.7	244.3
105°	449.5	444.3	379.1	268.7	246.9



TEST NUMBER: P828549

CATALOG NUMBER: OHBL-12HE-N-UNV-L950-CD-UPL12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	363.4	366.0	363.4	349.5	334.7
115°	313.0	313.0	313.9	311.3	306.0
117.5°	262.6	266.0	268.7	266.0	264.3
120°	220.0	225.2	226.9	223.4	223.4
122.5°	185.2	189.5	192.1	189.5	190.4
125°	153.0	159.1	162.6	160.8	161.7
127.5°	127.8	133.0	139.1	138.2	138.2
130°	111.3	114.8	119.1	120.0	120.0
132.5°	99.1	101.7	105.2	106.1	106.9
135°	88.7	91.3	94.8	95.6	95.6
137.5°	81.7	83.5	86.1	86.9	87.8
140°	74.8	77.4	79.1	80.0	80.0
142.5°	69.6	71.3	73.0	73.9	74.8
145°	65.2	66.9	67.8	68.7	69.6
147.5°	60.9	62.6	64.3	64.3	65.2
150°	58.3	59.1	60.0	60.9	60.9
152.5°	54.8	55.6	56.5	57.4	57.4
155°	52.2	53.0	53.9	54.8	54.8
157.5°	49.6	51.3	51.3	52.2	52.2
160°	47.8	48.7	49.6	49.6	49.6
162.5°	46.1	47.0	47.0	47.8	47.8
165°	45.2	45.2	46.1	46.1	46.1
167.5°	43.5	43.5	44.3	44.3	44.3
170°	42.6	42.6	42.6	43.5	43.5
172.5°	41.7	41.7	41.7	41.7	41.7
175°	40.9	40.9	40.9	40.9	40.9
177.5°	40.0	40.9	40.9	40.9	40.9
180°	40.0	40.0	40.0	40.0	40.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	452.1	453.8	418.2	324.3	268.7
110°	413.9	419.9	400.8	365.2	320.8



(END OF REPORT)