

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P826476

Luminaire Tested: **OHBL-15HE-NL-UNV-L830-CD-UPL24**

Issue Date: 5/3/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P826476  
REPORT IS A COMBINATION OF REPORTS P826219 AND G3-2310-221-6  
Test Lab: INNOVATION CENTER  
Issue Date: 5/3/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: OHBL-15HE-NL-UNV-L830-CD-UPL24  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2252.2 lumens  
Efficiency: N/A  
Efficacy: 129.4 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.1')  
CIE Type: Indirect  
  
Input Watts (W): 17.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P826476

CATALOG NUMBER: OHBL-15HE-NL-UNV-L830-CD-UPL24

### Luminous Intensity Polar Plot





TEST NUMBER: P826476

CATALOG NUMBER: OHBL-15HE-NL-UNV-L830-CD-UPL24

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	9	9	9	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	2	2	2	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P826476

CATALOG NUMBER: OHBL-15HE-NL-UNV-L830-CD-UPL24

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	5.7	0.3
90°-100°	215.8	9.6
100°-110°	749.0	33.3
110°-120°	642.5	28.5
120°-130°	308.2	13.7
130°-140°	154.2	6.8
140°-150°	89.4	4.0
150°-160°	52.1	2.3
160°-170°	27.0	1.2
170°-180°	8.2	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	5.7	0.3
90°-120°	1607.3	71.4
90°-150°	2159.2	95.9
90°-180°	2246.0	99.7
0°-180°	2252.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	5	32	44	58	64	3
95°	49	103	160	212	240	153
105°	933	923	785	559	514	886
115°	644	650	650	649	643	649
125°	314	331	338	337	334	295
135°	186	190	196	198	200	147
145°	135	139	141	142	143	86
155°	108	110	112	113	113	51
165°	93	94	95	95	95	27
175°	84	85	85	86	86	8
180°	84	84	84	84	84	



TEST NUMBER: P826476

CATALOG NUMBER: OHBL-15HE-NL-UNV-L830-CD-UPL24

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	4.7	31.6	43.7	57.7	64.2
92.5°	15.8	41.9	67.0	94.9	107.0
95°	49.3	103.3	160.1	212.2	240.1
97.5°	250.3	270.8	291.3	352.7	383.4
100°	513.7	545.3	440.2	465.3	473.7
102.5°	793.8	789.1	575.1	515.5	508.1
105°	933.3	923.1	785.4	559.3	513.7



TEST NUMBER: P826476

CATALOG NUMBER: OHBL-15HE-NL-UNV-L830-CD-UPL24

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	751.9	763.1	748.2	726.8	697.0
115°	643.9	650.5	650.5	648.6	643.0
117.5°	550.9	551.8	555.5	554.6	555.5
120°	456.0	466.2	474.6	469.9	464.3
122.5°	382.5	393.6	399.2	397.3	391.8
125°	314.5	331.3	337.8	336.9	334.1
127.5°	266.1	278.2	287.5	288.5	287.5
130°	231.7	239.2	248.5	249.4	250.3
132.5°	205.7	212.2	218.7	222.4	221.5
135°	186.1	189.8	196.3	198.2	200.1
137.5°	170.3	173.1	178.7	181.5	181.5
140°	156.3	160.1	164.7	166.6	167.5
142.5°	144.2	148.0	151.7	153.5	153.5
145°	134.9	138.7	141.4	142.4	143.3
147.5°	126.6	130.3	132.1	134.0	134.0
150°	120.0	121.9	124.7	125.6	126.6
152.5°	113.5	115.4	118.2	119.1	119.1
155°	107.9	109.8	111.7	112.6	112.6
157.5°	103.3	105.2	107.0	107.9	107.9
160°	99.6	100.5	102.4	103.3	103.3
162.5°	95.8	96.8	97.7	98.6	98.6
165°	93.1	94.0	94.9	94.9	94.9
167.5°	90.3	90.3	91.2	92.1	92.1
170°	87.5	88.4	88.4	89.3	89.3
172.5°	85.6	86.5	86.5	86.5	87.5
175°	83.8	84.7	84.7	85.6	85.6
177.5°	83.8	83.8	83.8	83.8	83.8
180°	83.8	83.8	83.8	83.8	83.8



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	937.1	940.8	868.2	678.4	564.8
110°	864.5	872.9	831.0	759.3	668.1



(END OF REPORT)