

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P236393

Luminaire Tested: **SKB4-LD5-18-N-UNV-L850-CD2-U**

Issue Date: 3/3/2020



Test Information

Test Method: LM-79-08
Report Number: P236393
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1710-365-8)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SKB4-LD5-18-N-UNV-L850-CD2-U
Description: METALUX SKYBAR LED WAVESTREAM LUMINAIRE
4 BLADES WITH NARROW DISTRIBUTION LENS, ALL BLADES VERTICAL
Light Source: (952) 5000K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20503.0 lumens
Efficiency: N/A
Efficacy: 143.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.56 / 1.53
Luminous Opening: Rectangular w/ Sides (W: 1.88' x L: 4' x H: 0.21')
CIE Type: Direct

Input Watts (W): 143.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P236393

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L850-CD2-U

Luminous Intensity Polar Plot





TEST NUMBER: P236393

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L850-CD2-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	93
1	107	103	99	95	104	100	96	93	94	91	89	89	87	85	85	83	81	78
2	98	90	84	78	95	88	82	77	83	78	74	79	75	71	75	72	69	66
3	90	80	72	66	87	78	71	65	74	68	63	70	65	61	67	63	59	57
4	83	71	63	57	80	70	62	56	66	60	54	63	57	53	60	55	51	49
5	76	64	55	49	74	63	55	49	60	53	47	57	51	46	55	49	45	43
6	71	58	49	43	68	57	49	43	54	47	42	52	46	41	50	44	40	38
7	66	53	44	38	64	51	44	38	49	42	37	47	41	36	45	40	36	34
8	61	48	40	34	59	47	39	34	45	38	33	44	37	33	42	36	32	30
9	57	44	36	31	55	43	36	31	42	35	30	40	34	30	39	33	29	27
10	54	41	33	28	52	40	33	28	39	32	27	37	31	27	36	30	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7962	7962	7962
5°	7974	8477	9017
10°	7887	9783	11071
15°	7746	11002	12441
20°	7571	11705	12990
25°	7314	11893	12853
30°	6982	11625	11943
35°	6576	10887	10426
40°	6107	9876	8848
45°	5548	8883	7634
50°	4905	7842	6755
55°	4214	6982	6022
60°	3602	6266	5205
65°	2955	5666	4535
70°	2443	5052	3978
75°	2014	4578	3589
80°	1739	4269	3111
85°	1594	3848	2716



TEST NUMBER: P236393

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L850-CD2-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	591.6	2.9
10°-20°	2058.0	10.0
20°-30°	3358.2	16.4
30°-40°	3756.7	18.3
40°-50°	3324.2	16.2
50°-60°	2574.5	12.6
60°-70°	1777.5	8.7
70°-80°	1105.2	5.4
80°-90°	548.8	2.7
90°-100°	228.4	1.1
100°-110°	191.1	0.9
110°-120°	210.3	1.0
120°-130°	218.2	1.1
130°-140°	213.7	1.0
140°-150°	184.4	0.9
150°-160°	116.7	0.6
160°-170°	41.0	0.2
170°-180°	4.3	0.0
0°-30°	6007.9	29.3
0°-40°	9764.6	47.6
0°-60°	15663.3	76.4
0°-90°	19094.8	93.1
90°-120°	629.8	3.1
90°-150°	1246.1	6.1
90°-180°	1408.0	6.9
0°-180°	20503.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5548	5548	5548	5548	5548	
5°	5560	5686	5944	6174	6320	528
15°	5286	6212	7634	8387	8623	1489
25°	4731	6393	7915	8480	8537	2173
35°	3890	5648	6716	6591	6414	2431
45°	2876	4294	4881	4482	4179	2210
55°	1810	2914	3250	2970	2788	1631
65°	967	1888	2081	1816	1654	976
75°	434	1240	1181	1041	916	471
85°	154	686	542	433	374	150
90°	62	394	297	239	203	40
95°	67	282	221	172	153	56
105°	70	262	169	148	138	74
115°	62	354	221	167	150	62
125°	55	368	269	200	181	49
135°	44	330	372	256	222	35
145°	40	256	381	367	350	25
155°	40	114	328	364	364	19
165°	41	46	133	222	252	12
175°	40	40	41	42	36	4
180°	39	39	39	39	39	



TEST NUMBER: P236393

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L850-CD2-U

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6
2.5°	5577.0	5565.4	5566.2	5582.4	5590.9	5587.0	5599.4	5617.1	5638.7	5664.2	5673.5
5°	5560.0	5554.6	5578.5	5627.9	5668.9	5685.8	5710.5	5766.1	5826.3	5873.4	5943.7
7.5°	5523.7	5529.1	5585.5	5666.5	5749.9	5787.7	5832.5	5933.7	6080.3	6211.6	6369.1
10°	5462.0	5484.3	5580.1	5696.6	5827.1	5903.5	5990.8	6195.4	6434.7	6641.6	6849.3
12.5°	5390.9	5429.5	5549.2	5709.8	5927.5	6050.2	6193.0	6484.1	6770.5	7026.0	7277.7
15°	5285.9	5356.2	5506.0	5722.1	6040.2	6211.6	6384.5	6719.6	7060.0	7381.2	7633.6
17.5°	5169.4	5263.6	5441.9	5739.9	6133.6	6327.4	6518.8	6901.0	7292.4	7599.6	7865.2
20°	5051.2	5147.0	5357.0	5739.9	6183.0	6399.2	6610.7	7037.6	7412.8	7730.1	7985.7
22.5°	4893.0	5025.8	5260.5	5710.5	6190.7	6423.1	6654.7	7070.0	7449.9	7744.8	7994.9
25°	4730.9	4858.2	5150.8	5638.0	6143.6	6393.0	6614.6	7029.1	7390.4	7676.8	7914.6
27.5°	4544.8	4679.9	5008.8	5528.3	6046.4	6285.7	6504.9	6901.0	7260.7	7535.6	7751.7
30°	4339.5	4489.2	4847.4	5367.0	5882.7	6114.3	6330.5	6707.2	7049.2	7291.6	7482.3
32.5°	4141.1	4273.1	4648.3	5172.5	5675.0	5896.6	6098.1	6464.8	6765.9	6982.0	7132.6
35°	3890.1	4030.7	4425.9	4944.7	5424.1	5648.0	5814.0	6154.4	6430.8	6600.7	6715.7
37.5°	3651.6	3778.2	4175.8	4690.7	5136.2	5329.2	5506.7	5816.3	6057.9	6211.6	6269.5
40°	3402.2	3517.3	3907.9	4393.5	4814.2	4993.3	5160.1	5443.4	5655.7	5765.4	5781.6
42.5°	3138.2	3238.6	3627.7	4077.7	4475.3	4649.0	4814.2	5054.3	5236.5	5337.7	5319.9
45°	2875.7	2955.2	3336.6	3759.7	4130.2	4293.9	4426.7	4655.2	4821.2	4876.8	4881.4
47.5°	2590.9	2678.9	3038.6	3447.8	3794.4	3933.4	4051.5	4271.5	4405.1	4440.6	4419.7
50°	2333.0	2411.0	2741.4	3118.9	3448.6	3564.4	3691.0	3894.8	3990.5	4027.6	3995.1
52.5°	2068.2	2150.8	2460.4	2809.3	3100.4	3245.5	3340.5	3524.2	3603.0	3623.0	3610.7
55°	1809.6	1906.1	2197.9	2513.7	2798.5	2913.6	3030.9	3183.8	3251.7	3248.6	3250.2
57.5°	1581.1	1660.6	1943.1	2248.1	2519.1	2617.1	2722.1	2850.3	2914.3	2929.8	2928.2
60°	1368.0	1446.7	1720.0	1991.0	2253.5	2358.5	2441.1	2547.6	2604.0	2615.6	2619.4
62.5°	1160.3	1248.3	1507.0	1774.1	2019.6	2119.2	2191.7	2293.6	2329.1	2336.9	2360.0
65°	967.3	1070.0	1317.8	1582.6	1802.6	1887.6	1951.6	2037.3	2076.7	2100.6	2081.3
67.5°	805.2	915.6	1158.8	1418.2	1618.9	1696.9	1755.5	1821.9	1855.9	1859.8	1816.5
70°	665.5	783.6	1018.3	1261.5	1454.5	1525.5	1578.8	1632.0	1625.8	1602.7	1585.7
72.5°	541.2	665.5	907.1	1133.3	1311.6	1374.9	1418.2	1449.8	1415.9	1400.4	1374.9
75°	433.9	565.9	811.4	1024.5	1185.8	1239.8	1260.7	1255.3	1232.9	1209.7	1181.2
77.5°	344.3	481.7	719.5	924.9	1066.9	1100.9	1110.9	1090.8	1060.0	1038.4	1010.6
80°	272.5	413.8	643.1	833.8	934.1	958.1	964.2	936.4	903.2	884.7	854.6
82.5°	207.7	353.6	569.7	728.8	808.3	823.0	819.1	788.2	761.2	727.2	697.1
85°	154.4	296.5	491.0	618.4	675.5	685.5	676.3	643.9	615.3	581.3	541.9
87.5°	108.1	243.2	402.2	499.5	544.3	543.5	532.7	504.1	470.2	440.0	409.2
90°	61.8	172.9	295.7	360.5	392.2	394.5	386.0	361.3	341.2	323.5	297.2
92.5°	63.3	132.0	223.9	294.9	330.4	334.3	333.5	317.3	295.7	274.1	254.8
95°	67.2	109.6	174.5	231.6	271.0	281.8	286.4	277.2	260.9	241.6	220.8
97.5°	69.5	115.0	171.4	211.5	234.7	241.6	248.6	244.0	231.6	215.4	198.4
100°	71.8	126.6	184.5	218.5	233.9	233.9	230.1	220.8	213.1	200.7	185.3
102.5°	71.8	132.0	203.0	233.1	247.0	245.5	242.4	220.0	198.4	190.7	179.1
105°	69.5	134.3	220.8	258.6	261.7	262.5	256.3	237.8	211.5	189.1	169.1
107.5°	69.5	132.0	227.7	274.8	281.0	276.4	271.7	252.4	227.0	205.4	181.4
110°	67.9	129.7	230.8	296.5	312.7	296.5	286.4	267.1	241.6	216.9	198.4



TEST NUMBER: P236393

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L850-CD2-U

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	64.8	121.2	228.5	302.6	332.0	325.8	307.3	280.2	254.8	230.1	209.2
115°	61.8	108.9	221.6	303.4	345.1	353.6	348.9	298.0	267.1	242.4	220.8
117.5°	60.2	98.8	218.5	303.4	354.4	363.6	368.2	324.2	281.8	253.2	232.4
120°	58.7	86.5	211.5	300.3	355.1	370.6	376.7	372.1	302.6	266.3	241.6
122.5°	57.1	74.9	203.8	294.9	352.8	370.6	382.1	382.1	343.5	283.3	253.2
125°	54.8	67.2	183.7	284.9	348.2	367.5	381.4	389.1	376.0	312.7	269.4
127.5°	52.5	59.4	168.3	276.4	341.2	362.1	376.7	389.9	386.0	364.4	294.1
130°	50.2	52.5	149.0	269.4	331.2	353.6	370.6	388.3	386.8	380.6	355.1
132.5°	47.1	48.6	126.6	254.0	317.3	343.5	362.1	383.7	389.1	378.3	378.3
135°	44.0	44.8	102.7	221.6	304.9	330.4	352.8	377.5	387.5	383.7	372.1
137.5°	42.5	43.2	80.3	196.1	301.9	316.5	338.9	370.6	384.5	386.0	379.1
140°	41.7	41.7	64.1	173.7	284.1	311.1	324.2	359.8	378.3	384.5	382.1
142.5°	40.9	40.9	53.3	149.0	240.9	298.8	317.3	345.9	370.6	381.4	382.9
145°	40.1	40.9	47.1	119.7	210.0	256.3	309.6	329.6	358.2	374.4	380.6
147.5°	40.1	40.9	45.5	88.8	181.4	216.2	261.7	324.2	341.2	363.6	375.2
150°	40.1	40.1	44.8	63.3	149.8	188.4	221.6	304.9	326.6	347.4	362.8
152.5°	40.1	40.1	44.0	52.5	114.3	155.2	189.1	247.8	320.4	328.9	343.5
155°	40.1	40.1	43.2	47.9	77.2	114.3	153.6	206.9	260.2	321.2	328.1
157.5°	40.9	40.9	42.5	46.3	57.1	75.7	108.9	170.6	213.1	262.5	311.1
160°	40.9	40.9	41.7	45.5	49.4	54.8	67.2	119.7	171.4	205.4	240.9
162.5°	40.9	40.9	41.7	44.0	47.1	48.6	51.7	72.6	119.7	166.0	193.0
165°	40.9	40.9	40.9	42.5	45.5	46.3	47.9	52.5	66.4	97.3	132.8
167.5°	40.9	40.9	40.9	41.7	43.2	44.8	45.5	47.9	50.2	54.0	66.4
170°	40.9	40.9	40.9	40.9	41.7	42.5	43.2	44.8	46.3	47.1	48.6
172.5°	40.1	40.9	40.1	40.1	40.1	40.9	40.9	41.7	42.5	43.2	44.0
175°	40.1	40.1	40.1	40.1	40.1	40.1	40.1	40.1	40.1	40.1	40.9
177.5°	40.1	40.1	40.1	40.1	40.1	40.1	40.1	40.1	40.1	39.4	39.4
180°	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4



TEST NUMBER: P236393

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L850-CD2-U

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6	5547.6
2.5°	5688.9	5694.3	5696.6	5722.1	5724.4	5721.4	5725.2	5751.5	5752.2	5752.2
5°	5985.4	6041.7	6108.1	6155.2	6173.7	6180.7	6236.3	6263.3	6270.2	6319.7
7.5°	6518.8	6598.4	6696.4	6782.1	6831.5	6860.1	6911.8	6975.9	7002.9	7057.7
10°	7028.4	7186.6	7315.5	7425.9	7500.1	7528.6	7598.9	7682.3	7742.5	7745.6
12.5°	7490.0	7680.7	7830.5	7967.9	8011.1	8062.1	8145.5	8203.4	8257.4	8271.3
15°	7862.9	8038.1	8194.9	8333.1	8387.1	8424.2	8508.3	8570.8	8602.5	8622.6
17.5°	8096.8	8266.7	8412.6	8536.1	8578.6	8621.8	8692.8	8746.9	8782.4	8794.7
20°	8191.0	8353.9	8488.2	8604.8	8646.5	8683.5	8751.5	8805.5	8839.5	8849.5
22.5°	8189.5	8340.0	8475.9	8585.5	8628.7	8670.4	8738.4	8786.2	8819.4	8834.1
25°	8097.6	8249.7	8371.7	8457.3	8480.5	8505.2	8538.4	8543.8	8563.1	8536.9
27.5°	7913.9	8045.1	8105.3	8126.9	8123.8	8117.7	8095.3	8074.4	8071.3	8044.3
30°	7607.4	7683.8	7710.8	7692.3	7699.2	7652.9	7644.4	7632.1	7653.7	7669.1
32.5°	7212.9	7249.2	7211.3	7188.9	7173.5	7165.0	7170.4	7172.7	7165.8	7156.5
35°	6748.9	6714.9	6671.7	6604.5	6591.4	6565.2	6519.6	6486.4	6459.4	6413.8
37.5°	6248.6	6194.6	6149.0	6067.2	6013.2	5988.5	5892.7	5824.8	5756.9	5735.2
40°	5747.6	5682.8	5626.4	5534.5	5490.5	5441.1	5313.7	5258.9	5201.0	5163.2
42.5°	5279.8	5231.1	5144.7	5045.8	4964.8	4903.8	4803.4	4730.9	4689.2	4662.2
45°	4822.7	4760.2	4651.3	4544.8	4481.5	4419.7	4326.3	4261.5	4201.3	4178.9
47.5°	4391.2	4305.5	4218.3	4107.1	4038.4	3989.7	3927.2	3850.8	3802.9	3779.8
50°	3951.9	3887.1	3793.6	3687.9	3648.5	3597.6	3524.2	3469.4	3432.3	3426.2
52.5°	3565.1	3507.2	3423.9	3327.4	3278.7	3253.2	3183.0	3134.4	3113.5	3098.8
55°	3217.0	3166.0	3081.9	3007.7	2969.9	2942.1	2879.6	2834.0	2817.8	2788.5
57.5°	2889.6	2853.3	2793.1	2715.2	2689.7	2648.8	2577.7	2529.9	2484.3	2463.5
60°	2603.2	2560.0	2489.7	2421.0	2372.4	2329.1	2258.9	2211.0	2163.9	2162.4
62.5°	2329.9	2272.0	2190.2	2108.4	2075.2	2046.6	1972.5	1923.1	1896.1	1893.7
65°	2035.0	1981.0	1913.0	1854.4	1815.8	1789.5	1749.4	1697.6	1665.2	1653.6
67.5°	1772.5	1731.6	1677.6	1626.6	1599.6	1575.7	1516.2	1475.3	1442.9	1434.4
70°	1550.2	1513.1	1469.9	1412.0	1388.1	1361.1	1311.6	1267.6	1236.8	1237.5
72.5°	1344.8	1311.6	1271.5	1220.5	1195.8	1178.9	1133.3	1101.7	1073.9	1065.4
75°	1154.9	1126.4	1101.7	1058.4	1040.7	1019.1	976.6	947.3	925.6	915.6
77.5°	991.3	970.4	934.9	893.2	879.3	851.5	813.7	785.9	764.3	763.5
80°	825.3	793.6	764.3	726.5	709.5	690.9	653.9	630.0	614.5	613.7
82.5°	664.7	637.7	609.1	573.6	562.0	548.1	525.7	502.6	491.8	481.0
85°	520.3	494.9	470.9	447.8	433.1	425.4	402.2	393.0	376.0	374.4
87.5°	387.5	369.0	357.4	336.6	329.6	324.2	309.6	295.7	290.3	283.3
90°	277.9	262.5	254.0	240.9	239.3	231.6	225.4	215.4	206.9	203.0
92.5°	236.2	220.0	210.8	200.7	196.1	193.8	185.3	178.3	175.2	171.4
95°	203.8	190.7	182.2	175.2	172.2	169.1	163.7	159.8	155.2	152.9
97.5°	182.2	172.2	165.2	159.0	156.7	155.2	150.5	146.7	143.6	141.3
100°	171.4	161.3	155.2	150.5	147.5	145.9	142.0	139.0	136.6	135.1
102.5°	166.8	157.5	152.1	148.2	146.7	144.4	141.3	139.0	136.6	135.1
105°	163.7	157.5	152.1	149.0	148.2	146.7	143.6	142.0	140.5	138.2
107.5°	163.7	149.0	145.9	149.0	149.0	147.5	145.1	143.6	142.0	140.5
110°	178.3	162.9	152.9	144.4	140.5	138.2	135.9	137.4	139.0	136.6



TEST NUMBER: P236393

CATALOG NUMBER: SKB4-LD5-18-N-UNV-L850-CD2-U

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
112.5°	192.2	177.6	165.2	155.2	152.1	149.0	147.5	145.9	142.8	142.0
115°	202.3	186.1	176.8	169.8	166.8	164.4	159.8	155.9	153.6	150.5
117.5°	213.1	196.1	183.7	175.2	172.9	171.4	169.1	166.8	164.4	162.9
120°	223.1	206.1	193.0	184.5	181.4	178.3	175.2	171.4	168.3	166.0
122.5°	231.6	216.2	203.0	193.0	190.7	187.6	183.0	179.1	175.2	173.7
125°	244.7	226.2	212.3	203.0	200.0	197.6	192.2	188.4	183.7	181.4
127.5°	259.4	239.3	224.7	213.1	209.2	205.4	200.0	195.3	191.5	189.9
130°	286.4	256.3	238.6	225.4	220.8	216.9	210.8	204.6	200.0	198.4
132.5°	349.7	291.8	257.9	240.9	235.5	228.5	221.6	215.4	210.0	208.4
135°	376.7	348.2	328.9	267.9	256.3	249.4	236.2	229.3	222.3	222.3
137.5°	367.5	370.6	362.8	338.9	332.7	325.0	278.7	254.8	245.5	243.2
140°	376.0	365.2	356.7	370.6	367.5	362.1	335.8	327.3	321.9	318.8
142.5°	379.8	374.4	365.9	357.4	355.1	352.0	357.4	362.8	362.8	360.5
145°	381.4	378.3	374.4	369.0	366.7	363.6	359.8	355.1	351.3	349.7
147.5°	379.1	379.1	376.7	374.4	372.1	370.6	366.7	363.6	359.8	358.2
150°	372.9	376.7	376.7	376.7	376.0	375.2	371.3	367.5	365.2	363.6
152.5°	359.0	367.5	372.1	373.7	374.4	376.0	376.0	375.2	372.9	371.3
155°	338.1	349.7	357.4	362.1	363.6	364.4	366.7	365.9	365.2	363.6
157.5°	327.3	327.3	338.1	347.4	348.9	351.3	353.6	353.6	351.3	350.5
160°	284.9	318.1	327.3	324.2	325.0	327.3	331.2	334.3	336.6	334.3
162.5°	215.4	238.6	267.9	296.5	305.7	312.7	324.2	323.5	321.2	320.4
165°	162.9	188.4	201.5	213.1	221.6	227.7	238.6	247.8	250.9	251.7
167.5°	92.6	113.5	135.1	152.1	159.0	168.3	172.2	180.6	183.0	179.1
170°	51.0	55.6	61.0	69.5	71.0	77.2	84.1	97.3	99.6	93.4
172.5°	45.5	46.3	47.1	47.9	47.9	47.9	47.9	47.9	45.5	43.2
175°	40.9	41.7	41.7	42.5	42.5	42.5	41.7	40.1	37.8	36.3
177.5°	39.4	39.4	39.4	39.4	39.4	39.4	38.6	36.3	34.0	32.4
180°	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4

(END OF REPORT)