

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P236534

Luminaire Tested: **SKB4-LD5-36-W-UNV-L850-CD4-U all blades horizontal**

Issue Date: 3/3/2020



Test Information

Test Method: LM-79-08
Report Number: P236534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P24075)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SKB4-LD5-36-W-UNV-L850-CD4-U all blades horizontal
Description: METALUX SKYBAR LED WAVESTREAM LUMINAIRE
4 BLADES WITH WIDE DISTRIBUTION LENS, ALL BLADES HORIZONTAL
Light Source: (952) 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 30536.0 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 2.46 / 2.11
Luminous Opening: Rectangular (W 1.88' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 333.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P236534

CATALOG NUMBER: SKB4-LD5-36-W-UNV-L850-CD4-U all blades horizontal

Luminous Intensity Polar Plot





TEST NUMBER: P236534

CATALOG NUMBER: SKB4-LD5-36-W-UNV-L850-CD4-U all blades horizontal

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68
1	99	93	87	83	93	87	83	78	77	74	70	68	65	62	59	57	55	51
2	88	78	71	64	82	74	67	61	65	59	55	57	53	49	50	46	43	39
3	79	67	58	51	74	63	55	48	56	49	44	49	43	39	42	38	34	31
4	71	58	49	42	67	55	46	40	48	41	36	42	37	32	37	32	28	25
5	65	51	42	35	61	48	40	33	43	35	30	37	31	27	32	27	23	20
6	60	45	36	29	56	43	34	28	38	31	25	33	27	22	29	24	20	17
7	55	41	32	25	51	38	30	24	34	27	22	30	24	19	26	21	17	15
8	51	37	28	22	47	35	26	21	31	24	19	27	21	17	23	19	15	13
9	47	33	25	19	44	31	24	18	28	21	17	25	19	15	21	17	13	11
10	44	30	22	17	41	29	21	16	26	19	15	23	17	13	20	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4516	4516	4516
5°	4548	4535	4552
10°	4572	4665	4775
15°	4607	4864	5125
20°	4646	5147	5654
25°	4705	5531	6454
30°	4783	6073	7475
35°	4909	6775	8736
40°	5100	7616	10213
45°	5349	8600	11947
50°	5636	9729	13925
55°	5903	10989	16121
60°	6149	12412	18387
65°	6315	13922	16884
70°	6416	14457	18656
75°	6456	15367	21421
80°	6390	18689	29393
85°	6289	30772	47920



TEST NUMBER: P236534

CATALOG NUMBER: SKB4-LD5-36-W-UNV-L850-CD4-U all blades horizontal

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.3	1.0
10°-20°	933.5	3.1
20°-30°	1635.8	5.4
30°-40°	2448.1	8.0
40°-50°	3299.2	10.8
50°-60°	3938.8	12.9
60°-70°	3724.2	12.2
70°-80°	2844.8	9.3
80°-90°	1774.9	5.8
90°-100°	189.5	0.6
100°-110°	996.7	3.3
110°-120°	1749.9	5.7
120°-130°	2183.4	7.2
130°-140°	1900.7	6.2
140°-150°	1269.3	4.2
150°-160°	730.3	2.4
160°-170°	454.9	1.5
170°-180°	158.7	0.5
0°-30°	2872.6	9.4
0°-40°	5320.7	17.4
0°-60°	12558.7	41.1
0°-90°	20902.6	68.5
90°-120°	2936.1	9.6
90°-150°	8289.5	27.1
90°-180°	9633.0	31.5
0°-180°	30536.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3147	3147	3147	3147	3147	
5°	3157	3173	3148	3159	3160	301
15°	3100	3169	3274	3398	3449	876
25°	2971	3138	3493	3918	4076	1372
35°	2802	3102	3867	4698	4986	1759
45°	2635	3092	4237	5463	5886	2036
55°	2359	2997	4392	5902	6443	2106
65°	1860	2598	4100	4756	4972	1833
75°	1164	1904	2771	3535	3863	1223
85°	382	833	1869	2590	2910	391
90°	16	100	386	750	960	34
95°	200	106	18	11	7	233
105°	852	970	975	936	862	890
115°	1349	1663	1681	1887	2396	1324
125°	1686	1767	2627	3227	3108	1500
135°	1742	1441	2561	3172	3426	1347
145°	1620	1525	1692	2650	2914	1029
155°	1660	1603	1400	1529	1575	770
165°	1726	1696	1624	1626	1466	488
175°	1766	1747	1666	1544	1714	168
180°	1676	1676	1676	1676	1676	



TEST NUMBER: P236534

CATALOG NUMBER: SKB4-LD5-36-W-UNV-L850-CD4-U all blades horizontal

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3146.7	3146.7	3146.7	3146.7	3146.7	3146.7	3146.7	3146.7	3146.7	3146.7	3146.7
2.5°	3159.9	3159.9	3167.8	3167.8	3173.1	3173.1	3169.1	3159.9	3153.3	3140.1	3132.1
5°	3157.2	3155.9	3166.5	3166.5	3173.1	3173.1	3169.1	3163.9	3157.2	3148.0	3144.0
7.5°	3150.6	3150.6	3159.9	3162.5	3170.5	3175.7	3177.1	3174.4	3174.4	3170.5	3169.1
10°	3137.4	3140.1	3150.6	3159.9	3179.7	3192.9	3199.5	3202.2	3203.5	3200.9	3203.5
12.5°	3121.6	3124.2	3141.4	3154.6	3166.5	3182.4	3195.6	3208.8	3223.3	3233.9	3247.1
15°	3100.4	3103.1	3120.2	3132.1	3155.9	3182.4	3204.8	3227.3	3253.7	3273.5	3293.4
17.5°	3075.3	3078.0	3093.8	3113.6	3148.0	3182.4	3214.1	3248.4	3286.8	3318.5	3351.5
20°	3042.3	3046.2	3066.1	3092.5	3134.8	3179.7	3223.3	3270.9	3323.8	3370.0	3417.6
22.5°	3009.2	3011.9	3037.0	3070.0	3120.2	3175.7	3231.3	3294.7	3363.4	3428.2	3495.6
25°	2970.9	2973.5	3003.9	3044.9	3104.4	3171.8	3243.1	3319.8	3411.0	3492.9	3582.8
27.5°	2928.6	2932.6	2969.6	3018.5	3087.2	3167.8	3255.0	3351.5	3461.2	3569.6	3688.5
30°	2886.3	2890.3	2932.6	2989.4	3070.0	3165.2	3269.6	3384.6	3526.0	3664.7	3808.8
32.5°	2844.0	2850.6	2898.2	2961.7	3054.2	3163.9	3288.1	3429.5	3603.9	3765.2	3935.7
35°	2801.7	2808.3	2862.5	2933.9	3039.6	3165.2	3309.2	3482.4	3683.2	3866.9	4062.5
37.5°	2760.8	2770.0	2828.2	2908.8	3025.1	3170.5	3340.9	3539.2	3759.9	3967.4	4188.1
40°	2722.4	2731.7	2793.8	2883.7	3013.2	3177.1	3376.6	3596.0	3840.5	4065.2	4311.0
42.5°	2681.5	2692.1	2759.5	2857.2	3000.0	3190.3	3409.7	3652.8	3913.2	4160.3	4419.4
45°	2635.2	2648.4	2718.5	2825.5	2982.8	3200.9	3438.7	3701.7	3974.0	4237.0	4523.8
47.5°	2586.3	2598.2	2672.2	2789.8	2964.3	3204.8	3457.2	3729.5	4018.9	4307.0	4614.9
50°	2524.2	2537.4	2615.4	2743.6	2940.5	3198.2	3457.2	3746.7	4053.3	4357.2	4683.7
52.5°	2451.5	2466.1	2549.3	2688.1	2904.8	3178.4	3445.3	3745.3	4063.8	4387.6	4729.9
55°	2359.0	2378.8	2467.4	2622.0	2858.6	3136.1	3405.7	3721.6	4054.6	4391.6	4748.4
57.5°	2259.9	2275.8	2372.2	2542.7	2793.8	3071.3	3351.5	3675.3	4017.6	4370.5	4741.8
60°	2142.3	2158.1	2263.9	2448.9	2706.6	2977.5	3273.5	3600.0	3960.8	4324.2	4696.9
62.5°	2007.5	2024.7	2138.3	2340.5	2595.6	2867.8	3171.8	3510.1	3878.8	4237.0	4593.8
65°	1859.5	1876.6	2002.2	2216.3	2455.5	2739.6	3054.2	3397.8	3761.2	4099.5	4465.6
67.5°	1699.5	1720.7	1862.1	2074.9	2310.1	2592.9	2912.8	3255.0	3594.7	3950.2	4108.8
70°	1529.1	1554.2	1706.2	1908.4	2143.6	2431.7	2750.2	3071.3	3413.6	3445.3	3403.1
72.5°	1349.3	1385.0	1546.2	1729.9	1962.5	2248.0	2545.4	2871.8	2836.1	2984.1	3215.4
75°	1164.3	1206.6	1369.2	1539.6	1772.2	2036.5	2339.2	2345.8	2553.3	2771.3	2973.5
77.5°	971.4	1037.4	1174.9	1344.0	1559.5	1819.8	1892.5	2090.7	2303.5	2501.7	2713.2
80°	773.1	856.4	972.7	1136.6	1338.8	1422.0	1613.6	1825.1	2053.7	2261.2	2448.9
82.5°	574.9	663.4	765.2	902.6	984.6	1149.8	1359.9	1575.3	1821.1	2085.4	2345.8
85°	381.9	452.0	527.3	598.7	736.1	929.1	1207.9	1472.2	1695.6	1868.7	2060.3
87.5°	186.3	232.6	286.8	412.3	590.7	718.9	872.2	1033.5	1202.6	1374.4	1560.8
90°	15.9	18.5	21.1	39.6	79.3	121.6	204.8	247.1	333.0	385.9	478.4
92.5°	31.7	27.8	18.5	13.2	11.9	10.6	7.9	6.6	4.0	1.3	0.0
95°	199.6	215.4	181.1	134.8	117.6	95.2	59.5	39.6	26.4	18.5	14.5
97.5°	367.4	412.3	408.4	344.9	313.2	284.1	239.2	244.5	215.4	178.4	145.4
100°	549.8	626.4	610.6	567.0	528.6	518.1	483.7	465.2	416.3	397.8	416.3
102.5°	733.5	794.3	808.8	851.1	734.8	718.9	720.3	720.3	708.4	691.2	663.4
105°	852.4	902.6	956.8	1005.7	1071.8	868.3	849.8	922.5	970.0	975.3	980.6
107.5°	959.5	993.8	1087.7	1151.1	1225.1	1272.7	992.5	996.5	1124.7	1206.6	1267.4
110°	1103.5	1116.7	1173.6	1304.4	1369.2	1485.5	1465.6	1167.0	1120.7	1244.9	1460.3



TEST NUMBER: P236534

CATALOG NUMBER: SKB4-LD5-36-W-UNV-L850-CD4-U all blades horizontal

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1234.4	1231.7	1211.9	1414.1	1501.3	1597.8	1772.2	1723.3	1392.9	1313.6	1359.9
115°	1349.3	1328.2	1250.2	1437.9	1615.0	1710.1	1855.5	2073.6	1999.5	1681.0	1547.6
117.5°	1445.8	1411.4	1337.4	1433.9	1708.8	1813.2	1940.1	2133.0	2355.0	2302.2	2070.9
120°	1531.7	1494.7	1444.5	1420.7	1700.9	1912.3	2039.2	2195.1	2398.7	2603.5	2620.7
122.5°	1611.0	1572.7	1556.8	1407.5	1637.4	1983.7	2109.2	2258.6	2427.7	2624.7	2818.9
125°	1686.3	1642.7	1640.1	1422.0	1581.9	1952.0	2183.2	2322.0	2462.1	2627.3	2813.6
127.5°	1744.5	1700.9	1696.9	1466.9	1538.3	1821.1	2204.4	2351.1	2497.8	2623.3	2803.1
130°	1784.1	1745.8	1723.3	1560.8	1466.9	1707.5	2080.2	2366.9	2487.2	2633.9	2778.0
132.5°	1778.8	1748.4	1710.1	1622.9	1426.0	1613.6	1874.0	2275.8	2471.3	2592.9	2764.7
135°	1741.8	1723.3	1679.7	1653.3	1414.1	1468.3	1702.2	2027.3	2397.3	2561.2	2700.0
137.5°	1706.2	1696.9	1648.0	1646.7	1468.3	1404.8	1599.1	1806.6	2162.1	2479.3	2635.2
140°	1665.2	1663.9	1618.9	1620.3	1530.4	1362.5	1445.8	1645.4	1891.2	2221.6	2515.0
142.5°	1636.1	1638.8	1593.8	1587.2	1566.1	1383.7	1386.3	1562.1	1687.7	1913.6	2228.2
145°	1620.3	1621.6	1579.3	1563.4	1567.4	1482.8	1349.3	1410.1	1596.5	1691.6	1908.4
147.5°	1634.8	1626.9	1571.4	1541.0	1560.8	1533.0	1395.6	1359.9	1424.7	1596.5	1677.1
150°	1654.6	1645.4	1593.8	1543.6	1552.9	1576.6	1517.2	1381.0	1373.1	1424.7	1589.9
152.5°	1652.0	1655.9	1633.5	1592.5	1581.9	1597.8	1576.6	1502.6	1386.3	1377.1	1419.4
155°	1659.9	1661.2	1654.6	1620.3	1600.4	1605.7	1595.1	1570.0	1510.6	1399.5	1377.1
157.5°	1677.1	1678.4	1667.8	1638.8	1616.3	1611.0	1611.0	1608.4	1585.9	1551.5	1439.2
160°	1694.3	1695.6	1691.6	1669.2	1645.4	1630.8	1622.9	1629.5	1626.9	1615.0	1584.6
162.5°	1711.4	1710.1	1714.1	1699.5	1674.4	1659.9	1640.1	1636.1	1636.1	1636.1	1634.8
165°	1726.0	1724.7	1729.9	1724.7	1707.5	1685.0	1663.9	1645.4	1634.8	1624.2	1630.8
167.5°	1737.9	1736.6	1740.5	1741.8	1733.9	1715.4	1687.7	1667.8	1644.0	1618.9	1605.7
170°	1748.4	1747.1	1749.8	1752.4	1747.1	1737.9	1710.1	1691.6	1666.5	1633.5	1601.8
172.5°	1759.0	1755.1	1755.1	1755.1	1751.1	1743.2	1723.3	1707.5	1687.7	1659.9	1626.9
175°	1765.6	1761.7	1760.3	1756.4	1751.1	1743.2	1724.7	1707.5	1687.7	1666.5	1640.1
177.5°	1768.3	1764.3	1761.7	1757.7	1751.1	1741.8	1722.0	1702.2	1678.4	1652.0	1628.2
180°	1675.8	1675.8	1675.8	1675.8	1675.8	1675.8	1675.8	1675.8	1675.8	1675.8	1675.8



TEST NUMBER: P236534

CATALOG NUMBER: SKB4-LD5-36-W-UNV-L850-CD4-U all blades horizontal

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	3146.7	3146.7	3146.7	3146.7	3146.7	3146.7	3146.7	3146.7
2.5°	3126.8	3132.1	3134.8	3140.1	3138.7	3140.1	3148.0	3140.1
5°	3142.7	3150.6	3155.9	3162.5	3161.2	3161.2	3166.5	3159.9
7.5°	3171.8	3185.0	3195.6	3204.8	3203.5	3206.1	3214.1	3204.8
10°	3211.4	3231.3	3245.8	3260.3	3265.6	3269.6	3280.2	3276.2
12.5°	3261.6	3290.7	3311.9	3330.4	3338.3	3347.6	3359.4	3352.8
15°	3321.1	3358.1	3385.9	3411.0	3424.2	3438.7	3454.6	3449.3
17.5°	3391.2	3441.4	3475.7	3512.7	3532.6	3551.1	3570.9	3563.0
20°	3475.7	3541.8	3590.7	3637.0	3664.7	3692.5	3709.7	3701.7
22.5°	3569.6	3658.1	3725.5	3789.0	3829.9	3860.3	3884.1	3881.5
25°	3685.9	3795.6	3881.5	3954.2	4011.0	4049.3	4078.4	4075.7
27.5°	3819.4	3948.9	4053.3	4141.8	4211.9	4262.1	4284.5	4287.2
30°	3963.4	4116.7	4240.9	4346.7	4427.3	4482.8	4506.6	4510.5
32.5°	4114.1	4292.5	4432.6	4551.5	4645.3	4710.1	4733.9	4747.1
35°	4263.4	4461.6	4628.2	4768.2	4870.0	4941.4	4966.5	4986.3
37.5°	4411.4	4638.7	4821.1	4973.1	5085.4	5166.0	5197.8	5203.0
40°	4555.5	4797.3	5007.5	5184.5	5311.4	5396.0	5435.6	5451.5
42.5°	4691.6	4962.5	5191.2	5389.4	5532.1	5619.3	5670.9	5686.7
45°	4821.1	5117.1	5360.3	5566.5	5714.5	5812.3	5870.4	5886.3
47.5°	4929.5	5242.7	5508.3	5735.6	5895.6	6005.2	6063.4	6087.2
50°	5020.7	5353.7	5636.5	5874.4	6037.0	6150.6	6215.4	6236.5
52.5°	5088.1	5423.7	5715.8	5968.2	6142.7	6272.2	6338.3	6368.7
55°	5119.8	5471.3	5772.6	6031.7	6204.8	6338.3	6408.3	6442.7
57.5°	5119.8	5472.6	5759.4	5998.6	6167.8	6309.2	6401.7	6436.1
60°	5057.7	5392.0	5700.0	5966.9	6150.6	6289.4	6388.5	6405.7
62.5°	4963.8	5306.1	5614.1	5682.8	5631.2	5574.4	5565.2	5585.0
65°	4833.0	4818.5	4784.1	4727.3	4781.5	4888.5	4938.7	4971.8
67.5°	4040.1	4073.1	4270.0	4424.6	4537.0	4629.5	4695.6	4729.9
70°	3640.9	3861.6	4053.3	4214.5	4304.4	4378.4	4415.4	4445.8
72.5°	3440.1	3617.2	3754.6	3874.9	3943.6	4011.0	4029.5	4049.3
75°	3155.9	3307.9	3461.2	3607.9	3717.6	3799.5	3843.1	3863.0
77.5°	2927.3	3095.1	3228.6	3363.4	3458.6	3526.0	3564.3	3597.3
80°	2647.1	2861.2	3059.4	3239.2	3370.0	3465.2	3529.9	3556.4
82.5°	2590.3	2808.3	3000.0	3149.3	3259.0	3343.6	3387.2	3407.0
85°	2226.9	2373.6	2518.9	2661.7	2776.6	2858.6	2898.2	2910.1
87.5°	1723.3	1875.3	2055.1	2174.0	2294.3	2388.1	2438.3	2447.6
90°	544.5	611.9	729.5	770.5	835.2	910.6	955.5	959.5
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	13.2	11.9	10.6	10.6	9.3	7.9	6.6	6.6
97.5°	121.6	91.2	72.7	58.1	46.3	41.0	39.6	39.6
100°	416.3	393.8	367.4	360.8	339.6	325.1	310.6	311.9
102.5°	633.0	586.8	598.7	625.1	639.6	644.9	638.3	642.3
105°	983.3	963.4	939.6	933.0	915.9	885.5	860.3	861.7
107.5°	1301.8	1320.3	1332.1	1334.8	1328.2	1318.9	1301.8	1304.4
110°	1554.2	1634.8	1692.9	1741.8	1756.4	1752.4	1759.0	1764.3



TEST NUMBER: P236534

CATALOG NUMBER: SKB4-LD5-36-W-UNV-L850-CD4-U all blades horizontal

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1552.9	1833.0	1946.7	2031.3	2082.8	2111.9	2131.7	2144.9
115°	1515.8	1611.0	1786.8	1987.7	2216.3	2337.9	2376.2	2396.0
117.5°	1876.6	1815.8	1815.8	1790.7	1862.1	1954.6	1998.2	2015.4
120°	2478.0	2267.8	2185.9	2146.2	2144.9	2156.8	2143.6	2143.6
122.5°	2940.5	2866.5	2771.3	2678.8	2582.4	2557.2	2532.1	2536.1
125°	3022.4	3202.2	3235.2	3219.4	3186.3	3144.0	3108.3	3108.3
127.5°	2978.8	3203.5	3355.5	3475.7	3563.0	3543.1	3533.9	3535.2
130°	2953.7	3130.8	3288.1	3445.3	3556.4	3622.4	3654.2	3666.1
132.5°	2920.7	3064.7	3211.4	3335.7	3421.6	3494.2	3532.6	3547.1
135°	2852.0	3011.9	3120.2	3223.3	3311.9	3380.6	3407.0	3425.5
137.5°	2760.8	2894.3	3021.1	3141.4	3218.0	3261.6	3273.5	3281.5
140°	2676.2	2788.5	2892.9	2985.4	3068.7	3141.4	3169.1	3179.7
142.5°	2512.3	2686.8	2771.3	2853.3	2920.7	2989.4	3026.4	3035.7
145°	2152.8	2426.4	2589.0	2711.9	2787.2	2849.3	2885.0	2914.1
147.5°	1856.8	2048.4	2208.4	2392.1	2524.2	2637.9	2696.0	2709.2
150°	1653.3	1768.3	1881.9	1989.0	2096.0	2193.8	2246.7	2255.9
152.5°	1496.0	1641.4	1679.7	1719.4	1789.4	1848.9	1858.1	1866.1
155°	1389.0	1420.7	1480.2	1578.0	1630.8	1617.6	1595.1	1575.3
157.5°	1385.0	1363.9	1373.1	1379.7	1361.2	1333.5	1293.8	1266.1
160°	1542.3	1436.6	1389.0	1352.0	1293.8	1235.7	1173.6	1167.0
162.5°	1626.9	1596.5	1571.4	1530.4	1423.3	1316.3	1278.0	1272.7
165°	1636.1	1636.1	1633.5	1617.6	1554.2	1489.4	1466.9	1465.6
167.5°	1601.8	1611.0	1616.3	1621.6	1601.8	1570.0	1538.3	1533.0
170°	1576.6	1571.4	1570.0	1566.1	1585.9	1581.9	1542.3	1504.0
172.5°	1584.6	1562.1	1547.6	1543.6	1579.3	1615.0	1589.9	1574.0
175°	1596.5	1559.5	1538.3	1548.9	1591.2	1661.2	1700.9	1714.1
177.5°	1585.9	1538.3	1514.5	1538.3	1589.9	1683.7	1789.4	1833.0
180°	1675.8	1675.8	1675.8	1675.8	1675.8	1675.8	1675.8	1675.8

(END OF REPORT)