

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P219338

Luminaire Tested: **SSLED-LD5-15-N-UNV-L850-CD1-SA23-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P219338
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27261)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SSLED-LD5-15-N-UNV-L850-CD1-SA23-U
Description: METALUX ROUND HIGH BAY STEELER LED WITH NARROW DISTRIBUTION LENS WITH Rev.G BOARD. LENS DIFFUSE 2407, 7.5% BLEND. SHROUD ACCESSORY INSTALLED. FIXTURE CENTERED TO LEDS
Light Source: (240) 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14979.9 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Circular (Dia: 1.41' x H: 0')
CIE Type: Direct


Input Watts (W): 110.74
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219338

CATALOG NUMBER: SSLED-LD5-15-N-UNV-L850-CD1-SA23-U

Luminous Intensity Polar Plot





TEST NUMBER: P219338

CATALOG NUMBER: SSLED-LD5-15-N-UNV-L850-CD1-SA23-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	82		88	84	81		85	82	80	78
4	95	87	81	77	94	86	81	76	84	79	76		82	78	75		80	77	74	72
5	90	81	75	70	89	80	74	70	78	73	69		77	72	69		75	71	68	67
6	85	76	69	65	84	75	69	65	74	68	64		72	67	64		71	67	63	62
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67	62	59	57
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59	55	52	50
10	69	59	53	49	68	59	53	49	58	52	49		57	52	49		56	52	48	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111100
5°	109362
10°	105006
15°	97483
20°	86376
25°	71673
30°	55972
35°	41622
40°	27732
45°	17951
50°	11585
55°	7882
60°	5472
65°	3499
70°	961
75°	626
80°	623
85°	878



TEST NUMBER: P219338

CATALOG NUMBER: SSLED-LD5-15-N-UNV-L850-CD1-SA23-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1483.2	9.9
10°-20°	3796.6	25.3
20°-30°	4295.5	28.7
30°-40°	3068.3	20.5
40°-50°	1474.6	9.8
50°-60°	610.3	4.1
60°-70°	212.5	1.4
70°-80°	27.5	0.2
80°-90°	11.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	9575.3	63.9
0°-40°	12643.7	84.4
0°-60°	14728.5	98.3
0°-90°	14979.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14979.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16117	
5°	15804	###
15°	13659	3797
25°	9423	4295
35°	4946	3068
45°	1841	1475
55°	656	610
65°	214	212
75°	24	27
85°	11	11
90°	0	



TEST NUMBER: P219338

CATALOG NUMBER: SSLED-LD5-15-N-UNV-L850-CD1-SA23-U

CANDELA DISTRIBUTION (FULL):

	0°
0°	16116.6
2.5°	16037.5
5°	15804.1
7.5°	15459.5
10°	15001.1
12.5°	14397.6
15°	13659.4
17.5°	12785.8
20°	11774.3
22.5°	10648.3
25°	9423.0
27.5°	8208.1
30°	7031.7
32.5°	5943.7
35°	4945.9
37.5°	3903.0
40°	3081.7
42.5°	2395.1
45°	1841.3
47.5°	1407.8
50°	1080.2
52.5°	838.9
55°	655.8
57.5°	513.3
60°	396.9
62.5°	300.1
65°	214.5
67.5°	128.2
70°	47.7
72.5°	30.1
75°	23.5
77.5°	19.0
80°	15.7
82.5°	13.7
85°	11.1
87.5°	9.2
90°	0.0

(END OF REPORT)