

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P219463

Luminaire Tested: **SSLED-LD5-15-W-UNV-L840-CD1-SA23-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P219463  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27263)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: SSLED-LD5-15-W-UNV-L840-CD1-SA23-U  
Description: METALUX ROUND HIGH BAY STEELER LED WITH WIDE DISTRIBUTION LENS WITH Rev.G BOARD. LENS DIFFUSE 2407, 7.5% BLEND. SHROUD ACCESSORY INSTALLED. FIXTURE CENTERED TO LEDS  
Light Source: (240) 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14503.5 lumens  
Efficiency: N/A  
Efficacy: 131.0 lumens/watt  
Spacing Criteria (0/90/45): 1.7 / 1.7 / 1.49  
Luminous Opening: Circular (Dia: 1.41' x H: 0')  
CIE Type: Direct


Input Watts (W): 110.74  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219463

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L840-CD1-SA23-U

### Luminous Intensity Polar Plot





TEST NUMBER: P219463

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L840-CD1-SA23-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85		90	86	83		87	84	82	80
3	97	88	82	77	94	87	81	76	84	79	75		81	77	73		79	75	72	70
4	90	80	72	67	88	78	72	67	76	70	66		74	69	65		72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58		67	62	58		66	61	57	55
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	52	47	70	59	52	46	58	51	46		56	50	46		55	50	46	44
8	67	55	47	42	65	54	47	42	53	46	41		52	46	41		50	45	41	39
9	62	50	43	38	61	50	42	38	49	42	37		48	42	37		47	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	36975
5°	37015
10°	37594
15°	39771
20°	44174
25°	49658
30°	54723
35°	58270
40°	55266
45°	45629
50°	29108
55°	15982
60°	8651
65°	4063
70°	1278
75°	996
80°	1032
85°	1099



TEST NUMBER: P219463

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L840-CD1-SA23-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	511.1	3.5
10°-20°	1602.5	11.0
20°-30°	3018.7	20.8
30°-40°	4230.4	29.2
40°-50°	3510.7	24.2
50°-60°	1293.0	8.9
60°-70°	280.5	1.9
70°-80°	41.7	0.3
80°-90°	14.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5132.4	35.4
0°-40°	9362.7	64.6
0°-60°	14166.4	97.7
0°-90°	14503.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14503.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5364	
5°	5349	511
15°	5573	1602
25°	6529	3019
35°	6924	4230
45°	4680	3511
55°	1330	1293
65°	249	280
75°	37	42
85°	14	15
90°	0	



TEST NUMBER: P219463

CATALOG NUMBER: SSLED-LD5-15-W-UNV-L840-CD1-SA23-U

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5363.7
2.5°	5361.8
5°	5349.1
7.5°	5345.9
10°	5370.6
12.5°	5437.2
15°	5572.8
17.5°	5772.5
20°	6021.6
22.5°	6282.7
25°	6528.7
27.5°	6726.4
30°	6874.8
32.5°	6951.5
35°	6924.2
37.5°	6607.9
40°	6141.4
42.5°	5533.5
45°	4680.4
47.5°	3683.9
50°	2714.2
52.5°	1911.1
55°	1329.8
57.5°	931.1
60°	627.5
62.5°	414.5
65°	249.1
67.5°	135.6
70°	63.4
72.5°	45.0
75°	37.4
77.5°	31.1
80°	26.0
82.5°	20.9
85°	13.9
87.5°	7.0
90°	0.0

(END OF REPORT)