

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P219465

Luminaire Tested: **SSLED-LD5-18-W-UNV-L835-CD1-SA23-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P219465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27263)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SSLED-LD5-18-W-UNV-L835-CD1-SA23-U
Description: METALUX ROUND HIGH BAY STEELER LED WITH WIDE DISTRIBUTION LENS WITH Rev.G BOARD. LENS DIFFUSE 2407, 7.5% BLEND. SHROUD ACCESSORY INSTALLED. FIXTURE CENTERED TO LEDS
Light Source: (240) 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15931.1 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.7 / 1.7 / 1.49
Luminous Opening: Circular (Dia: 1.41' x H: 0')
CIE Type: Direct


Input Watts (W): 133.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219465

CATALOG NUMBER: SSLED-LD5-18-W-UNV-L835-CD1-SA23-U

Luminous Intensity Polar Plot





TEST NUMBER: P219465

CATALOG NUMBER: SSLED-LD5-18-W-UNV-L835-CD1-SA23-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	80	72	67	88	78	72	67	76	70	66	74	69	65	72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	50	45	41	39
9	62	50	43	38	61	50	42	38	49	42	37	48	42	37	47	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40614
5°	40658
10°	41294
15°	43687
20°	48522
25°	54546
30°	60109
35°	64005
40°	60706
45°	50119
50°	31973
55°	17555
60°	9503
65°	4463
70°	1403
75°	1095
80°	1131
85°	1210



TEST NUMBER: P219465

CATALOG NUMBER: SSLED-LD5-18-W-UNV-L835-CD1-SA23-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	561.4	3.5
10°-20°	1760.2	11.0
20°-30°	3315.9	20.8
30°-40°	4646.7	29.2
40°-50°	3856.3	24.2
50°-60°	1420.2	8.9
60°-70°	308.1	1.9
70°-80°	45.8	0.3
80°-90°	16.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5637.5	35.4
0°-40°	10284.3	64.6
0°-60°	15560.8	97.7
0°-90°	15931.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15931.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5892	
5°	5876	561
15°	6121	1760
25°	7171	3316
35°	7606	4647
45°	5141	3856
55°	1461	1420
65°	274	308
75°	41	46
85°	15	16
90°	0	



TEST NUMBER: P219465

CATALOG NUMBER: SSLED-LD5-18-W-UNV-L835-CD1-SA23-U

CANDELA DISTRIBUTION (FULL):

	0°
0°	5891.6
2.5°	5889.5
5°	5875.6
7.5°	5872.1
10°	5899.3
12.5°	5972.4
15°	6121.4
17.5°	6340.7
20°	6614.3
22.5°	6901.1
25°	7171.3
27.5°	7388.5
30°	7551.4
32.5°	7635.7
35°	7605.7
37.5°	7258.3
40°	6745.9
42.5°	6078.2
45°	5141.0
47.5°	4046.6
50°	2981.3
52.5°	2099.2
55°	1460.7
57.5°	1022.8
60°	689.3
62.5°	455.3
65°	273.6
67.5°	149.0
70°	69.6
72.5°	49.4
75°	41.1
77.5°	34.1
80°	28.5
82.5°	23.0
85°	15.3
87.5°	7.7
90°	0.0

(END OF REPORT)