

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P520765

Luminaire Tested: **8WSLA-50-L940-UNV-U**

Issue Date: 5/3/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P520765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2002-689-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/3/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 8WSLA-50-L940-UNV-U
Description: 8 FOOT, 1000 LUMEN PER FOOT, WSLA LED LUMINAIRE WITH 4000K, 90 CRI
LEDS WITH NO UPLIGHT
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3408.0 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.17 / 1.33
Luminous Opening: Rectangular (W 0.5' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 30.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P520765

CATALOG NUMBER: 8WSLA-50-L940-UNV-U

Luminous Intensity Polar Plot





TEST NUMBER: P520765

CATALOG NUMBER: 8WSLA-50-L940-UNV-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84																			
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	73	70																			
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	60																			
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51																			
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	44																			
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	39																			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34																			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31																			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	28																			
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3419	3419	3419	3419
5°	3452	3404	3446	3426
10°	3464	3378	3455	3449
15°	3475	3199	3460	3448
20°	3488	3074	3474	3396
25°	3499	3023	3480	3311
30°	3503	2980	3477	3202
35°	3497	2922	3461	3083
40°	3486	2844	3431	2940
45°	3447	2210	3369	2697
50°	3395	1892	3313	2516
55°	3335	1772	3248	2420
60°	3272	1691	3173	2380
65°	3194	1601	3086	2352
70°	3067	1523	2939	2316
75°	2856	1339	2721	2204
80°	2535	1119	2376	1869
85°	2399	800	2106	1074



TEST NUMBER: P520765

CATALOG NUMBER: 8WSLA-50-L940-UNV-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.7	3.5
10°-20°	344.3	10.1
20°-30°	514.5	15.1
30°-40°	612.4	18.0
40°-50°	612.1	18.0
50°-60°	526.7	15.5
60°-70°	396.4	11.6
70°-80°	225.9	6.6
80°-90°	55.0	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	979.5	28.7
0°-40°	1591.8	46.7
0°-60°	2730.7	80.1
0°-90°	3408.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3408.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1270	1270	1270	1270	1270	
5°	1278	1260	1276	1268	1278	122
15°	1247	1148	1242	1238	1247	352
25°	1178	1018	1172	1115	1178	543
35°	1065	889	1054	938	1065	666
45°	906	581	885	709	906	698
55°	711	378	692	516	711	636
65°	502	252	485	369	502	495
75°	275	129	262	212	275	291
85°	78	26	68	35	78	85
90°	0	0	0	0	0	



TEST NUMBER: P520765

CATALOG NUMBER: 8WSLA-50-L940-UNV-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	1270.4	1270.4	1270.4	1270.4	1270.4	1270.4	1270.4	1270.4	1270.4	1270.4	1270.4
2.5°	1279.9	1268.3	1275.2	1273.1	1262.2	1266.3	1270.4	1266.3	1278.6	1267.7	1275.2
5°	1277.9	1265.6	1269.7	1265.6	1260.2	1261.5	1267.7	1263.6	1275.8	1264.3	1273.8
7.5°	1273.8	1258.8	1262.9	1260.8	1256.1	1256.8	1262.9	1259.5	1270.4	1259.5	1270.4
10°	1267.7	1252.0	1255.4	1246.5	1236.3	1243.8	1256.1	1252.7	1264.3	1252.0	1264.3
12.5°	1258.1	1242.4	1239.0	1209.7	1191.3	1205.6	1243.1	1243.1	1254.0	1242.4	1255.4
15°	1247.2	1230.2	1211.8	1167.5	1148.4	1162.7	1214.5	1232.2	1241.8	1230.2	1243.1
17.5°	1234.3	1214.5	1179.1	1127.3	1109.5	1123.9	1177.0	1215.9	1228.1	1215.9	1227.5
20°	1217.9	1194.7	1144.3	1085.0	1073.4	1086.4	1139.5	1196.1	1213.1	1198.1	1206.3
22.5°	1200.2	1172.2	1105.5	1052.3	1046.8	1055.0	1103.4	1171.6	1194.1	1178.4	1183.8
25°	1178.4	1145.7	1066.6	1022.3	1018.2	1023.0	1068.0	1142.9	1172.2	1155.9	1157.9
27.5°	1155.2	1119.8	1029.8	997.1	993.0	995.0	1032.5	1110.9	1147.0	1130.7	1127.3
30°	1127.3	1089.1	993.0	963.0	958.9	966.4	998.5	1078.2	1119.1	1102.7	1092.5
32.5°	1099.3	1055.7	956.9	933.7	925.5	932.3	963.0	1044.1	1088.4	1071.4	1054.3
35°	1064.6	1020.3	919.4	896.2	889.4	896.9	927.6	1008.7	1053.7	1036.6	1013.4
37.5°	1028.4	982.8	885.3	864.2	851.9	860.8	891.5	971.9	1017.5	999.8	971.2
40°	992.3	943.3	847.2	825.3	809.7	822.6	854.0	933.0	976.6	960.3	927.6
42.5°	950.1	903.7	809.7	779.0	734.7	776.3	813.8	894.2	934.4	918.7	879.2
45°	905.8	861.5	770.1	695.9	580.7	702.7	772.9	853.3	885.3	870.3	827.4
47.5°	855.3	817.8	729.9	616.8	505.0	623.6	731.3	814.4	839.0	822.6	774.9
50°	811.0	774.2	687.7	550.0	451.9	557.5	687.0	770.8	791.3	776.3	723.1
52.5°	760.6	728.6	642.0	490.7	412.3	498.2	640.6	725.8	742.2	724.5	671.3
55°	710.8	682.2	593.6	438.2	377.6	445.0	592.3	679.5	692.4	672.0	616.8
57.5°	660.4	634.5	543.9	391.2	345.5	398.7	547.3	631.8	640.6	614.7	564.3
60°	607.9	586.1	493.4	349.6	314.2	355.8	492.1	584.1	589.5	561.6	513.2
62.5°	555.5	535.7	443.0	311.5	282.2	315.6	446.4	533.6	537.1	510.5	460.7
65°	501.6	483.2	393.9	271.3	251.5	278.1	397.3	481.2	484.6	454.6	409.6
67.5°	445.7	430.7	341.5	240.6	222.2	242.6	348.3	428.0	430.1	400.7	359.9
70°	389.8	376.9	295.1	207.2	193.6	207.9	299.9	369.4	373.5	342.1	309.4
72.5°	332.6	322.4	250.1	172.4	160.2	172.4	252.9	315.6	318.3	292.4	260.3
75°	274.7	267.2	204.5	138.4	128.8	137.7	205.8	261.7	261.7	237.2	212.0
77.5°	218.8	213.3	156.8	106.3	99.5	105.0	157.4	207.2	205.8	186.7	167.0
80°	163.6	159.5	112.5	77.0	72.2	75.0	112.5	153.3	153.3	139.7	115.9
82.5°	117.2	112.5	74.3	50.4	47.7	49.1	72.9	107.0	109.0	98.8	78.4
85°	77.7	66.8	40.2	27.9	25.9	26.6	38.2	62.0	68.2	57.2	40.9
87.5°	34.1	22.5	10.2	4.1	2.0	2.7	8.2	19.8	25.9	17.0	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P520765

CATALOG NUMBER: 8WSLA-50-L940-UNV-U

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	1270.4	1270.4	1270.4	1270.4	1270.4	1270.4
2.5°	1274.5	1263.6	1267.7	1270.4	1267.7	1279.9
5°	1273.1	1268.3	1267.7	1271.1	1265.6	1277.9
7.5°	1271.1	1268.3	1267.7	1269.0	1262.2	1273.8
10°	1266.3	1262.2	1263.6	1265.6	1256.8	1267.7
12.5°	1257.4	1253.4	1254.0	1260.8	1248.6	1258.1
15°	1242.4	1237.7	1242.4	1249.9	1239.0	1247.2
17.5°	1222.7	1215.2	1223.4	1234.9	1226.8	1234.3
20°	1197.5	1185.9	1194.7	1215.9	1208.4	1217.9
22.5°	1166.8	1152.5	1161.3	1192.0	1190.0	1200.2
25°	1132.0	1115.0	1127.3	1164.8	1168.8	1178.4
27.5°	1093.2	1074.1	1090.5	1134.8	1144.3	1155.2
30°	1050.9	1030.5	1049.6	1101.4	1115.7	1127.3
32.5°	1007.3	984.8	1006.6	1063.9	1084.3	1099.3
35°	961.7	938.5	963.0	1025.0	1049.6	1064.6
37.5°	912.6	890.1	916.7	984.1	1013.4	1028.4
40°	862.1	836.9	866.9	935.8	974.6	992.3
42.5°	810.4	779.0	815.8	890.1	932.3	950.1
45°	752.4	708.8	758.6	841.7	886.0	905.8
47.5°	694.5	650.9	701.3	789.9	837.6	855.3
50°	638.6	601.1	641.3	733.3	788.5	811.0
52.5°	587.5	556.8	590.9	678.1	738.1	760.6
55°	539.8	515.9	543.9	623.6	684.9	710.8
57.5°	494.8	479.8	498.9	571.8	635.9	660.4
60°	452.5	442.3	455.9	520.7	577.9	607.9
62.5°	411.0	405.5	415.7	466.9	524.1	555.5
65°	370.8	369.4	374.8	419.8	467.5	501.6
67.5°	330.5	329.9	333.3	370.1	412.3	445.7
70°	290.3	294.4	292.4	316.2	357.1	389.8
72.5°	249.4	255.6	252.2	267.2	306.7	332.6
75°	203.8	212.0	205.1	222.2	246.7	274.7
77.5°	156.8	165.6	157.4	172.4	199.0	218.8
80°	112.5	120.6	113.8	125.4	148.6	163.6
82.5°	70.9	77.0	71.6	83.1	106.3	117.2
85°	31.4	34.8	36.1	45.0	65.4	77.7
87.5°	1.4	0.7	1.4	8.9	23.2	34.1
90°	0.0	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270° - · - · 135°-315°









(END OF REPORT)