

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P229411

Luminaire Tested: **22ALNG-LD5-31-UNV-L835-CD1-SVPD1-U**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P229411  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P36087)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 22ALNG-LD5-31-UNV-L835-CD1-SVPD1-U  
Description: METALUX 2X2 ARCLINE LED TROFFER WITH CURVED LENS AND SENSOR  
Light Source: (126)3500K CCT, 80 CRI LEDs  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3011.0 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.23 / 1.31  
Luminous Opening: Rectangular (W 1.83' x L: 1.83' x H: 0')  
CIE Type: Direct


Input Watts (W): 25.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P229411

CATALOG NUMBER: 22ALNG-LD5-31-UNV-L835-CD1-SVPD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P229411

CATALOG NUMBER: 22ALNG-LD5-31-UNV-L835-CD1-SVPD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	73	70
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	60
4	83	71	63	56	81	70	62	56	67	60	55	65	59	54	63	58	53	51
5	76	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	46	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	44	37	64	51	43	37	50	42	37	48	42	37	47	41	37	35
8	61	48	39	34	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3708	3708	3708
5°	3693	3703	3713
10°	3662	3677	3687
15°	3609	3628	3654
20°	3534	3570	3616
25°	3455	3504	3573
30°	3353	3426	3532
35°	3237	3338	3462
40°	3101	3240	3379
45°	2989	3140	3304
50°	2851	3032	3205
55°	2705	2916	3119
60°	2569	2793	3006
65°	2374	2684	2936
70°	2183	2566	2849
75°	1910	2435	2735
80°	1592	2206	2346
85°	1224	1558	1448



TEST NUMBER: P229411

CATALOG NUMBER: 22ALNG-LD5-31-UNV-L835-CD1-SVPD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	109.3	3.6
10°-20°	308.6	10.3
20°-30°	457.3	15.2
30°-40°	534.7	17.8
40°-50°	534.4	17.7
50°-60°	465.8	15.5
60°-70°	348.3	11.6
70°-80°	202.7	6.7
80°-90°	49.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	875.2	29.1
0°-40°	1410.0	46.8
0°-60°	2410.2	80.0
0°-90°	3011.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3011.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1158	1158	1158	1158	1158	
5°	1149	1150	1152	1155	1155	109
15°	1088	1090	1094	1099	1102	307
25°	978	981	992	1005	1011	450
35°	828	834	854	878	886	517
45°	660	668	693	719	730	508
55°	484	494	522	546	559	434
65°	313	326	354	377	388	312
75°	154	171	197	212	221	165
85°	33	39	42	41	39	40
90°	0	0	0	0	0	



TEST NUMBER: P229411

CATALOG NUMBER: 22ALNG-LD5-31-UNV-L835-CD1-SVPD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1158.0	1158.0	1158.0	1158.0	1158.0
2.5°	1155.0	1155.0	1158.0	1159.5	1161.0
5°	1148.9	1150.4	1152.0	1155.0	1155.0
7.5°	1139.8	1141.4	1142.9	1145.9	1145.9
10°	1126.2	1127.7	1130.8	1133.8	1133.8
12.5°	1109.6	1111.1	1114.1	1117.1	1120.2
15°	1088.4	1089.9	1094.4	1099.0	1102.0
17.5°	1064.2	1067.2	1073.2	1079.3	1082.3
20°	1036.9	1039.9	1047.5	1058.1	1061.1
22.5°	1009.7	1011.2	1020.3	1032.4	1036.9
25°	977.9	980.9	991.5	1005.1	1011.2
27.5°	941.5	946.1	961.2	977.9	987.0
30°	906.7	909.8	926.4	947.6	955.2
32.5°	867.4	873.4	891.6	912.8	920.4
35°	828.0	834.1	853.7	878.0	885.5
37.5°	785.6	791.7	815.9	840.1	849.2
40°	741.7	750.8	775.0	800.8	808.3
42.5°	700.9	708.4	732.6	758.4	770.5
45°	660.0	667.6	693.3	719.0	729.6
47.5°	614.6	622.1	650.9	676.6	687.2
50°	572.2	579.8	608.5	634.3	643.3
52.5°	528.3	537.4	563.1	590.4	599.4
55°	484.4	493.5	522.2	546.5	558.6
57.5°	442.0	452.6	476.8	502.6	514.7
60°	401.1	408.7	436.0	460.2	469.3
62.5°	357.2	366.3	393.6	419.3	428.4
65°	313.3	325.5	354.2	376.9	387.5
67.5°	272.5	284.6	313.3	334.5	346.6
70°	233.1	245.2	274.0	293.7	304.3
72.5°	193.8	208.9	234.6	252.8	261.9
75°	154.4	171.1	196.8	211.9	221.0
77.5°	119.6	136.2	158.9	172.6	175.6
80°	86.3	102.9	119.6	125.6	127.2
82.5°	59.0	71.1	80.2	80.2	83.3
85°	33.3	39.4	42.4	40.9	39.4
87.5°	12.1	13.6	12.1	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)