

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P520747

Luminaire Tested: **8WSLA-50-L830-UNV-U**

Issue Date: 5/3/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P520747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2002-689-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/3/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 8WSLA-50-L830-UNV-U
Description: 8 FOOT, 1000 LUMEN PER FOOT, WSLA LED LUMINAIRE WITH 3000K, 80 CRI
LEDS WITH NO UPLIGHT
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3938.0 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.17 / 1.33
Luminous Opening: Rectangular (W 0.5' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 30.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P520747

CATALOG NUMBER: 8WSLA-50-L830-UNV-U

Luminous Intensity Polar Plot





TEST NUMBER: P520747

CATALOG NUMBER: 8WSLA-50-L830-UNV-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84			
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	73	70			
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	60			
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51			
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	44			
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	39			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	28			
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3950	3950	3950	3950
5°	3989	3933	3982	3959
10°	4003	3904	3992	3985
15°	4015	3697	3997	3984
20°	4030	3552	4014	3924
25°	4043	3494	4022	3825
30°	4048	3443	4018	3700
35°	4041	3376	4000	3562
40°	4028	3287	3964	3397
45°	3983	2554	3893	3117
50°	3924	2186	3828	2908
55°	3854	2047	3754	2797
60°	3781	1954	3666	2751
65°	3691	1850	3565	2718
70°	3544	1760	3396	2677
75°	3300	1547	3144	2546
80°	2929	1294	2746	2160
85°	2773	923	2433	1241



TEST NUMBER: P520747

CATALOG NUMBER: 8WSLA-50-L830-UNV-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.5	3.5
10°-20°	397.8	10.1
20°-30°	594.5	15.1
30°-40°	707.6	18.0
40°-50°	707.3	18.0
50°-60°	608.6	15.5
60°-70°	458.1	11.6
70°-80°	261.0	6.6
80°-90°	63.5	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1131.8	28.7
0°-40°	1839.4	46.7
0°-60°	3155.3	80.1
0°-90°	3938.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3938.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1468	1468	1468	1468	1468	
5°	1477	1456	1474	1466	1477	141
15°	1441	1327	1435	1430	1441	407
25°	1362	1177	1355	1288	1362	628
35°	1230	1028	1218	1084	1230	770
45°	1047	671	1023	819	1047	806
55°	821	436	800	596	821	734
65°	580	291	560	427	580	572
75°	317	149	302	245	317	336
85°	90	30	79	40	90	98
90°	0	0	0	0	0	



TEST NUMBER: P520747

CATALOG NUMBER: 8WSLA-50-L830-UNV-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0
2.5°	1479.0	1465.6	1473.5	1471.1	1458.5	1463.2	1468.0	1463.2	1477.4	1464.8	1473.5
5°	1476.6	1462.4	1467.2	1462.4	1456.1	1457.7	1464.8	1460.1	1474.3	1460.9	1471.9
7.5°	1471.9	1454.6	1459.3	1456.9	1451.4	1452.2	1459.3	1455.4	1468.0	1455.4	1468.0
10°	1464.8	1446.7	1450.6	1440.4	1428.6	1437.2	1451.4	1447.5	1460.9	1446.7	1460.9
12.5°	1453.8	1435.7	1431.7	1397.9	1376.6	1393.1	1436.5	1436.5	1449.1	1435.7	1450.6
15°	1441.2	1421.5	1400.2	1349.0	1327.0	1343.5	1403.4	1423.9	1434.9	1421.5	1436.5
17.5°	1426.2	1403.4	1362.4	1302.6	1282.1	1298.6	1360.1	1405.0	1419.1	1405.0	1418.3
20°	1407.3	1380.5	1322.3	1253.7	1240.4	1255.3	1316.8	1382.1	1401.8	1384.5	1393.9
22.5°	1386.8	1354.6	1277.4	1215.9	1209.6	1219.1	1275.0	1353.8	1379.8	1361.6	1367.9
25°	1361.6	1323.8	1232.5	1181.3	1176.6	1182.1	1234.1	1320.7	1354.6	1335.7	1338.0
27.5°	1334.9	1293.9	1190.0	1152.2	1147.4	1149.8	1193.1	1283.7	1325.4	1306.5	1302.6
30°	1302.6	1258.5	1147.4	1112.8	1108.1	1116.7	1153.7	1245.9	1293.1	1274.2	1262.4
32.5°	1270.3	1219.9	1105.7	1078.9	1069.5	1077.3	1112.8	1206.5	1257.7	1238.0	1218.3
35°	1230.1	1178.9	1062.4	1035.6	1027.7	1036.4	1071.8	1165.5	1217.5	1197.8	1171.1
37.5°	1188.4	1135.6	1023.0	998.6	984.4	994.7	1030.1	1123.0	1175.8	1155.3	1122.2
40°	1146.6	1089.9	978.9	953.7	935.6	950.5	986.8	1078.1	1128.5	1109.6	1071.8
42.5°	1097.8	1044.3	935.6	900.1	849.0	897.0	940.3	1033.2	1079.7	1061.6	1015.9
45°	1046.6	995.4	889.9	804.1	671.0	811.9	893.1	986.0	1023.0	1005.7	956.1
47.5°	988.4	945.0	843.4	712.7	583.6	720.6	845.0	941.1	969.4	950.5	895.4
50°	937.2	894.6	794.6	635.5	522.1	644.2	793.8	890.7	914.3	897.0	835.6
52.5°	878.9	841.9	741.9	567.0	476.5	575.7	740.3	838.7	857.6	837.1	775.7
55°	821.4	788.3	685.9	506.4	436.3	514.3	684.4	785.2	800.1	776.5	712.7
57.5°	763.1	733.2	628.4	452.0	399.3	460.7	632.4	730.0	740.3	710.4	652.1
60°	702.5	677.3	570.2	404.0	363.1	411.1	568.6	674.9	681.2	648.9	593.0
62.5°	641.8	619.0	511.9	359.9	326.0	364.6	515.8	616.6	620.6	589.9	532.4
65°	579.6	558.4	455.2	313.4	290.6	321.3	459.1	556.0	559.9	525.3	473.3
67.5°	515.0	497.7	394.6	278.0	256.7	280.4	402.4	494.6	496.9	463.1	415.8
70°	450.5	435.5	341.0	239.4	223.7	240.2	346.5	426.8	431.6	395.3	357.5
72.5°	384.3	372.5	289.0	199.2	185.1	199.2	292.2	364.6	367.8	337.9	300.8
75°	317.4	308.7	236.3	159.9	148.8	159.1	237.8	302.4	302.4	274.1	244.9
77.5°	252.8	246.5	181.1	122.9	115.0	121.3	181.9	239.4	237.8	215.8	192.9
80°	189.0	184.3	129.9	89.0	83.5	86.6	129.9	177.2	177.2	161.4	133.9
82.5°	135.5	129.9	85.8	58.3	55.1	56.7	84.3	123.6	126.0	114.2	90.6
85°	89.8	77.2	46.5	32.3	29.9	30.7	44.1	71.7	78.8	66.2	47.3
87.5°	39.4	26.0	11.8	4.7	2.4	3.2	9.5	22.8	29.9	19.7	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P520747

CATALOG NUMBER: 8WSLA-50-L830-UNV-U

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0
2.5°	1472.7	1460.1	1464.8	1468.0	1464.8	1479.0
5°	1471.1	1465.6	1464.8	1468.7	1462.4	1476.6
7.5°	1468.7	1465.6	1464.8	1466.4	1458.5	1471.9
10°	1463.2	1458.5	1460.1	1462.4	1452.2	1464.8
12.5°	1453.0	1448.3	1449.1	1456.9	1442.8	1453.8
15°	1435.7	1430.2	1435.7	1444.3	1431.7	1441.2
17.5°	1412.8	1404.2	1413.6	1427.0	1417.6	1426.2
20°	1383.7	1370.3	1380.5	1405.0	1396.3	1407.3
22.5°	1348.3	1331.7	1342.0	1377.4	1375.0	1386.8
25°	1308.1	1288.4	1302.6	1345.9	1350.6	1361.6
27.5°	1263.2	1241.1	1260.0	1311.2	1322.3	1334.9
30°	1214.4	1190.7	1212.8	1272.6	1289.2	1302.6
32.5°	1164.0	1138.0	1163.2	1229.3	1253.0	1270.3
35°	1111.2	1084.4	1112.8	1184.4	1212.8	1230.1
37.5°	1054.5	1028.5	1059.2	1137.2	1171.1	1188.4
40°	996.2	967.1	1001.7	1081.3	1126.2	1146.6
42.5°	936.4	900.1	942.7	1028.5	1077.3	1097.8
45°	869.4	819.0	876.5	972.6	1023.8	1046.6
47.5°	802.5	752.1	810.4	912.7	967.9	988.4
50°	737.9	694.6	741.1	847.4	911.2	937.2
52.5°	678.9	643.4	682.8	783.6	852.9	878.9
55°	623.7	596.2	628.4	720.6	791.5	821.4
57.5°	571.7	554.4	576.5	660.7	734.8	763.1
60°	522.9	511.1	526.9	601.7	667.8	702.5
62.5°	474.9	468.6	480.4	539.5	605.6	641.8
65°	428.4	426.8	433.1	485.1	540.2	579.6
67.5°	382.0	381.2	385.1	427.6	476.5	515.0
70°	335.5	340.2	337.9	365.4	412.7	450.5
72.5°	288.2	295.3	291.4	308.7	354.4	384.3
75°	235.5	244.9	237.0	256.7	285.1	317.4
77.5°	181.1	191.4	181.9	199.2	230.0	252.8
80°	129.9	139.4	131.5	144.9	171.7	189.0
82.5°	81.9	89.0	82.7	96.1	122.9	135.5
85°	36.2	40.2	41.7	52.0	75.6	89.8
87.5°	1.6	0.8	1.6	10.2	26.8	39.4
90°	0.0	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270° - · - · 135°-315°









(END OF REPORT)