

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P732062

Luminaire Tested: **22CZ2-44HE-B2750-W2D-3000K**

Issue Date: 1/5/2024



Test Information

Test Method: LM-79-08
Report Number: P732062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P271965)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 1/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 22CZ2-44HE-B2750-W2D-3000K
Description: 2X2 4400 LUMEN CRUZE TROFFER WITH BIO UP LEDS AT 3000K CCT AND RIBBED LENS

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4041.0 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.27 / 1.36
Luminous Opening: Rectangular (W 1.92' x L: 1.98' x H: 0')
CIE Type: Direct

Input Watts (W): 36
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P732062

CATALOG NUMBER: 22CZ2-44HE-B2750-W2D-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P732062

CATALOG NUMBER: 22CZ2-44HE-B2750-W2D-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82								
2	98	89	82	76	95	87	81	75	84	78	73	80	76	71	77	73	70	68								
3	89	78	69	63	86	76	68	62	73	66	61	70	65	60	68	63	59	56								
4	81	69	60	53	79	67	59	52	65	57	52	63	56	51	60	55	50	48								
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43	41								
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	36								
7	64	50	41	35	62	49	41	35	48	40	34	46	39	34	45	39	34	32								
8	59	46	37	31	58	45	37	31	44	36	31	42	35	30	41	35	30	28								
9	56	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27	25								
10	52	39	31	25	51	38	30	25	37	30	25	36	30	25	35	29	25	23								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3899	3899	3899
5°	3874	3902	3914
10°	3850	3890	3907
15°	3802	3861	3896
20°	3747	3819	3872
25°	3679	3798	3860
30°	3603	3727	3838
35°	3519	3678	3830
40°	3432	3616	3837
45°	3336	3575	3862
50°	3239	3537	3906
55°	3129	3522	3974
60°	3035	3521	4096
65°	2883	3578	4246
70°	2690	3646	4521
75°	2465	3773	4884
80°	2146	3932	4809
85°	1879	3493	3822



TEST NUMBER: P732062

CATALOG NUMBER: 22CZ2-44HE-B2750-W2D-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.9	3.2
10°-20°	370.1	9.2
20°-30°	555.6	13.7
30°-40°	663.9	16.4
40°-50°	690.4	17.1
50°-60°	639.9	15.8
60°-70°	524.8	13.0
70°-80°	354.8	8.8
80°-90°	111.5	2.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1055.7	26.1
0°-40°	1719.6	42.6
0°-60°	3049.8	75.5
0°-90°	4041.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4041.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1374	1374	1374	1374	1374	
5°	1360	1362	1370	1372	1374	129
15°	1294	1300	1314	1322	1326	365
25°	1175	1185	1213	1227	1233	541
35°	1016	1030	1062	1094	1106	635
45°	831	847	891	942	962	642
55°	632	652	712	775	803	568
65°	429	453	533	602	632	425
75°	225	262	344	414	446	238
85°	58	80	107	119	117	65
90°	0	0	0	0	0	



TEST NUMBER: P732062

CATALOG NUMBER: 22CZ2-44HE-B2750-W2D-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1374.0	1374.0	1374.0	1374.0	1374.0
2.5°	1366.1	1369.9	1375.9	1378.1	1378.1
5°	1360.1	1362.0	1369.9	1372.1	1374.0
7.5°	1350.0	1354.1	1362.0	1364.2	1366.1
10°	1336.1	1340.2	1350.0	1354.1	1356.0
12.5°	1318.4	1322.2	1334.2	1340.2	1342.1
15°	1294.4	1300.4	1314.3	1322.2	1326.3
17.5°	1270.7	1276.5	1290.6	1302.3	1306.4
20°	1240.8	1254.6	1264.7	1280.5	1282.4
22.5°	1211.0	1218.9	1236.7	1252.7	1260.6
25°	1175.1	1185.2	1213.0	1226.9	1232.8
27.5°	1137.5	1151.4	1173.2	1195.0	1202.9
30°	1099.6	1109.4	1137.5	1163.1	1171.3
32.5°	1057.9	1071.8	1101.5	1127.4	1139.4
35°	1016.0	1029.9	1061.8	1093.6	1105.6
37.5°	970.5	986.3	1018.1	1055.8	1071.8
40°	926.6	938.6	976.2	1022.0	1035.9
42.5°	880.8	894.7	934.5	984.4	1000.2
45°	831.2	847.1	890.9	942.4	962.3
47.5°	783.3	799.4	847.1	898.8	922.5
50°	733.7	753.6	801.3	861.0	884.9
52.5°	686.0	704.0	757.7	819.3	841.1
55°	632.4	652.2	711.9	775.4	803.2
57.5°	588.5	602.4	668.1	733.7	761.5
60°	534.8	552.8	620.4	689.9	721.7
62.5°	477.3	507.0	576.5	648.2	680.0
65°	429.4	453.4	532.9	602.4	632.4
67.5°	379.8	405.7	483.1	556.9	590.7
70°	324.2	358.0	439.5	513.0	544.9
72.5°	274.4	310.3	393.7	465.3	499.1
75°	224.8	262.4	344.1	413.6	445.5
77.5°	177.1	218.8	298.3	352.0	371.9
80°	131.3	171.1	240.6	278.4	294.3
82.5°	91.5	125.3	177.1	197.0	200.8
85°	57.7	79.6	107.3	119.3	117.4
87.5°	25.9	31.9	39.8	43.9	41.7
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)