

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P798377

Luminaire Tested: 22CZSB-SCT3-S-UNV-LOW-3000K

Issue Date: 3/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P798377
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25712)
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: 22CZSB-SCT3-S-UNV-LOW-3000K
Description: Cruze SB Selectable Troffer
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2746.8 lumens
Efficiency: N/A
Efficacy: 137.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.24 / 1.33
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P798377
CATALOG NUMBER: 22CZSB-SCT3-S-UNV-LOW-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P798377

CATALOG NUMBER: 22CZSB-SCT3-S-UNV-LOW-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	109	104	99	95	106	101	97	94	97	94	91	93	91	88	90	87	85	85	85	85	83
2	99	90	83	77	96	88	82	77	85	79	75	81	77	73	78	75	71	71	71	71	69
3	90	79	71	64	87	78	70	64	75	68	63	72	66	62	69	64	60	60	60	60	58
4	82	70	61	54	80	69	61	54	66	59	53	64	58	53	62	56	52	52	52	52	50
5	76	63	54	47	74	62	53	47	59	52	46	57	51	46	56	50	45	45	45	45	43
6	70	56	47	41	68	56	47	41	54	46	40	52	45	40	50	44	40	40	40	40	38
7	65	51	42	36	63	50	42	36	49	41	36	47	41	36	46	40	35	35	35	35	33
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	32	32	32	32	30
9	56	43	35	29	55	42	34	29	41	34	29	40	34	29	39	33	29	29	29	29	27
10	53	40	32	26	52	39	32	26	38	31	26	37	31	26	36	30	26	26	26	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2695	2695	2695
5°	2691	2691	2684
10°	2675	2679	2679
15°	2635	2653	2676
20°	2588	2615	2653
25°	2523	2566	2628
30°	2452	2513	2603
35°	2371	2458	2579
40°	2290	2401	2558
45°	2199	2345	2561
50°	2099	2298	2558
55°	1999	2259	2556
60°	1882	2223	2577
65°	1765	2193	2613
70°	1629	2169	2678
75°	1469	2153	2483
80°	1288	2002	2165
85°	1059	1507	1343

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 70°
 Luminance: 2678 cd/sqm



TEST NUMBER: P798377
 CATALOG NUMBER: 22CZSB-SCT3-S-UNV-LOW-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	3.4
10°-20°	268.6	9.8
20°-30°	399.0	14.5
30°-40°	469.6	17.1
40°-50°	478.8	17.4
50°-60°	431.8	15.7
60°-70°	340.1	12.4
70°-80°	209.8	7.6
80°-90°	54.5	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.2	27.7
0°-40°	1231.8	44.8
0°-60°	2142.4	78.0
0°-90°	2746.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2746.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	996	997	996	995	994	95
15°	946	950	952	958	960	267
25°	850	855	864	879	885	392
35°	722	730	748	772	785	451
45°	578	587	616	653	673	445
55°	426	441	482	525	545	380
65°	277	297	344	388	410	274
75°	141	165	207	231	239	151
85°	34	44	49	46	44	40
90°	0	0	0	0	0	



TEST NUMBER: P798377

CATALOG NUMBER: 22CZSB-SCT3-S-UNV-LOW-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1001.4	1001.4	1001.4	1001.4	1001.4
2.5°	1002.6	1002.6	1000.0	997.4	993.5
5°	996.2	997.4	996.2	994.7	993.5
7.5°	988.2	989.5	989.5	989.5	989.5
10°	978.9	980.3	980.3	980.3	980.3
12.5°	965.8	967.1	968.4	969.7	972.3
15°	946.0	949.8	952.4	957.8	960.4
17.5°	926.3	930.1	934.2	940.7	946.0
20°	903.8	906.4	913.1	920.9	926.3
22.5°	878.7	882.6	889.2	899.8	907.7
25°	849.7	854.9	864.1	878.7	885.2
27.5°	822.0	825.9	837.7	853.6	862.9
30°	789.0	794.2	808.9	828.5	837.7
32.5°	756.1	762.5	778.4	800.9	811.5
35°	721.6	729.6	748.1	771.8	785.0
37.5°	687.4	695.3	716.4	742.8	757.3
40°	651.8	659.7	683.5	712.5	728.2
42.5°	614.8	624.0	650.3	683.5	701.9
45°	577.8	587.1	616.2	653.1	673.0
47.5°	539.7	550.2	581.9	622.8	642.5
50°	501.4	513.2	548.8	591.1	611.0
52.5°	463.0	476.3	514.6	558.2	579.3
55°	426.1	440.6	481.5	525.0	544.9
57.5°	386.6	403.7	447.2	489.5	511.9
60°	349.7	368.1	413.1	455.2	478.9
62.5°	312.7	332.4	379.9	422.3	444.6
65°	277.2	296.8	344.4	387.8	410.3
67.5°	241.4	263.9	310.1	353.6	376.0
70°	207.1	230.8	275.7	318.0	340.4
72.5°	174.2	197.9	242.7	282.4	295.5
75°	141.3	165.0	207.1	230.8	238.8
77.5°	110.8	133.3	170.2	184.7	195.3
80°	83.1	102.9	129.2	138.5	139.7
82.5°	56.6	73.9	89.8	91.1	89.8
85°	34.3	43.5	48.8	46.1	43.5
87.5°	15.9	17.1	15.9	10.6	6.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)