

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P842985

Luminaire Tested: **24CZ2-30-RDP-UNV-B50**

Issue Date: 1/5/2024



Test Information

Test Method: LM-79-08
Report Number: P842985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P274775)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 1/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-30-RDP-UNV-B50
Description: 2X4 3000 LUMEN CRUZE TROFFER WITH BIO UP LEDS AT 5000K CCT AND RDP LENS

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1784.0 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 1.92' x L: 3.98' x H: 0')
CIE Type: Direct

Input Watts (W): 23
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P842985

CATALOG NUMBER: 24CZ2-30-RDP-UNV-B50

Luminous Intensity Polar Plot





TEST NUMBER: P842985

CATALOG NUMBER: 24CZ2-30-RDP-UNV-B50

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82	82	82	82	82	82		
	2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67	67	67	67	67	67		
	3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56	56	56	56	56	56		
	4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47	47	47	47	47	47		
	5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40	40	40	40	40	40		
	6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35	35	35	35	35	35		
	7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31	31	31	31	31	31		
	8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27	27	27	27	27	27		
	9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24	24	24	24	24	24		
	10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22	22	22	22	22	22		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	792	792	792
5°	795	790	794
10°	793	790	794
15°	791	790	795
20°	785	789	797
25°	783	791	799
30°	776	789	802
35°	768	787	805
40°	760	786	815
45°	747	786	834
50°	730	791	859
55°	712	803	897
60°	682	819	947
65°	638	848	1005
70°	581	887	1081
75°	492	936	1129
80°	388	942	914
85°	287	717	802



TEST NUMBER: P842985

CATALOG NUMBER: 24CZ2-30-RDP-UNV-B50

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	3.0
10°-20°	153.2	8.6
20°-30°	234.2	13.1
30°-40°	286.3	16.0
40°-50°	305.2	17.1
50°-60°	291.8	16.4
60°-70°	247.2	13.9
70°-80°	166.1	9.3
80°-90°	46.9	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	440.6	24.7
0°-40°	726.9	40.7
0°-60°	1323.9	74.2
0°-90°	1784.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1784.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	561	561	561	561	561	
5°	561	560	558	560	560	53
15°	542	542	541	545	544	153
25°	503	504	508	512	513	232
35°	446	450	457	465	467	279
45°	374	380	394	411	418	289
55°	289	300	326	352	365	258
65°	191	211	254	288	301	190
75°	90	123	172	201	207	97
85°	18	36	44	48	50	22
90°	0	0	0	0	0	



TEST NUMBER: P842985

CATALOG NUMBER: 24CZ2-30-RDP-UNV-B50

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	561.0	561.0	561.0	561.0	561.0
2.5°	561.9	561.9	559.2	561.0	561.0
5°	561.0	560.2	557.5	560.2	560.2
7.5°	558.4	557.5	555.7	558.4	557.5
10°	553.0	553.0	551.3	554.0	554.0
12.5°	548.6	547.8	546.8	550.4	549.5
15°	541.6	541.6	540.6	545.1	544.2
17.5°	532.7	533.6	534.5	538.0	538.9
20°	522.9	524.7	525.6	530.9	530.9
22.5°	514.1	515.0	516.7	522.1	522.1
25°	502.7	504.4	507.9	512.4	513.2
27.5°	491.1	492.0	496.5	502.7	503.5
30°	476.1	478.8	484.0	491.1	492.0
32.5°	462.8	465.4	471.6	478.8	480.5
35°	446.0	449.5	456.6	465.4	467.2
37.5°	431.0	433.6	442.5	452.2	454.9
40°	412.4	417.6	426.5	438.0	442.5
42.5°	393.8	399.1	409.7	424.8	430.1
45°	374.3	380.5	393.8	410.6	417.6
47.5°	354.9	361.9	377.0	396.4	404.4
50°	332.7	341.5	360.1	382.3	391.2
52.5°	311.5	322.1	342.5	367.3	378.8
55°	289.4	299.9	326.5	352.2	364.6
57.5°	264.6	278.7	307.9	337.2	350.4
60°	241.6	254.8	290.2	322.1	335.4
62.5°	216.8	234.5	272.5	306.1	319.5
65°	191.1	210.6	253.9	287.6	300.9
67.5°	168.2	189.4	235.4	269.0	282.3
70°	140.7	167.2	215.0	248.6	261.9
72.5°	115.0	144.3	193.8	226.5	238.9
75°	90.3	123.0	171.7	200.9	207.1
77.5°	67.2	101.8	148.6	161.0	156.6
80°	47.8	81.4	115.9	109.7	112.4
82.5°	30.9	62.0	71.7	81.4	84.1
85°	17.7	36.3	44.3	47.8	49.5
87.5°	8.0	13.2	17.7	17.7	16.9
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)