

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P881165

Luminaire Tested: **24CZ2-30VHE-UNV-B40**

Issue Date: 10/2/2024

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P881165
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P473819)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 10/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-30VHE-UNV-B40
Description: 2X4 3000 LUMEN CRUZE TROFFER WITH BIO UP LEDS AT 4000K CCT AND RIBBED LENS

Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2874.0 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.36
Luminous Opening: Rectangular (W 1.92' x L: 3.98' x H: 0')
CIE Type: Direct

Input Watts (W): 23
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P881165

CATALOG NUMBER: 24CZ2-30VHE-UNV-B40

Luminous Intensity Polar Plot





TEST NUMBER: P881165

CATALOG NUMBER: 24CZ2-30VHE-UNV-B40

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	108	103	99	95	105	101	97	93	97	93	90	93	90	87	89	87	85	83																			
2	98	89	82	76	95	88	81	75	84	78	74	81	76	72	78	74	70	68																			
3	89	78	70	63	87	77	69	63	74	67	61	71	65	60	68	63	59	57																			
4	82	69	60	53	79	68	59	53	65	58	52	63	57	51	61	55	51	48																			
5	75	62	53	46	73	61	52	46	58	51	45	56	50	44	55	49	44	42																			
6	69	56	46	40	67	55	46	40	53	45	39	51	44	39	49	43	39	37																			
7	64	50	41	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32																			
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29																			
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26																			
10	52	39	31	26	51	38	31	26	37	30	25	36	30	25	36	30	25	23																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1402	1402	1402
5°	1402	1395	1402
10°	1395	1390	1399
15°	1380	1380	1393
20°	1360	1368	1388
25°	1336	1351	1381
30°	1304	1336	1371
35°	1274	1318	1366
40°	1240	1297	1360
45°	1197	1283	1364
50°	1161	1269	1368
55°	1119	1260	1384
60°	1072	1254	1409
65°	1022	1250	1445
70°	962	1262	1512
75°	846	1289	1572
80°	706	1298	1517
85°	505	1112	1127



TEST NUMBER: P881165

CATALOG NUMBER: 24CZ2-30VHE-UNV-B40

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.9	3.3
10°-20°	267.4	9.3
20°-30°	401.2	14.0
30°-40°	479.0	16.7
40°-50°	496.1	17.3
50°-60°	456.7	15.9
60°-70°	368.4	12.8
70°-80°	240.7	8.4
80°-90°	70.6	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.5	26.5
0°-40°	1241.4	43.2
0°-60°	2194.3	76.3
0°-90°	2874.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2874.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	990	989	985	990	990	94
15°	945	945	944	954	954	266
25°	858	860	868	884	887	395
35°	740	746	765	786	793	462
45°	600	615	643	672	684	464
55°	455	474	512	550	562	407
65°	306	327	374	417	433	303
75°	155	184	236	277	288	166
85°	31	54	69	73	70	39
90°	0	0	0	0	0	



TEST NUMBER: P881165

CATALOG NUMBER: 24CZ2-30VHE-UNV-B40

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	993.1	993.1	993.1	993.1	993.1
2.5°	994.5	993.1	988.0	994.1	993.6
5°	989.9	989.0	984.8	990.3	989.9
7.5°	982.5	982.0	978.8	984.8	984.8
10°	973.2	972.3	969.9	976.9	976.4
12.5°	960.2	959.7	958.4	966.7	966.2
15°	944.8	944.8	944.4	953.7	953.7
17.5°	926.3	926.7	928.6	939.3	939.7
20°	905.4	907.3	911.0	923.0	924.0
22.5°	881.7	885.4	890.5	904.0	905.4
25°	858.0	859.9	867.8	883.5	886.8
27.5°	829.2	833.9	844.1	860.4	863.6
30°	800.0	806.5	819.5	836.3	841.4
32.5°	771.2	776.8	792.1	811.1	817.2
35°	739.7	746.1	765.1	786.1	792.6
37.5°	704.8	715.0	735.0	759.1	766.1
40°	672.8	682.1	703.9	730.8	738.3
42.5°	636.1	647.7	674.2	701.5	710.8
45°	599.8	614.8	643.0	671.9	683.5
47.5°	566.0	578.1	611.5	644.0	654.2
50°	528.8	542.7	578.1	612.5	623.1
52.5°	492.2	508.9	544.6	580.8	592.4
55°	454.6	474.0	512.1	549.8	562.3
57.5°	418.3	437.9	477.3	517.2	530.2
60°	379.8	400.7	444.4	482.8	499.2
62.5°	342.7	363.5	409.5	451.3	466.6
65°	305.9	326.9	374.3	416.9	432.8
67.5°	267.9	290.7	341.3	382.6	397.9
70°	233.1	254.9	305.9	350.1	366.3
72.5°	193.1	219.2	271.2	314.8	330.1
75°	155.1	184.3	236.3	277.2	288.3
77.5°	119.8	149.1	201.0	231.7	238.6
80°	86.9	116.5	159.7	181.1	186.6
82.5°	56.2	86.9	115.6	130.0	131.8
85°	31.2	53.9	68.7	72.9	69.6
87.5°	11.1	20.4	19.9	16.2	13.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)