

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P387435

Luminaire Tested: **14CZ2-29-SQR-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P387435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1911-580-2)
Test Lab: INNOVATIONS CENTER(G2)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 14CZ2-29-SQR-UNV-L935-CD1-SDWPD1-U
Description: 1x4 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND SQUARE LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2280.9 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.34 / 1.44
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 24.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P387435

CATALOG NUMBER: 14CZ2-29-SQR-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P387435

CATALOG NUMBER: 14CZ2-29-SQR-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90	93	90	87	89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61	70	64	60	68	63	59	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	51	60	54	50	48
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	68	55	45	39	67	54	45	39	52	44	38	50	43	38	49	42	38	35
7	63	49	40	34	62	49	40	34	47	39	34	46	39	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	39	32	27	38	32	27	37	31	27	25
10	52	38	30	25	50	37	30	24	36	29	24	36	29	24	35	29	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1940	1940	1940
5°	1953	1947	1947
10°	1944	1957	1963
15°	1928	1960	1979
20°	1906	1965	1995
25°	1884	1963	2004
30°	1850	1961	2018
35°	1820	1964	2047
40°	1789	1975	2084
45°	1763	1995	2135
50°	1723	2017	2190
55°	1694	2049	2254
60°	1658	2091	2314
65°	1581	2130	2372
70°	1501	2135	2370
75°	1375	2127	2092
80°	1176	1818	1621
85°	923	1028	602



TEST NUMBER: P387435

CATALOG NUMBER: 14CZ2-29-SQR-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.5	3.0
10°-20°	197.9	8.7
20°-30°	302.6	13.3
30°-40°	370.9	16.3
40°-50°	398.9	17.5
50°-60°	383.3	16.8
60°-70°	319.2	14.0
70°-80°	195.9	8.6
80°-90°	43.6	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	569.0	24.9
0°-40°	939.9	41.2
0°-60°	1722.1	75.5
0°-90°	2280.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2280.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	721	721	721	721	721	
5°	723	716	721	721	721	69
15°	692	690	704	708	710	195
25°	635	640	661	669	675	292
35°	554	568	598	614	623	347
45°	463	484	524	548	561	357
55°	361	392	437	467	480	322
65°	248	286	334	362	372	246
75°	132	172	205	204	201	140
85°	30	45	33	23	20	36
90°	0	0	0	0	0	



TEST NUMBER: P387435

CATALOG NUMBER: 14CZ2-29-SQR-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	720.8	720.8	720.8	720.8	720.8
2.5°	725.4	718.5	721.9	720.8	717.3
5°	723.1	716.2	720.8	720.8	720.8
7.5°	717.3	711.6	718.5	719.6	719.6
10°	711.6	707.0	716.2	717.3	718.5
12.5°	702.4	698.9	710.4	712.7	715.0
15°	692.0	689.7	703.5	708.1	710.4
17.5°	679.4	680.5	695.5	701.2	703.5
20°	665.6	669.1	686.3	692.0	696.6
22.5°	650.7	655.3	673.7	680.5	685.1
25°	634.6	640.3	661.0	669.1	674.8
27.5°	615.0	624.2	647.2	657.6	663.3
30°	595.5	605.8	631.1	643.8	649.5
32.5°	575.9	587.4	616.2	628.8	638.0
35°	554.1	567.9	597.8	613.9	623.1
37.5°	532.3	548.3	580.5	598.9	609.3
40°	509.3	526.5	562.1	582.8	593.2
42.5°	486.3	505.8	542.6	565.6	577.1
45°	463.3	484.0	524.2	548.3	561.0
47.5°	436.8	462.1	502.4	530.0	542.6
50°	411.5	439.1	481.7	510.4	523.1
52.5°	386.3	415.0	459.8	489.7	502.4
55°	361.0	392.0	436.8	466.7	480.5
57.5°	334.5	366.7	412.7	443.7	456.4
60°	308.1	341.4	388.6	417.3	429.9
62.5°	277.0	316.1	362.1	390.9	402.4
65°	248.3	286.2	334.5	362.1	372.5
67.5°	219.6	258.7	305.8	331.1	340.3
70°	190.8	229.9	271.3	295.4	301.2
72.5°	162.1	201.2	240.3	254.1	251.8
75°	132.2	172.4	204.6	203.5	201.2
77.5°	103.5	142.5	162.1	154.0	150.6
80°	75.9	113.8	117.3	109.2	104.6
82.5°	51.7	81.6	73.6	64.4	59.8
85°	29.9	44.8	33.3	23.0	19.5
87.5°	12.6	11.5	3.4	3.4	2.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)