

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P387507

Luminaire Tested: **14CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P387507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1911-580-2)
Test Lab: INNOVATIONS CENTER(G2)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 14CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U
Description: 1x4 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND SQUARE LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3141.2 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.34 / 1.44
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 29.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P387507

CATALOG NUMBER: 14CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P387507

CATALOG NUMBER: 14CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90	93	90	87	89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61	70	64	60	68	63	59	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	51	60	54	50	48
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	68	55	45	39	67	54	45	39	52	44	38	50	43	38	49	42	38	35
7	63	49	40	34	62	49	40	34	47	39	34	46	39	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	39	32	27	38	32	27	37	31	27	25
10	52	38	30	25	50	37	30	24	36	29	24	36	29	24	35	29	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2671	2671	2671
5°	2690	2681	2681
10°	2678	2695	2704
15°	2655	2699	2726
20°	2625	2707	2747
25°	2595	2703	2759
30°	2548	2701	2779
35°	2507	2704	2819
40°	2464	2720	2870
45°	2428	2747	2940
50°	2373	2777	3015
55°	2332	2822	3105
60°	2284	2880	3187
65°	2178	2933	3266
70°	2068	2939	3264
75°	1893	2930	2881
80°	1619	2503	2233
85°	1272	1417	831



TEST NUMBER: P387507

CATALOG NUMBER: 14CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	3.0
10°-20°	272.5	8.7
20°-30°	416.7	13.3
30°-40°	510.8	16.3
40°-50°	549.4	17.5
50°-60°	527.9	16.8
60°-70°	439.6	14.0
70°-80°	269.8	8.6
80°-90°	60.1	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	783.6	24.9
0°-40°	1294.4	41.2
0°-60°	2371.7	75.5
0°-90°	3141.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3141.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	996	986	993	993	993	94
15°	953	950	969	975	978	269
25°	874	882	910	921	929	402
35°	763	782	823	845	858	478
45°	638	666	722	755	773	491
55°	497	540	602	643	662	444
65°	342	394	461	499	513	339
75°	182	238	282	280	277	193
85°	41	62	46	32	27	50
90°	0	0	0	0	0	



TEST NUMBER: P387507

CATALOG NUMBER: 14CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	992.6	992.6	992.6	992.6	992.6
2.5°	999.0	989.5	994.2	992.6	987.9
5°	995.8	986.3	992.6	992.6	992.6
7.5°	987.9	980.0	989.5	991.1	991.1
10°	980.0	973.6	986.3	987.9	989.5
12.5°	967.3	962.6	978.4	981.6	984.7
15°	953.1	949.9	968.9	975.2	978.4
17.5°	935.7	937.2	957.8	965.7	968.9
20°	916.7	921.4	945.2	953.1	959.4
22.5°	896.1	902.4	927.7	937.2	943.6
25°	873.9	881.8	910.3	921.4	929.3
27.5°	847.0	859.7	891.3	905.6	913.5
30°	820.1	834.3	869.2	886.6	894.5
32.5°	793.2	809.0	848.6	866.0	878.7
35°	763.1	782.1	823.2	845.4	858.1
37.5°	733.0	755.2	799.5	824.8	839.1
40°	701.3	725.1	774.2	802.7	816.9
42.5°	669.7	696.6	747.3	778.9	794.8
45°	638.0	666.5	721.9	755.2	772.6
47.5°	601.6	636.4	691.8	729.8	747.3
50°	566.8	604.8	663.3	702.9	720.3
52.5°	531.9	571.5	633.3	674.4	691.8
55°	497.1	539.9	601.6	642.8	661.8
57.5°	460.7	505.0	568.4	611.1	628.5
60°	424.3	470.2	535.1	574.7	592.1
62.5°	381.5	435.4	498.7	538.3	554.1
65°	342.0	394.2	460.7	498.7	512.9
67.5°	302.4	356.2	421.1	456.0	468.6
70°	262.8	316.6	373.6	406.9	414.8
72.5°	223.2	277.1	330.9	349.9	346.7
75°	182.1	237.5	281.8	280.2	277.1
77.5°	142.5	196.3	223.2	212.1	207.4
80°	104.5	156.7	161.5	150.4	144.1
82.5°	71.2	112.4	101.3	88.7	82.3
85°	41.2	61.7	45.9	31.7	26.9
87.5°	17.4	15.8	4.7	4.7	3.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)