

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P390528

Luminaire Tested: **22CZ2-60VHE-RDP-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P390528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-24)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 22CZ2-60VHE-RDP-UNV-L935-CD1-SDWPD1-U
Description: 2x2 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND RDP LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3389.9 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 44.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P390528

CATALOG NUMBER: 22CZ2-60VHE-RDP-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P390528

CATALOG NUMBER: 22CZ2-60VHE-RDP-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	86	88	86	84	82
2	97	88	81	75	95	86	80	74	83	77	72	80	75	71	76	72	69	67
3	88	77	68	61	86	75	67	61	72	65	60	70	64	59	67	62	58	55
4	80	68	59	51	78	66	58	51	64	56	50	61	55	50	59	54	49	47
5	74	60	51	44	72	59	50	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	35
7	63	49	40	33	61	48	39	33	47	39	33	45	38	33	44	37	33	31
8	59	45	36	30	57	44	35	30	43	35	29	41	34	29	40	34	29	27
9	55	41	32	27	53	40	32	27	39	32	26	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2865	2865	2865
5°	2850	2870	2870
10°	2842	2862	2876
15°	2828	2855	2876
20°	2806	2849	2878
25°	2799	2858	2888
30°	2774	2836	2890
35°	2744	2826	2908
40°	2707	2821	2943
45°	2667	2818	3037
50°	2610	2840	3163
55°	2539	2901	3346
60°	2456	2979	3583
65°	2287	3128	3875
70°	2099	3277	4238
75°	1841	3449	4381
80°	1584	3285	3439
85°	1386	2387	2618



TEST NUMBER: P390528

CATALOG NUMBER: 22CZ2-60VHE-RDP-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.7	3.0
10°-20°	289.2	8.5
20°-30°	441.2	13.0
30°-40°	538.8	15.9
40°-50°	576.0	17.0
50°-60°	556.0	16.4
60°-70°	478.6	14.1
70°-80°	323.8	9.6
80°-90°	85.4	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	831.2	24.5
0°-40°	1369.9	40.4
0°-60°	2502.0	73.8
0°-90°	3389.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3389.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1065	1065	1065	1065	1065	
5°	1055	1057	1062	1062	1062	100
15°	1015	1017	1025	1030	1032	286
25°	943	948	963	968	973	434
35°	835	843	860	878	885	523
45°	701	713	741	778	798	541
55°	541	559	618	681	713	485
65°	359	394	491	569	608	357
75°	177	234	332	399	421	190
85°	45	62	77	80	85	51
90°	0	0	0	0	0	



TEST NUMBER: P390528

CATALOG NUMBER: 22CZ2-60VHE-RDP-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1064.8	1064.8	1064.8	1064.8	1064.8
2.5°	1057.3	1059.8	1064.8	1064.8	1067.3
5°	1054.9	1057.3	1062.3	1062.3	1062.3
7.5°	1047.4	1049.9	1054.9	1057.3	1057.3
10°	1039.9	1042.4	1047.4	1049.9	1052.4
12.5°	1027.4	1029.9	1037.4	1042.4	1042.4
15°	1015.0	1017.4	1024.9	1029.9	1032.4
17.5°	1000.0	1005.0	1012.5	1017.4	1019.9
20°	980.0	985.0	995.0	1002.5	1005.0
22.5°	962.6	967.6	977.5	985.0	990.0
25°	942.6	947.6	962.6	967.6	972.6
27.5°	917.7	922.7	935.2	945.1	952.6
30°	892.8	897.7	912.7	925.2	930.2
32.5°	865.3	872.8	890.3	900.2	907.7
35°	835.4	842.9	860.3	877.8	885.3
37.5°	805.5	813.0	830.4	852.9	862.8
40°	770.6	780.5	803.0	832.9	837.9
42.5°	738.1	750.6	770.6	805.5	817.9
45°	700.7	713.2	740.6	778.0	798.0
47.5°	665.8	678.3	708.2	753.1	778.0
50°	623.4	640.9	678.3	730.7	755.6
52.5°	583.5	598.5	648.4	705.7	735.7
55°	541.1	558.6	618.4	680.8	713.2
57.5°	503.7	518.7	586.0	655.9	693.3
60°	456.4	476.3	553.6	628.4	665.8
62.5°	406.5	436.4	521.2	598.5	638.4
65°	359.1	394.0	491.3	568.6	608.5
67.5°	316.7	354.1	453.9	536.2	573.6
70°	266.8	314.2	416.5	496.3	538.6
72.5°	221.9	274.3	374.1	453.9	491.3
75°	177.1	234.4	331.7	399.0	421.4
77.5°	137.2	192.0	284.3	304.2	306.7
80°	102.2	152.1	212.0	214.5	221.9
82.5°	69.8	107.2	137.2	149.6	152.1
85°	44.9	62.3	77.3	79.8	84.8
87.5°	19.9	22.4	27.4	24.9	24.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)