

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P388224

Luminaire Tested: **22CZ2-24VHE-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P388224
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-27)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 22CZ2-24VHE-UNV-L935-CD1-SDWPD1-U
Description: 2x2 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND RIBBED LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2063.1 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.27 / 1.36
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 17.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P388224

CATALOG NUMBER: 22CZ2-24VHE-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P388224

CATALOG NUMBER: 22CZ2-24VHE-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	81	75	84	78	73	80	76	71	77	73	70	68
3	89	78	69	63	86	76	68	62	73	66	61	70	65	60	68	63	59	56
4	81	69	60	53	79	67	59	52	65	57	52	63	56	51	60	55	50	48
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	44	41
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	36
7	64	50	41	35	62	49	41	35	48	40	34	46	39	34	45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31	42	35	30	41	35	30	28
9	56	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27	25
10	52	39	31	25	51	38	30	25	37	30	25	36	30	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1888	1888	1888
5°	1876	1890	1895
10°	1864	1884	1892
15°	1841	1869	1886
20°	1814	1849	1875
25°	1781	1839	1869
30°	1744	1804	1858
35°	1704	1781	1854
40°	1662	1751	1858
45°	1615	1731	1870
50°	1568	1713	1891
55°	1514	1705	1924
60°	1470	1704	1983
65°	1396	1733	2055
70°	1302	1766	2189
75°	1193	1826	2364
80°	1038	1903	2328
85°	908	1692	1849



TEST NUMBER: P388224

CATALOG NUMBER: 22CZ2-24VHE-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.3	3.2
10°-20°	189.0	9.2
20°-30°	283.7	13.7
30°-40°	339.0	16.4
40°-50°	352.5	17.1
50°-60°	326.7	15.8
60°-70°	268.0	13.0
70°-80°	181.1	8.8
80°-90°	56.9	2.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	539.0	26.1
0°-40°	877.9	42.6
0°-60°	1557.1	75.5
0°-90°	2063.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2063.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	702	702	702	702	702	
5°	694	695	700	700	702	66
15°	661	664	671	675	677	186
25°	600	605	619	626	629	276
35°	519	526	542	558	564	324
45°	424	432	455	481	491	328
55°	323	333	363	396	410	290
65°	219	232	272	308	323	217
75°	115	134	176	211	227	122
85°	29	41	55	61	60	33
90°	0	0	0	0	0	



TEST NUMBER: P388224

CATALOG NUMBER: 22CZ2-24VHE-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	701.5	701.5	701.5	701.5	701.5
2.5°	697.4	699.5	702.5	703.5	703.5
5°	694.4	695.4	699.5	700.5	701.5
7.5°	689.3	691.3	695.4	696.4	697.4
10°	682.2	684.2	689.3	691.3	692.4
12.5°	673.1	675.1	681.2	684.2	685.2
15°	660.9	663.9	671.0	675.1	677.1
17.5°	648.7	651.7	658.9	664.9	667.0
20°	633.5	640.6	645.7	653.8	654.8
22.5°	618.2	622.3	631.4	639.6	643.6
25°	600.0	605.0	619.3	626.4	629.4
27.5°	580.7	587.8	599.0	610.1	614.2
30°	561.4	566.5	580.7	593.9	597.9
32.5°	540.1	547.2	562.4	575.6	581.7
35°	518.8	525.9	542.1	558.4	564.4
37.5°	495.4	503.5	519.8	539.1	547.2
40°	473.1	479.2	498.5	521.8	528.9
42.5°	449.7	456.8	477.1	502.5	510.6
45°	424.3	432.5	454.8	481.2	491.3
47.5°	400.0	408.1	432.5	458.9	471.0
50°	374.6	384.8	409.1	439.6	451.8
52.5°	350.2	359.4	386.8	418.3	429.4
55°	322.8	333.0	363.4	395.9	410.1
57.5°	300.5	307.6	341.1	374.6	388.8
60°	273.1	282.2	316.7	352.3	368.5
62.5°	243.6	258.9	294.4	330.9	347.2
65°	219.3	231.5	272.1	307.6	322.8
67.5°	193.9	207.1	246.7	284.3	301.5
70°	165.5	182.7	224.4	261.9	278.2
72.5°	140.1	158.4	201.0	237.6	254.8
75°	114.7	134.0	175.6	211.2	227.4
77.5°	90.4	111.7	152.3	179.7	189.8
80°	67.0	87.3	122.8	142.1	150.2
82.5°	46.7	64.0	90.4	100.5	102.5
85°	29.4	40.6	54.8	60.9	59.9
87.5°	13.2	16.2	20.3	22.3	21.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)