

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: METALUX

Report Number: P388296

Luminaire Tested: **22CZ2-39VHE-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P388296  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-27)  
Test Lab: INNOVATIONS CENTER(G3)  
Issue Date: 2/28/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 22CZ2-39VHE-UNV-L935-CD1-SDWPD1-U  
Description: 2x2 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND RIBBED LENS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3364.0 lumens  
Efficiency: N/A  
Efficacy: 117.6 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.27 / 1.36  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P388296

CATALOG NUMBER: 22CZ2-39VHE-UNV-L935-CD1-SDWPD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P388296

CATALOG NUMBER: 22CZ2-39VHE-UNV-L935-CD1-SDWPD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90		92	90	87		89	86	84	82
2	98	89	82	76	95	87	81	75	84	78	73		80	76	71		77	73	70	68
3	89	78	69	63	86	76	68	62	73	66	61		70	65	60		68	63	59	56
4	81	69	60	53	79	67	59	52	65	57	52		63	56	51		60	55	50	48
5	75	61	52	45	72	60	52	45	58	50	44		56	49	44		54	48	44	41
6	69	55	46	39	67	54	46	39	52	45	39		51	44	39		49	43	38	36
7	64	50	41	35	62	49	41	35	48	40	34		46	39	34		45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31		42	35	30		41	35	30	28
9	56	42	34	28	54	41	33	28	40	33	28		39	32	27		38	32	27	25
10	52	39	31	25	51	38	30	25	37	30	25		36	30	25		35	29	25	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3078	3078	3078
5°	3058	3081	3090
10°	3040	3071	3085
15°	3002	3048	3076
20°	2958	3015	3058
25°	2905	2998	3047
30°	2844	2942	3030
35°	2779	2904	3024
40°	2710	2855	3029
45°	2633	2822	3049
50°	2557	2793	3084
55°	2470	2780	3137
60°	2397	2780	3234
65°	2276	2825	3352
70°	2123	2878	3569
75°	1945	2978	3855
80°	1694	3104	3797
85°	1482	2760	3017



TEST NUMBER: P388296

CATALOG NUMBER: 22CZ2-39VHE-UNV-L935-CD1-SDWPD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.2	3.2
10°-20°	308.1	9.2
20°-30°	462.5	13.7
30°-40°	552.7	16.4
40°-50°	574.7	17.1
50°-60°	532.7	15.8
60°-70°	436.9	13.0
70°-80°	295.4	8.8
80°-90°	92.8	2.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	878.8	26.1
0°-40°	1431.5	42.6
0°-60°	2538.9	75.5
0°-90°	3364.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3364.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1144	1144	1144	1144	1144	
5°	1132	1134	1140	1142	1144	107
15°	1078	1083	1094	1101	1104	304
25°	978	987	1010	1021	1026	451
35°	846	858	884	910	920	529
45°	692	705	742	785	801	534
55°	526	543	593	646	669	473
65°	358	377	444	502	526	353
75°	187	218	286	344	371	198
85°	48	66	89	99	98	54
90°	0	0	0	0	0	



TEST NUMBER: P388296

CATALOG NUMBER: 22CZ2-39VHE-UNV-L935-CD1-SDWPD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1143.8	1143.8	1143.8	1143.8	1143.8
2.5°	1137.2	1140.5	1145.5	1147.1	1147.1
5°	1132.2	1133.9	1140.5	1142.2	1143.8
7.5°	1124.0	1127.3	1133.9	1135.5	1137.2
10°	1112.4	1115.7	1124.0	1127.3	1128.9
12.5°	1097.5	1100.8	1110.7	1115.7	1117.3
15°	1077.6	1082.6	1094.2	1100.8	1104.1
17.5°	1057.7	1062.7	1074.3	1084.2	1087.5
20°	1032.9	1044.5	1052.8	1066.0	1067.7
22.5°	1008.1	1014.7	1029.6	1042.8	1049.5
25°	978.3	986.6	1009.7	1021.3	1026.3
27.5°	946.8	958.4	976.6	994.8	1001.5
30°	915.4	923.7	946.8	968.4	975.0
32.5°	880.6	892.2	917.0	938.6	948.5
35°	845.9	857.5	883.9	910.4	920.4
37.5°	807.8	821.0	847.5	879.0	892.2
40°	771.4	781.3	812.8	850.8	862.4
42.5°	733.3	744.9	778.0	819.4	832.6
45°	691.9	705.2	741.6	784.6	801.2
47.5°	652.2	665.4	705.2	748.2	768.1
50°	610.8	627.4	667.1	716.8	736.6
52.5°	571.1	586.0	630.7	682.0	700.2
55°	526.4	542.9	592.6	645.6	668.7
57.5°	490.0	501.6	556.2	610.8	634.0
60°	445.3	460.2	516.5	574.4	600.9
62.5°	397.3	422.1	480.0	539.6	566.1
65°	357.5	377.4	443.6	501.6	526.4
67.5°	316.2	337.7	402.2	463.5	491.6
70°	269.8	298.0	365.8	427.1	453.6
72.5°	228.4	258.2	327.8	387.3	415.5
75°	187.1	218.5	286.4	344.3	370.8
77.5°	147.3	182.1	248.3	293.0	309.5
80°	109.3	142.4	200.3	231.7	245.0
82.5°	76.1	104.3	147.3	163.9	167.2
85°	48.0	66.2	89.4	99.3	97.7
87.5°	21.5	26.5	33.1	36.4	34.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)