

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P389135

Luminaire Tested: **22CZ2-20VHE-S-UNV-L930-CD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P389135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-23)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 22CZ2-20VHE-S-UNV-L930-CD1-U
Description: 2x2 CRUZE LED TROFFER WITH 3000K, 90 LEDS, AND SMOOTH LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1740.8 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.26 / 1.34
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P389135

CATALOG NUMBER: 22CZ2-20VHE-S-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P389135

CATALOG NUMBER: 22CZ2-20VHE-S-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	106	101	97	94	97	94	91		93	90	88		89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74		81	77	73		78	74	71	69
3	90	79	71	64	87	77	70	63	74	68	62		72	66	61		69	64	60	58
4	82	70	61	54	80	69	60	54	66	59	53		64	57	52		61	56	52	49
5	75	62	53	47	73	61	53	46	59	52	46		57	51	45		55	50	45	43
6	70	56	47	41	68	55	47	41	53	46	40		52	45	40		50	44	39	37
7	65	51	42	36	63	50	42	36	49	41	36		47	40	35		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		43	37	32		42	36	31	30
9	56	43	35	29	55	42	34	29	41	34	29		40	33	29		39	33	28	27
10	53	40	32	26	51	39	31	26	38	31	26		37	31	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1679	1679	1679
5°	1667	1681	1685
10°	1658	1673	1682
15°	1636	1659	1674
20°	1610	1642	1668
25°	1577	1625	1657
30°	1537	1592	1643
35°	1494	1564	1628
40°	1444	1532	1612
45°	1391	1496	1595
50°	1340	1455	1581
55°	1277	1429	1570
60°	1220	1394	1565
65°	1138	1386	1582
70°	1048	1374	1629
75°	946	1393	1714
80°	818	1435	1612
85°	676	1204	1204



TEST NUMBER: P389135

CATALOG NUMBER: 22CZ2-20VHE-S-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.0	3.4
10°-20°	167.9	9.6
20°-30°	251.2	14.4
30°-40°	297.5	17.1
40°-50°	303.1	17.4
50°-60°	271.7	15.6
60°-70°	212.7	12.2
70°-80°	137.2	7.9
80°-90°	40.5	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	478.0	27.5
0°-40°	775.5	44.5
0°-60°	1350.4	77.6
0°-90°	1740.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1740.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	617	619	622	623	624	59
15°	587	590	595	600	601	166
25°	531	536	547	555	558	245
35°	455	460	476	491	496	284
45°	366	374	393	413	419	282
55°	272	281	305	326	335	244
65°	179	189	218	239	248	178
75°	91	105	134	157	165	98
85°	22	30	39	39	39	26
90°	0	0	0	0	0	



TEST NUMBER: P389135

CATALOG NUMBER: 22CZ2-20VHE-S-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	623.8	623.8	623.8	623.8	623.8
2.5°	619.7	621.3	624.6	625.4	625.4
5°	617.3	618.9	622.2	623.0	623.8
7.5°	613.2	614.0	618.1	619.7	620.5
10°	606.7	608.4	612.4	614.8	615.7
12.5°	597.8	600.2	605.1	608.4	609.2
15°	587.2	590.5	595.4	600.2	601.0
17.5°	575.9	579.1	585.6	591.3	592.9
20°	562.1	566.1	573.4	579.9	582.4
22.5°	548.2	551.5	560.4	568.6	571.0
25°	531.2	536.1	547.4	554.7	558.0
27.5°	513.3	519.0	530.4	540.1	543.4
30°	494.6	500.3	512.5	524.7	528.8
32.5°	475.1	481.6	496.3	508.4	512.5
35°	454.8	460.5	476.0	490.6	495.5
37.5°	433.7	438.6	456.5	471.9	476.8
40°	411.0	417.5	436.2	454.0	458.9
42.5°	388.2	395.5	414.2	433.7	438.6
45°	365.5	373.6	393.1	413.4	419.1
47.5°	343.6	350.1	372.0	391.5	399.6
50°	320.0	326.5	347.6	369.6	377.7
52.5°	295.6	304.6	327.3	348.4	358.2
55°	272.1	281.0	304.6	325.7	334.6
57.5°	250.2	257.5	281.8	303.8	312.7
60°	226.6	233.1	259.1	282.7	290.8
62.5°	201.4	211.2	238.0	259.9	269.7
65°	178.7	189.2	217.7	238.8	248.5
67.5°	157.6	167.3	194.9	217.7	228.2
70°	133.2	146.2	174.6	197.4	207.1
72.5°	113.7	125.1	154.3	177.1	187.6
75°	91.0	104.8	134.0	156.8	164.9
77.5°	72.3	86.1	113.7	131.6	135.6
80°	52.8	66.6	92.6	101.5	104.0
82.5°	35.7	48.7	66.6	69.0	69.9
85°	21.9	30.1	39.0	39.0	39.0
87.5°	10.6	12.2	13.8	13.0	13.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)