

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P389255

Luminaire Tested: **22CZ2-44VHE-S-UNV-L930-CD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P389255
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-23)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 22CZ2-44VHE-S-UNV-L930-CD1-U
Description: 2x2 CRUZE LED TROFFER WITH 3000K, 90 LEDS, AND SMOOTH LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4005.2 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.26 / 1.34
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 32.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P389255

CATALOG NUMBER: 22CZ2-44VHE-S-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P389255

CATALOG NUMBER: 22CZ2-44VHE-S-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	94	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	71	64	87	77	70	63	74	68	62	72	66	61	69	64	60	58
4	82	70	61	54	80	69	60	54	66	59	53	64	57	52	61	56	52	49
5	75	62	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	43
6	70	56	47	41	68	55	47	41	53	46	40	52	45	40	50	44	39	37
7	65	51	42	36	63	50	42	36	49	41	36	47	40	35	46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	31	30
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	28	27
10	53	40	32	26	51	39	31	26	38	31	26	37	31	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3862	3862	3862
5°	3836	3867	3877
10°	3814	3850	3871
15°	3764	3816	3853
20°	3703	3778	3837
25°	3629	3740	3812
30°	3536	3664	3780
35°	3438	3597	3745
40°	3322	3525	3709
45°	3200	3442	3670
50°	3082	3348	3638
55°	2937	3288	3612
60°	2806	3208	3601
65°	2618	3189	3641
70°	2412	3161	3749
75°	2176	3205	3945
80°	1883	3301	3707
85°	1559	2770	2770



TEST NUMBER: P389255

CATALOG NUMBER: 22CZ2-44VHE-S-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.7	3.4
10°-20°	386.2	9.6
20°-30°	577.9	14.4
30°-40°	684.4	17.1
40°-50°	697.5	17.4
50°-60°	625.2	15.6
60°-70°	489.4	12.2
70°-80°	315.6	7.9
80°-90°	93.2	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1099.9	27.5
0°-40°	1784.3	44.5
0°-60°	3106.9	77.6
0°-90°	4005.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4005.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1435	1435	1435	1435	1435	
5°	1420	1424	1432	1433	1435	135
15°	1351	1359	1370	1381	1383	381
25°	1222	1233	1260	1276	1284	563
35°	1046	1060	1095	1129	1140	654
45°	841	860	904	951	964	649
55°	626	647	701	749	770	561
65°	411	435	501	549	572	408
75°	209	241	308	361	379	224
85°	50	69	90	90	90	59
90°	0	0	0	0	0	



TEST NUMBER: P389255

CATALOG NUMBER: 22CZ2-44VHE-S-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1435.2	1435.2	1435.2	1435.2	1435.2
2.5°	1425.8	1429.6	1437.1	1438.9	1438.9
5°	1420.2	1424.0	1431.5	1433.3	1435.2
7.5°	1410.9	1412.8	1422.1	1425.8	1427.7
10°	1395.9	1399.7	1409.0	1414.6	1416.5
12.5°	1375.4	1381.0	1392.2	1399.7	1401.6
15°	1351.1	1358.6	1369.8	1381.0	1382.9
17.5°	1324.9	1332.4	1347.4	1360.4	1364.2
20°	1293.2	1302.5	1319.3	1334.3	1339.9
22.5°	1261.4	1268.9	1289.4	1308.1	1313.7
25°	1222.2	1233.4	1259.5	1276.3	1283.8
27.5°	1181.0	1194.1	1220.3	1242.7	1250.2
30°	1138.1	1151.1	1179.2	1207.2	1216.5
32.5°	1093.2	1108.2	1141.8	1169.8	1179.2
35°	1046.5	1059.6	1095.1	1128.7	1139.9
37.5°	997.9	1009.1	1050.2	1085.7	1096.9
40°	945.6	960.5	1003.5	1044.6	1055.8
42.5°	893.3	910.1	953.1	997.9	1009.1
45°	840.9	859.6	904.5	951.2	964.3
47.5°	790.5	805.4	855.9	900.7	919.4
50°	736.3	751.2	799.8	850.3	869.0
52.5°	680.2	700.8	753.1	801.7	824.1
55°	626.0	646.6	700.8	749.4	769.9
57.5°	575.6	592.4	648.5	698.9	719.5
60°	521.4	536.3	596.1	650.3	669.0
62.5°	463.4	485.9	547.5	598.0	620.4
65°	411.1	435.4	500.8	549.4	571.8
67.5°	362.5	385.0	448.5	500.8	525.1
70°	306.5	336.4	401.8	454.1	476.5
72.5°	261.6	287.8	355.1	407.4	431.7
75°	209.3	241.1	308.3	360.7	379.4
77.5°	166.3	198.1	261.6	302.7	312.1
80°	121.5	153.2	213.0	233.6	239.2
82.5°	82.2	112.1	153.2	158.8	160.7
85°	50.5	69.1	89.7	89.7	89.7
87.5°	24.3	28.0	31.8	29.9	29.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)