

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P387843

Luminaire Tested: **22CZ2-32-SQR-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P387843
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-542-6)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 22CZ2-32-SQR-UNV-L935-CD1-SDWPD1-U
Description: 2x2 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND SQUARE LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2598.6 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.31 / 1.37
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 26.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P387843

CATALOG NUMBER: 22CZ2-32-SQR-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P387843

CATALOG NUMBER: 22CZ2-32-SQR-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	99	95	106	101	97	94	97	94	91	93	91	88	90	87	85	83
2	99	90	83	77	96	88	82	76	85	79	75	81	77	73	78	75	71	69
3	90	79	71	64	87	77	70	63	74	68	62	72	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	64	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	43
6	70	56	47	41	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2443	2443	2443
5°	2425	2449	2462
10°	2403	2447	2474
15°	2364	2436	2481
20°	2313	2419	2487
25°	2249	2395	2483
30°	2173	2365	2480
35°	2095	2330	2488
40°	2006	2301	2496
45°	1910	2272	2516
50°	1828	2251	2535
55°	1730	2234	2575
60°	1639	2224	2602
65°	1531	2207	2623
70°	1407	2174	2659
75°	1269	2116	2565
80°	1089	1874	1931
85°	877	1105	877



TEST NUMBER: P387843

CATALOG NUMBER: 22CZ2-32-SQR-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.1	3.3
10°-20°	246.0	9.5
20°-30°	369.5	14.2
30°-40°	440.7	17.0
40°-50°	455.7	17.5
50°-60°	418.9	16.1
60°-70°	333.5	12.8
70°-80°	203.8	7.8
80°-90°	44.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.6	27.0
0°-40°	1142.4	44.0
0°-60°	2017.0	77.6
0°-90°	2598.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2598.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	908	908	908	908	908	
5°	898	900	906	910	911	85
15°	848	858	874	887	890	239
25°	757	776	807	829	836	348
35°	638	665	709	746	757	398
45°	502	538	597	645	661	388
55°	369	410	476	530	549	330
65°	240	281	347	395	412	238
75°	122	158	204	239	247	130
85°	28	34	36	31	28	33
90°	0	0	0	0	0	



TEST NUMBER: P387843

CATALOG NUMBER: 22CZ2-32-SQR-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	907.7	907.7	907.7	907.7	907.7
2.5°	902.8	904.0	907.7	910.2	910.2
5°	897.9	900.3	906.5	910.2	911.4
7.5°	890.5	894.2	902.8	907.7	909.0
10°	879.4	884.3	895.4	902.8	905.3
12.5°	865.8	873.2	886.8	896.6	899.1
15°	848.5	858.4	874.4	886.8	890.5
17.5°	828.8	841.1	860.9	875.7	880.6
20°	807.8	820.2	844.8	862.1	868.3
22.5°	783.2	799.2	827.6	847.3	852.2
25°	757.3	775.8	806.6	828.8	836.2
27.5°	728.9	751.1	784.4	811.5	817.7
30°	699.3	722.7	761.0	790.6	798.0
32.5°	668.5	695.6	736.3	769.6	779.5
35°	637.6	664.8	709.2	746.2	757.3
37.5°	601.9	633.9	683.3	721.5	735.1
40°	571.0	601.9	654.9	696.8	710.4
42.5°	536.5	569.8	625.3	670.9	687.0
45°	502.0	537.7	596.9	645.0	661.1
47.5°	469.9	505.7	567.3	617.9	633.9
50°	436.6	473.6	537.7	589.5	605.6
52.5°	400.8	441.5	508.1	559.9	578.4
55°	368.8	409.5	476.1	530.3	548.8
57.5°	335.5	377.4	446.5	498.3	515.5
60°	304.6	345.3	413.2	463.7	483.5
62.5°	271.3	313.3	379.9	429.2	447.7
65°	240.5	281.2	346.6	394.7	411.9
67.5°	209.7	250.4	312.0	357.7	377.4
70°	178.8	219.5	276.3	320.7	337.9
72.5°	151.7	187.5	241.7	282.4	298.5
75°	122.1	157.9	203.5	239.3	246.7
77.5°	95.0	127.0	165.3	181.3	183.8
80°	70.3	95.0	120.9	124.6	124.6
82.5°	46.9	65.4	75.2	76.5	75.2
85°	28.4	34.5	35.8	30.8	28.4
87.5°	9.9	9.9	6.2	3.7	1.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)