

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P387939

Luminaire Tested: **22CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P387939
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-542-6)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 22CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U
Description: 2x2 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND SQUARE LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3113.5 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.31 / 1.37
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 30.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P387939

CATALOG NUMBER: 22CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P387939

CATALOG NUMBER: 22CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	104	99	95	106	101	97	94	97	94	91	93	91	88	90	87	85
2	99	90	83	77	96	88	82	76	85	79	75	81	77	73	78	75	71
3	90	79	71	64	87	77	70	63	74	68	62	72	66	61	69	64	60
4	82	70	61	54	80	68	60	54	66	59	53	64	57	52	61	56	51
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45
6	70	56	47	41	68	55	47	40	53	46	40	52	45	40	50	44	39
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2927	2927	2927
5°	2906	2934	2950
10°	2879	2931	2964
15°	2832	2919	2972
20°	2772	2899	2979
25°	2694	2869	2975
30°	2604	2833	2971
35°	2510	2791	2981
40°	2403	2757	2990
45°	2289	2722	3014
50°	2190	2697	3038
55°	2073	2676	3085
60°	1964	2664	3118
65°	1835	2644	3143
70°	1686	2604	3186
75°	1521	2535	3072
80°	1305	2244	2314
85°	1050	1325	1050



TEST NUMBER: P387939

CATALOG NUMBER: 22CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.1	3.3
10°-20°	294.8	9.5
20°-30°	442.8	14.2
30°-40°	528.1	17.0
40°-50°	546.0	17.5
50°-60°	502.0	16.1
60°-70°	399.6	12.8
70°-80°	244.1	7.8
80°-90°	53.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	840.7	27.0
0°-40°	1368.7	44.0
0°-60°	2416.7	77.6
0°-90°	3113.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3113.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1088	1088	1088	1088	1088	
5°	1076	1079	1086	1091	1092	102
15°	1017	1028	1048	1062	1067	286
25°	907	930	966	993	1002	417
35°	764	796	850	894	907	477
45°	601	644	715	773	792	465
55°	442	491	570	635	658	395
65°	288	337	415	473	494	285
75°	146	189	244	287	296	156
85°	34	41	43	37	34	39
90°	0	0	0	0	0	



TEST NUMBER: P387939

CATALOG NUMBER: 22CZ2-39HE-SQR-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1087.6	1087.6	1087.6	1087.6	1087.6
2.5°	1081.7	1083.2	1087.6	1090.6	1090.6
5°	1075.8	1078.8	1086.1	1090.6	1092.1
7.5°	1066.9	1071.4	1081.7	1087.6	1089.1
10°	1053.6	1059.5	1072.8	1081.7	1084.7
12.5°	1037.4	1046.2	1062.5	1074.3	1077.3
15°	1016.7	1028.5	1047.7	1062.5	1066.9
17.5°	993.0	1007.8	1031.5	1049.2	1055.1
20°	967.9	982.7	1012.3	1032.9	1040.3
22.5°	938.4	957.6	991.6	1015.2	1021.1
25°	907.3	929.5	966.4	993.0	1001.9
27.5°	873.3	899.9	939.8	972.4	979.7
30°	837.9	866.0	911.8	947.2	956.1
32.5°	800.9	833.4	882.2	922.1	933.9
35°	764.0	796.5	849.7	894.0	907.3
37.5°	721.1	759.6	818.7	864.5	880.7
40°	684.2	721.1	784.7	834.9	851.2
42.5°	642.8	682.7	749.2	803.9	823.1
45°	601.4	644.3	715.2	772.9	792.1
47.5°	563.0	605.9	679.8	740.4	759.6
50°	523.1	567.5	644.3	706.4	725.6
52.5°	480.3	529.0	608.8	670.9	693.1
55°	441.8	490.6	570.4	635.4	657.6
57.5°	401.9	452.2	534.9	597.0	617.7
60°	365.0	413.8	495.0	555.6	579.3
62.5°	325.1	375.3	455.1	514.3	536.4
65°	288.2	336.9	415.2	472.9	493.6
67.5°	251.2	300.0	373.9	428.5	452.2
70°	214.3	263.0	331.0	384.2	404.9
72.5°	181.8	224.6	289.6	338.4	357.6
75°	146.3	189.2	243.8	286.7	295.5
77.5°	113.8	152.2	198.0	217.2	220.2
80°	84.2	113.8	144.8	149.3	149.3
82.5°	56.2	78.3	90.1	91.6	90.1
85°	34.0	41.4	42.9	36.9	34.0
87.5°	11.8	11.8	7.4	4.4	1.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)