

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: METALUX

Report Number: P295028

Luminaire Tested: **24CZ2-40HE-HRP-UNV-L935-CD1-U**

Issue Date: 12/2/2019

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P295028
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 12/2/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-40HE-HRP-UNV-L935-CD1-U
Description: 2'x4' TROFFER LED MODULE, HIGH EFFICIENCY ROUND PERF. LENS
Light Source: (168) 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2646.5 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 30.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P295028

CATALOG NUMBER: 24CZ2-40HE-HRP-UNV-L935-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P295028

CATALOG NUMBER: 24CZ2-40HE-HRP-UNV-L935-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90		92	90	87		89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61		70	64	59		68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51		62	56	50		60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44		56	49	44		54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34		46	39	34		44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30		42	35	30		41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	24		35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1155	1155	1155
5°	1157	1152	1157
10°	1154	1152	1160
15°	1147	1150	1161
20°	1139	1147	1163
25°	1125	1141	1165
30°	1112	1138	1169
35°	1094	1132	1170
40°	1074	1125	1181
45°	1050	1124	1200
50°	1016	1122	1231
55°	980	1131	1276
60°	924	1148	1333
65°	854	1174	1408
70°	745	1216	1499
75°	605	1279	1549
80°	446	1254	1254
85°	343	923	1044



TEST NUMBER: P295028

CATALOG NUMBER: 24CZ2-40HE-HRP-UNV-L935-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.3	3.1
10°-20°	233.6	8.8
20°-30°	355.6	13.4
30°-40°	431.8	16.3
40°-50°	456.2	17.2
50°-60°	430.5	16.3
60°-70°	357.9	13.5
70°-80°	235.5	8.9
80°-90°	64.2	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.5	25.3
0°-40°	1102.3	41.7
0°-60°	1988.9	75.2
0°-90°	2646.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2646.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	859	859	859	859	859	
5°	856	856	853	856	856	81
15°	823	824	825	833	833	232
25°	758	762	769	782	784	350
35°	666	674	689	707	712	417
45°	552	563	590	619	630	425
55°	418	435	482	527	544	372
65°	268	299	369	423	442	265
75°	116	170	246	291	298	125
85°	22	49	60	66	68	27
90°	0	0	0	0	0	



TEST NUMBER: P295028

CATALOG NUMBER: 24CZ2-40HE-HRP-UNV-L935-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	858.7	858.7	858.7	858.7	858.7
2.5°	859.8	858.7	854.2	858.7	858.7
5°	856.4	856.4	853.1	856.4	856.4
7.5°	850.9	850.9	848.7	853.1	853.1
10°	844.3	844.3	843.1	848.7	848.7
12.5°	834.3	835.4	834.3	840.9	840.9
15°	823.2	824.3	825.4	833.2	833.2
17.5°	808.8	811.0	813.2	822.1	823.2
20°	795.5	796.6	801.0	811.0	812.1
22.5°	777.8	781.1	786.6	796.6	799.9
25°	757.8	762.3	768.9	782.2	784.4
27.5°	739.0	742.3	751.2	765.6	770.0
30°	715.7	721.3	732.3	746.8	752.3
32.5°	693.6	699.1	712.4	727.9	732.3
35°	665.9	673.6	689.1	706.9	712.4
37.5°	639.3	647.0	665.9	685.8	692.5
40°	611.6	620.4	640.4	663.7	672.5
42.5°	581.7	593.9	616.0	641.5	651.5
45°	551.8	562.8	590.5	619.3	630.4
47.5°	519.6	532.9	562.8	597.2	610.5
50°	485.3	501.9	536.2	573.9	588.3
52.5°	450.9	469.8	508.5	550.6	566.2
55°	417.7	435.4	482.0	527.4	544.0
57.5°	381.1	403.3	454.3	503.0	519.6
60°	343.5	367.8	426.6	477.5	495.2
62.5°	305.8	333.5	400.0	450.9	469.8
65°	268.1	299.1	368.9	423.2	442.1
67.5°	231.6	265.9	340.1	394.4	413.3
70°	189.5	232.7	309.1	362.3	381.1
72.5°	150.7	200.5	279.2	329.1	345.7
75°	116.3	169.5	246.0	291.4	298.0
77.5°	85.3	138.5	211.6	227.1	228.2
80°	57.6	110.8	161.8	159.5	161.8
82.5°	37.7	83.1	101.9	114.1	115.2
85°	22.2	48.7	59.8	66.5	67.6
87.5°	11.1	16.6	21.1	22.2	24.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)