

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: METALUX

Report Number: P295057

Luminaire Tested: **24CZ2-55-HRP-UNV-L940-CD1-U**

Issue Date: 12/2/2019

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P295057  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)  
Test Lab: INNOVATIONS CENTER(G3)  
Issue Date: 12/2/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-55-HRP-UNV-L940-CD1-U  
Description: 2'x4' TROFFER LED MODULE, HIGH EFFICIENCY ROUND PERF. LENS  
Light Source: (112) 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3697.1 lumens  
Efficiency: N/A  
Efficacy: 73.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 50.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P295057  
CATALOG NUMBER: 24CZ2-55-HRP-UNV-L940-CD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P295057

CATALOG NUMBER: 24CZ2-55-HRP-UNV-L940-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	96	93	96	93	90	92	90	87	89	86	84	82
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	77	73	70	67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36
7	63	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31
8	59	45	36	30	57	44	36	30	43	36	30	42	35	30	41	34	30	28
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25	36	29	24	35	29	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1614	1614	1614
5°	1616	1610	1616
10°	1611	1609	1620
15°	1602	1606	1621
20°	1591	1602	1624
25°	1572	1595	1627
30°	1553	1590	1633
35°	1528	1581	1635
40°	1501	1571	1650
45°	1467	1570	1676
50°	1419	1568	1720
55°	1369	1579	1783
60°	1291	1604	1862
65°	1193	1641	1966
70°	1041	1699	2094
75°	845	1786	2165
80°	624	1751	1751
85°	479	1291	1457



TEST NUMBER: P295057

CATALOG NUMBER: 24CZ2-55-HRP-UNV-L940-CD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.6	3.1
10°-20°	326.3	8.8
20°-30°	496.8	13.4
30°-40°	603.2	16.3
40°-50°	637.3	17.2
50°-60°	601.3	16.3
60°-70°	500.0	13.5
70°-80°	328.9	8.9
80°-90°	89.7	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.7	25.3
0°-40°	1539.9	41.7
0°-60°	2778.5	75.2
0°-90°	3697.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3697.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1200	1200	1200	1200	1200	
5°	1196	1196	1192	1196	1196	114
15°	1150	1152	1153	1164	1164	324
25°	1059	1065	1074	1093	1096	488
35°	930	941	963	988	995	582
45°	771	786	825	865	881	594
55°	584	608	673	737	760	520
65°	375	418	515	591	618	370
75°	162	237	344	407	416	175
85°	31	68	84	93	94	38
90°	0	0	0	0	0	



TEST NUMBER: P295057

CATALOG NUMBER: 24CZ2-55-HRP-UNV-L940-CD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1199.5	1199.5	1199.5	1199.5	1199.5
2.5°	1201.1	1199.5	1193.3	1199.5	1199.5
5°	1196.4	1196.4	1191.8	1196.4	1196.4
7.5°	1188.7	1188.7	1185.6	1191.8	1191.8
10°	1179.4	1179.4	1177.9	1185.6	1185.6
12.5°	1165.5	1167.0	1165.5	1174.8	1174.8
15°	1150.0	1151.5	1153.1	1163.9	1163.9
17.5°	1129.9	1133.0	1136.1	1148.4	1150.0
20°	1111.3	1112.8	1119.0	1133.0	1134.5
22.5°	1086.5	1091.2	1098.9	1112.8	1117.5
25°	1058.7	1064.9	1074.2	1092.7	1095.8
27.5°	1032.4	1037.0	1049.4	1069.5	1075.7
30°	999.9	1007.6	1023.1	1043.2	1050.9
32.5°	968.9	976.6	995.2	1016.9	1023.1
35°	930.2	941.0	962.7	987.5	995.2
37.5°	893.1	903.9	930.2	958.1	967.4
40°	854.4	866.8	894.6	927.1	939.5
42.5°	812.6	829.6	860.6	896.2	910.1
45°	770.8	786.3	825.0	865.2	880.7
47.5°	725.9	744.5	786.3	834.2	852.8
50°	677.9	701.1	749.1	801.7	821.9
52.5°	629.9	656.3	710.4	769.2	790.9
55°	583.5	608.3	673.3	736.7	760.0
57.5°	532.4	563.4	634.6	702.7	725.9
60°	479.8	513.9	595.9	667.1	691.9
62.5°	427.2	465.9	558.7	629.9	656.3
65°	374.6	417.9	515.4	591.2	617.6
67.5°	323.5	371.5	475.2	551.0	577.3
70°	264.7	325.0	431.8	506.1	532.4
72.5°	210.5	280.1	390.0	459.7	482.9
75°	162.5	236.8	343.6	407.1	416.4
77.5°	119.2	193.5	295.6	317.3	318.8
80°	80.5	154.8	226.0	222.9	226.0
82.5°	52.6	116.1	142.4	159.4	161.0
85°	31.0	68.1	83.6	92.9	94.4
87.5°	15.5	23.2	29.4	31.0	34.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)