

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P391224

Luminaire Tested: **24CZ2-30VHE-HRP-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P391224
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-30VHE-HRP-UNV-L935-CD1-SDWPD1-U
Description: 2x4 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND HRP LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2108.4 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P391224

CATALOG NUMBER: 24CZ2-30VHE-HRP-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P391224

CATALOG NUMBER: 24CZ2-30VHE-HRP-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	892	892	892
5°	895	890	894
10°	893	890	894
15°	891	890	896
20°	885	889	898
25°	882	891	901
30°	874	889	903
35°	866	886	907
40°	856	885	918
45°	842	886	939
50°	823	891	967
55°	802	905	1011
60°	768	923	1067
65°	719	955	1132
70°	654	1000	1218
75°	555	1055	1272
80°	438	1062	1029
85°	323	807	905



TEST NUMBER: P391224

CATALOG NUMBER: 24CZ2-30VHE-HRP-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.9	3.0
10°-20°	181.0	8.6
20°-30°	276.8	13.1
30°-40°	338.4	16.0
40°-50°	360.7	17.1
50°-60°	344.8	16.4
60°-70°	292.1	13.9
70°-80°	196.3	9.3
80°-90°	55.4	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.7	24.7
0°-40°	859.1	40.7
0°-60°	1564.6	74.2
0°-90°	2108.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2108.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	663	663	663	663	663	
5°	663	662	659	662	662	63
15°	640	640	639	644	643	180
25°	594	596	600	606	607	274
35°	527	531	540	550	552	330
45°	442	450	465	485	494	341
55°	342	354	386	416	431	305
65°	226	249	300	340	356	224
75°	107	145	203	237	245	114
85°	21	43	52	56	59	26
90°	0	0	0	0	0	



TEST NUMBER: P391224

CATALOG NUMBER: 24CZ2-30VHE-HRP-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	663.0	663.0	663.0	663.0	663.0
2.5°	664.1	664.1	660.9	663.0	663.0
5°	663.0	662.0	658.8	662.0	662.0
7.5°	659.9	658.8	656.8	659.9	658.8
10°	653.6	653.6	651.5	654.7	654.7
12.5°	648.4	647.3	646.3	650.5	649.4
15°	640.0	640.0	639.0	644.2	643.2
17.5°	629.6	630.6	631.7	635.8	636.9
20°	618.1	620.2	621.2	627.5	627.5
22.5°	607.6	608.7	610.7	617.0	617.0
25°	594.0	596.1	600.3	605.5	606.6
27.5°	580.4	581.5	586.7	594.0	595.1
30°	562.6	565.8	572.0	580.4	581.5
32.5°	546.9	550.1	557.4	565.8	567.9
35°	527.1	531.3	539.6	550.1	552.2
37.5°	509.3	512.4	522.9	534.4	537.5
40°	487.3	493.6	504.1	517.7	522.9
42.5°	465.4	471.7	484.2	502.0	508.3
45°	442.4	449.7	465.4	485.2	493.6
47.5°	419.4	427.7	445.5	468.5	477.9
50°	393.2	403.7	425.6	451.8	462.2
52.5°	368.1	380.7	404.7	434.0	447.6
55°	342.0	354.5	385.9	416.2	430.9
57.5°	312.7	329.4	363.9	398.4	414.1
60°	285.5	301.2	343.0	380.7	396.4
62.5°	256.2	277.1	322.1	361.8	377.5
65°	225.9	248.9	300.1	339.9	355.6
67.5°	198.7	223.8	278.2	317.9	333.6
70°	166.3	197.7	254.1	293.9	309.6
72.5°	136.0	170.5	229.0	267.7	282.4
75°	106.7	145.4	202.9	237.4	244.7
77.5°	79.5	120.3	175.7	190.3	185.1
80°	56.5	96.2	137.0	129.7	132.8
82.5°	36.6	73.2	84.7	96.2	99.4
85°	20.9	42.9	52.3	56.5	58.6
87.5°	9.4	15.7	20.9	20.9	19.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)