

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P391321

Luminaire Tested: **24CZ2-40VHE-HRP-UNV-L935-CD1-SWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P391321  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)  
Test Lab: INNOVATIONS CENTER(G3)  
Issue Date: 2/28/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-40VHE-HRP-UNV-L935-CD1-SWPD1-U  
Description: 2x4 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND HRP LENS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2864.8 lumens  
Efficiency: N/A  
Efficacy: 109.3 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 26.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P391321

CATALOG NUMBER: 24CZ2-40VHE-HRP-UNV-L935-CD1-SWPD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P391321

CATALOG NUMBER: 24CZ2-40VHE-HRP-UNV-L935-CD1-SWPD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1212	1212	1212
5°	1217	1209	1215
10°	1213	1210	1215
15°	1211	1209	1217
20°	1202	1209	1221
25°	1198	1211	1224
30°	1188	1208	1228
35°	1176	1204	1232
40°	1163	1203	1248
45°	1144	1203	1276
50°	1118	1211	1315
55°	1090	1230	1373
60°	1044	1254	1449
65°	977	1298	1538
70°	889	1358	1655
75°	753	1433	1729
80°	594	1442	1399
85°	438	1096	1229



TEST NUMBER: P391321

CATALOG NUMBER: 24CZ2-40VHE-HRP-UNV-L935-CD1-SWPD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	85.5	3.0
10°-20°	245.9	8.6
20°-30°	376.1	13.1
30°-40°	459.8	16.0
40°-50°	490.0	17.1
50°-60°	468.5	16.4
60°-70°	396.9	13.9
70°-80°	266.8	9.3
80°-90°	75.2	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	707.5	24.7
0°-40°	1167.3	40.7
0°-60°	2125.9	74.2
0°-90°	2864.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2864.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	901	901	901	901	901	
5°	901	900	895	900	900	86
15°	870	870	868	875	874	245
25°	807	810	816	823	824	372
35°	716	722	733	747	750	449
45°	601	611	632	659	671	464
55°	465	482	524	566	585	414
65°	307	338	408	462	483	305
75°	145	198	276	323	332	155
85°	28	58	71	77	80	35
90°	0	0	0	0	0	



TEST NUMBER: P391321

CATALOG NUMBER: 24CZ2-40VHE-HRP-UNV-L935-CD1-SWPD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	900.9	900.9	900.9	900.9	900.9
2.5°	902.3	902.3	898.1	900.9	900.9
5°	900.9	899.5	895.2	899.5	899.5
7.5°	896.6	895.2	892.4	896.6	895.2
10°	888.1	888.1	885.3	889.5	889.5
12.5°	881.0	879.6	878.2	883.8	882.4
15°	869.6	869.6	868.2	875.3	873.9
17.5°	855.4	856.8	858.3	864.0	865.4
20°	839.8	842.6	844.1	852.6	852.6
22.5°	825.6	827.0	829.8	838.4	838.4
25°	807.1	810.0	815.6	822.7	824.2
27.5°	788.6	790.1	797.2	807.1	808.5
30°	764.5	768.7	777.3	788.6	790.1
32.5°	743.2	747.4	757.4	768.7	771.6
35°	716.2	721.9	733.2	747.4	750.3
37.5°	692.0	696.3	710.5	726.1	730.4
40°	662.2	670.7	684.9	703.4	710.5
42.5°	632.3	640.9	657.9	682.1	690.6
45°	601.1	611.0	632.3	659.3	670.7
47.5°	569.8	581.2	605.3	636.6	649.4
50°	534.3	548.5	578.3	613.9	628.1
52.5°	500.2	517.2	549.9	589.7	608.2
55°	464.7	481.7	524.3	565.5	585.4
57.5°	424.9	447.6	494.5	541.4	562.7
60°	387.9	409.2	466.1	517.2	538.5
62.5°	348.1	376.6	437.7	491.7	513.0
65°	306.9	338.2	407.8	461.8	483.1
67.5°	270.0	304.1	378.0	432.0	453.3
70°	225.9	268.6	345.3	399.3	420.6
72.5°	184.7	231.6	311.2	363.8	383.7
75°	144.9	197.5	275.7	322.6	332.5
77.5°	108.0	163.4	238.7	258.6	251.5
80°	76.7	130.7	186.1	176.2	180.5
82.5°	49.7	99.5	115.1	130.7	135.0
85°	28.4	58.3	71.0	76.7	79.6
87.5°	12.8	21.3	28.4	28.4	27.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)