

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: METALUX

Report Number: P391324

Luminaire Tested: **24CZ2-40VHE-HRP-UNV-L940-CD1-SWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P391324  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)  
Test Lab: INNOVATIONS CENTER(G3)  
Issue Date: 2/28/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-40VHE-HRP-UNV-L940-CD1-SWPD1-U  
Description: 2x4 CRUZE LED TROFFER WITH 4000K, 90 LEDS, AND HRP LENS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2894.5 lumens  
Efficiency: N/A  
Efficacy: 110.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P391324

CATALOG NUMBER: 24CZ2-40VHE-HRP-UNV-L940-CD1-SWPD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P391324

CATALOG NUMBER: 24CZ2-40VHE-HRP-UNV-L940-CD1-SWPD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	68	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1225	1225	1225
5°	1229	1222	1227
10°	1226	1222	1228
15°	1224	1222	1230
20°	1215	1221	1233
25°	1211	1223	1236
30°	1200	1220	1240
35°	1189	1217	1245
40°	1175	1215	1261
45°	1156	1216	1290
50°	1130	1223	1328
55°	1101	1243	1388
60°	1055	1267	1464
65°	987	1312	1554
70°	898	1373	1672
75°	761	1448	1747
80°	600	1457	1413
85°	443	1108	1241



TEST NUMBER: P391324

CATALOG NUMBER: 24CZ2-40VHE-HRP-UNV-L940-CD1-SWPD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.3	3.0
10°-20°	248.5	8.6
20°-30°	380.0	13.1
30°-40°	464.6	16.0
40°-50°	495.1	17.1
50°-60°	473.4	16.4
60°-70°	401.0	13.9
70°-80°	269.5	9.3
80°-90°	76.0	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	714.9	24.7
0°-40°	1179.4	40.7
0°-60°	2147.9	74.2
0°-90°	2894.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2894.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	910	910	910	910	910	
5°	910	909	904	909	909	86
15°	879	879	877	884	883	248
25°	816	818	824	831	833	376
35°	724	729	741	755	758	453
45°	607	617	639	666	678	468
55°	470	487	530	571	592	418
65°	310	342	412	467	488	308
75°	146	200	278	326	336	157
85°	29	59	72	78	80	36
90°	0	0	0	0	0	



TEST NUMBER: P391324

CATALOG NUMBER: 24CZ2-40VHE-HRP-UNV-L940-CD1-SWPD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	910.2	910.2	910.2	910.2	910.2
2.5°	911.7	911.7	907.4	910.2	910.2
5°	910.2	908.8	904.5	908.8	908.8
7.5°	905.9	904.5	901.6	905.9	904.5
10°	897.3	897.3	894.4	898.8	898.8
12.5°	890.1	888.7	887.3	893.0	891.6
15°	878.7	878.7	877.2	884.4	883.0
17.5°	864.3	865.7	867.2	872.9	874.3
20°	848.5	851.4	852.8	861.4	861.4
22.5°	834.1	835.6	838.5	847.1	847.1
25°	815.5	818.4	824.1	831.3	832.7
27.5°	796.8	798.3	805.4	815.5	816.9
30°	772.4	776.7	785.3	796.8	798.3
32.5°	750.9	755.2	765.2	776.7	779.6
35°	723.6	729.3	740.8	755.2	758.1
37.5°	699.2	703.5	717.9	733.6	738.0
40°	669.0	677.7	692.0	710.7	717.9
42.5°	638.9	647.5	664.7	689.1	697.8
45°	607.3	617.4	638.9	666.2	677.7
47.5°	575.7	587.2	611.6	643.2	656.1
50°	539.8	554.2	584.3	620.2	634.6
52.5°	505.4	522.6	555.6	595.8	614.5
55°	469.5	486.7	529.8	571.4	591.5
57.5°	429.3	452.2	499.6	547.0	568.5
60°	391.9	413.5	470.9	522.6	544.1
62.5°	351.7	380.5	442.2	496.8	518.3
65°	310.1	341.7	412.0	466.6	488.1
67.5°	272.8	307.2	381.9	436.5	458.0
70°	228.3	271.3	348.9	403.4	425.0
72.5°	186.6	234.0	314.4	367.5	387.6
75°	146.4	199.6	278.5	325.9	336.0
77.5°	109.1	165.1	241.2	261.3	254.1
80°	77.5	132.1	188.1	178.0	182.3
82.5°	50.2	100.5	116.3	132.1	136.4
85°	28.7	58.9	71.8	77.5	80.4
87.5°	12.9	21.5	28.7	28.7	27.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)