

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P274799

Luminaire Tested: **24CZ2-45HE-RDP-UNV-L930-CD1-U**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P274799
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-45HE-RDP-UNV-L930-CD1-U
Description: 2'x4' TROFFER LED MODULE,SMOOTH LENS WITH INSERT, 90CRI
Light Source: (168) 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2542.0 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 35.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274799

CATALOG NUMBER: 24CZ2-45HE-RDP-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P274799

CATALOG NUMBER: 24CZ2-45HE-RDP-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89		92	89	87		88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72		80	75	71		77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60		70	64	59		67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51		62	55	50		59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43		55	48	43		53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38		50	43	37		48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33		45	38	33		44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30		41	34	29		40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27		38	31	26		37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24		35	29	24		34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1076	1076	1076
5°	1080	1073	1078
10°	1077	1073	1078
15°	1075	1073	1080
20°	1067	1072	1083
25°	1063	1074	1086
30°	1054	1072	1089
35°	1044	1069	1093
40°	1032	1067	1107
45°	1015	1068	1132
50°	992	1074	1167
55°	967	1091	1219
60°	926	1113	1286
65°	867	1152	1365
70°	789	1205	1468
75°	669	1272	1534
80°	528	1280	1241
85°	389	973	1090



TEST NUMBER: P274799

CATALOG NUMBER: 24CZ2-45HE-RDP-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.8	3.0
10°-20°	218.2	8.6
20°-30°	333.7	13.1
30°-40°	408.0	16.0
40°-50°	434.8	17.1
50°-60°	415.8	16.4
60°-70°	352.2	13.9
70°-80°	236.7	9.3
80°-90°	66.8	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	627.8	24.7
0°-40°	1035.8	40.7
0°-60°	1886.3	74.2
0°-90°	2542.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2542.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	799	799	799	799	799	
5°	799	798	794	798	798	76
15°	772	772	770	777	775	218
25°	716	719	724	730	731	330
35°	636	640	651	663	666	398
45°	533	542	561	585	595	411
55°	412	427	465	502	520	367
65°	272	300	362	410	429	270
75°	129	175	245	286	295	138
85°	25	52	63	68	71	31
90°	0	0	0	0	0	



TEST NUMBER: P274799

CATALOG NUMBER: 24CZ2-45HE-RDP-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	799.4	799.4	799.4	799.4	799.4
2.5°	800.6	800.6	796.9	799.4	799.4
5°	799.4	798.1	794.3	798.1	798.1
7.5°	795.6	794.3	791.8	795.6	794.3
10°	788.0	788.0	785.5	789.3	789.3
12.5°	781.7	780.5	779.2	784.3	783.0
15°	771.6	771.6	770.4	776.7	775.4
17.5°	759.0	760.3	761.6	766.6	767.9
20°	745.2	747.7	749.0	756.5	756.5
22.5°	732.6	733.8	736.3	743.9	743.9
25°	716.2	718.7	723.7	730.0	731.3
27.5°	699.8	701.0	707.3	716.2	717.4
30°	678.3	682.1	689.7	699.8	701.0
32.5°	659.4	663.2	672.0	682.1	684.6
35°	635.5	640.5	650.6	663.2	665.7
37.5°	614.0	617.8	630.4	644.3	648.1
40°	587.6	595.1	607.7	624.1	630.4
42.5°	561.1	568.6	583.8	605.2	612.8
45°	533.3	542.2	561.1	585.0	595.1
47.5°	505.6	515.7	537.1	564.9	576.2
50°	474.1	486.7	513.2	544.7	557.3
52.5°	443.8	459.0	488.0	523.3	539.6
55°	412.3	427.4	465.3	501.8	519.5
57.5°	377.0	397.2	438.8	480.4	499.3
60°	344.2	363.1	413.6	459.0	477.9
62.5°	308.9	334.1	388.3	436.3	455.2
65°	272.3	300.1	361.9	409.8	428.7
67.5°	239.6	269.8	335.4	383.3	402.2
70°	200.5	238.3	306.4	354.3	373.2
72.5°	163.9	205.5	276.1	322.8	340.4
75°	128.6	175.3	244.6	286.2	295.0
77.5°	95.8	145.0	211.8	229.5	223.2
80°	68.1	116.0	165.2	156.3	160.1
82.5°	44.1	88.3	102.1	116.0	119.8
85°	25.2	51.7	63.0	68.1	70.6
87.5°	11.3	18.9	25.2	25.2	24.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)