

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P391559

Luminaire Tested: **24CZ2-65VHE-HRP-UNV-L930-CD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P391559
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-65VHE-HRP-UNV-L930-CD1-U
Description: 2x4 CRUZE LED TROFFER WITH 3000K, 90 LEDS, AND HRP LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4597.8 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 42.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P391559

CATALOG NUMBER: 24CZ2-65VHE-HRP-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P391559

CATALOG NUMBER: 24CZ2-65VHE-HRP-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	88	86	84	82
2	97	89	81	75	95	87	80	74	83	77	72	80	75	71	77	73	69	67
3	88	77	68	62	86	76	67	61	72	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	51	64	57	51	62	55	50	59	54	49	47
5	74	60	51	44	72	59	51	44	57	49	43	55	48	43	53	47	42	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1945	1945	1945
5°	1953	1941	1950
10°	1947	1941	1950
15°	1944	1941	1954
20°	1930	1940	1959
25°	1923	1943	1964
30°	1906	1938	1970
35°	1888	1933	1978
40°	1867	1931	2003
45°	1836	1931	2048
50°	1795	1943	2110
55°	1749	1974	2204
60°	1675	2013	2326
65°	1568	2084	2469
70°	1426	2180	2655
75°	1209	2300	2774
80°	955	2315	2244
85°	704	1760	1971



TEST NUMBER: P391559

CATALOG NUMBER: 24CZ2-65VHE-HRP-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	3.0
10°-20°	394.7	8.6
20°-30°	603.6	13.1
30°-40°	737.9	16.0
40°-50°	786.5	17.1
50°-60°	752.0	16.4
60°-70°	637.0	13.9
70°-80°	428.1	9.3
80°-90°	120.8	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1135.5	24.7
0°-40°	1873.4	40.7
0°-60°	3411.9	74.2
0°-90°	4597.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4597.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1446	1446	1446	1446	1446	
5°	1446	1444	1437	1444	1444	137
15°	1396	1396	1393	1405	1402	394
25°	1295	1300	1309	1320	1323	597
35°	1149	1158	1177	1200	1204	720
45°	965	981	1015	1058	1076	744
55°	746	773	842	908	940	664
65°	493	543	654	741	775	489
75°	233	317	442	518	534	249
85°	46	94	114	123	128	56
90°	0	0	0	0	0	



TEST NUMBER: P391559

CATALOG NUMBER: 24CZ2-65VHE-HRP-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1445.9	1445.9	1445.9	1445.9	1445.9
2.5°	1448.2	1448.2	1441.3	1445.9	1445.9
5°	1445.9	1443.6	1436.8	1443.6	1443.6
7.5°	1439.0	1436.8	1432.2	1439.0	1436.8
10°	1425.4	1425.4	1420.8	1427.6	1427.6
12.5°	1413.9	1411.7	1409.4	1418.5	1416.2
15°	1395.7	1395.7	1393.4	1404.8	1402.5
17.5°	1372.9	1375.2	1377.5	1386.6	1388.9
20°	1347.8	1352.4	1354.7	1368.3	1368.3
22.5°	1325.0	1327.3	1331.8	1345.5	1345.5
25°	1295.4	1299.9	1309.0	1320.4	1322.7
27.5°	1265.7	1268.0	1279.4	1295.4	1297.6
30°	1226.9	1233.8	1247.5	1265.7	1268.0
32.5°	1192.7	1199.6	1215.5	1233.8	1238.3
35°	1149.4	1158.5	1176.8	1199.6	1204.1
37.5°	1110.6	1117.5	1140.3	1165.4	1172.2
40°	1062.7	1076.4	1099.2	1128.9	1140.3
42.5°	1014.9	1028.5	1055.9	1094.7	1108.4
45°	964.7	980.6	1014.9	1058.2	1076.4
47.5°	914.5	932.8	971.5	1021.7	1042.2
50°	857.5	880.3	928.2	985.2	1008.0
52.5°	802.8	830.1	882.6	946.4	976.1
55°	745.7	773.1	841.5	907.7	939.6
57.5°	681.9	718.4	793.6	868.9	903.1
60°	622.6	656.8	748.0	830.1	864.3
62.5°	558.7	604.3	702.4	789.1	823.3
65°	492.6	542.8	654.5	741.2	775.4
67.5°	433.3	488.0	606.6	693.3	727.5
70°	362.6	431.0	554.2	640.8	675.0
72.5°	296.5	371.7	499.4	583.8	615.8
75°	232.6	317.0	442.4	517.7	533.7
77.5°	173.3	262.3	383.1	415.1	403.7
80°	123.2	209.8	298.8	282.8	289.6
82.5°	79.8	159.6	184.7	209.8	216.7
85°	45.6	93.5	114.0	123.2	127.7
87.5°	20.5	34.2	45.6	45.6	43.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)