

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: METALUX

Report Number: P389712

Luminaire Tested: **24CZ2-35VHE-S-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P389712  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)  
Test Lab: INNOVATIONS CENTER(G3)  
Issue Date: 2/28/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-35VHE-S-UNV-L935-CD1-SDWPD1-U  
Description: 2x4 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND SMOOTH LENS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3056.2 lumens  
Efficiency: N/A  
Efficacy: 134.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 22.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P389712

CATALOG NUMBER: 24CZ2-35VHE-S-UNV-L935-CD1-SDWPD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P389712

CATALOG NUMBER: 24CZ2-35VHE-S-UNV-L935-CD1-SDWPD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1445	1445	1445
5°	1444	1440	1449
10°	1438	1438	1448
15°	1424	1431	1445
20°	1405	1419	1441
25°	1379	1405	1432
30°	1348	1389	1421
35°	1319	1366	1410
40°	1274	1344	1393
45°	1232	1317	1378
50°	1185	1292	1361
55°	1132	1268	1348
60°	1079	1249	1345
65°	1011	1227	1354
70°	935	1234	1390
75°	837	1256	1469
80°	677	1331	1437
85°	509	1169	1139



TEST NUMBER: P389712

CATALOG NUMBER: 24CZ2-35VHE-S-UNV-L935-CD1-SDWPD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.6	3.3
10°-20°	290.4	9.5
20°-30°	436.6	14.3
30°-40°	520.0	17.0
40°-50°	532.3	17.4
50°-60°	479.2	15.7
60°-70°	376.3	12.3
70°-80°	244.2	8.0
80°-90°	75.5	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	828.7	27.1
0°-40°	1348.7	44.1
0°-60°	2360.1	77.2
0°-90°	3056.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3056.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1074	1074	1074	1074	1074	
5°	1069	1071	1066	1072	1073	102
15°	1022	1025	1027	1036	1038	288
25°	929	937	946	962	965	428
35°	803	812	832	852	858	501
45°	648	663	692	718	724	499
55°	482	504	541	569	575	433
65°	317	342	385	417	425	316
75°	161	192	242	275	282	170
85°	33	61	76	74	74	40
90°	0	0	0	0	0	



TEST NUMBER: P389712

CATALOG NUMBER: 24CZ2-35VHE-S-UNV-L935-CD1-SDWPD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1073.7	1073.7	1073.7	1073.7	1073.7
2.5°	1074.6	1074.6	1069.8	1074.6	1075.6
5°	1068.8	1070.8	1065.9	1071.7	1072.7
7.5°	1063.0	1063.0	1060.1	1065.9	1066.9
10°	1052.3	1053.3	1052.3	1059.1	1060.1
12.5°	1038.7	1040.7	1041.6	1048.4	1049.4
15°	1022.2	1025.1	1027.1	1035.8	1037.7
17.5°	1003.8	1006.7	1011.5	1021.2	1023.2
20°	981.4	985.3	991.1	1003.8	1006.7
22.5°	957.2	961.1	970.8	982.4	987.3
25°	929.0	936.8	946.5	962.0	964.9
27.5°	900.9	907.7	920.3	936.8	940.7
30°	867.9	878.5	894.1	910.6	914.5
32.5°	835.8	846.5	864.9	882.4	887.3
35°	802.8	812.5	831.9	852.3	858.2
37.5°	765.0	777.6	798.9	819.3	825.1
40°	725.2	740.7	765.0	786.3	793.1
42.5°	687.3	703.8	728.1	751.4	759.1
45°	647.5	663.0	692.2	718.4	724.2
47.5°	606.7	624.2	655.3	681.5	691.2
50°	566.0	584.4	617.4	644.6	650.4
52.5°	525.2	544.6	579.5	608.7	611.6
55°	482.5	503.8	540.7	568.9	574.7
57.5°	443.6	462.1	501.9	531.0	537.8
60°	400.9	421.3	464.0	491.2	499.9
62.5°	360.2	381.5	426.2	453.3	461.1
65°	317.4	341.7	385.4	417.4	425.2
67.5°	280.6	303.8	350.4	381.5	389.3
70°	237.8	264.0	313.6	345.6	353.4
72.5°	200.9	228.1	277.6	308.7	320.4
75°	161.1	192.2	241.7	274.7	282.5
77.5°	122.3	158.2	208.7	234.0	234.0
80°	87.4	125.2	171.8	183.5	185.4
82.5°	57.3	94.2	127.2	126.2	126.2
85°	33.0	61.2	75.7	73.8	73.8
87.5°	12.6	25.2	27.2	27.2	26.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)