

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P389743

Luminaire Tested: **24CZ2-40VHE-S-UNV-L950-CD1-SWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P389743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-40VHE-S-UNV-L950-CD1-SWPD1-U
Description: 2x4 CRUZE LED TROFFER WITH 5000K, 90 LEDS, AND SMOOTH LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3803.1 lumens
Efficiency: N/A
Efficacy: 145.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P389743

CATALOG NUMBER: 24CZ2-40VHE-S-UNV-L950-CD1-SWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P389743

CATALOG NUMBER: 24CZ2-40VHE-S-UNV-L950-CD1-SWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83					83			
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69					69			
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58					58			
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49					49			
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42					42			
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37					37			
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33					33			
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29					29			
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26					26			
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24					24			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1798	1798	1798
5°	1796	1791	1803
10°	1789	1789	1802
15°	1772	1780	1799
20°	1749	1766	1794
25°	1716	1749	1783
30°	1678	1729	1768
35°	1641	1701	1754
40°	1585	1672	1733
45°	1533	1639	1715
50°	1474	1608	1694
55°	1408	1578	1677
60°	1343	1554	1674
65°	1258	1527	1684
70°	1164	1535	1730
75°	1042	1564	1827
80°	842	1657	1788
85°	634	1454	1417



TEST NUMBER: P389743

CATALOG NUMBER: 24CZ2-40VHE-S-UNV-L950-CD1-SWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.5	3.3
10°-20°	361.4	9.5
20°-30°	543.3	14.3
30°-40°	647.1	17.0
40°-50°	662.3	17.4
50°-60°	596.3	15.7
60°-70°	468.3	12.3
70°-80°	303.9	8.0
80°-90°	94.0	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1031.2	27.1
0°-40°	1678.3	44.1
0°-60°	2936.9	77.2
0°-90°	3803.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3803.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1336	1336	1336	1336	1336	
5°	1330	1332	1326	1334	1335	126
15°	1272	1276	1278	1289	1291	359
25°	1156	1166	1178	1197	1201	533
35°	999	1011	1035	1061	1068	623
45°	806	825	861	894	901	621
55°	600	627	673	708	715	538
65°	395	425	480	519	529	393
75°	200	239	301	342	352	212
85°	41	76	94	92	92	50
90°	0	0	0	0	0	



TEST NUMBER: P389743

CATALOG NUMBER: 24CZ2-40VHE-S-UNV-L950-CD1-SWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1336.1	1336.1	1336.1	1336.1	1336.1
2.5°	1337.3	1337.3	1331.2	1337.3	1338.5
5°	1330.0	1332.4	1326.4	1333.6	1334.8
7.5°	1322.8	1322.8	1319.1	1326.4	1327.6
10°	1309.5	1310.7	1309.5	1317.9	1319.1
12.5°	1292.6	1295.0	1296.2	1304.6	1305.9
15°	1272.0	1275.7	1278.1	1288.9	1291.4
17.5°	1249.1	1252.7	1258.7	1270.8	1273.2
20°	1221.3	1226.1	1233.4	1249.1	1252.7
22.5°	1191.1	1195.9	1208.0	1222.5	1228.5
25°	1156.1	1165.7	1177.8	1197.1	1200.8
27.5°	1121.0	1129.5	1145.2	1165.7	1170.6
30°	1080.0	1093.2	1112.6	1133.1	1137.9
32.5°	1040.1	1053.4	1076.3	1098.1	1104.1
35°	999.0	1011.1	1035.3	1060.6	1067.9
37.5°	951.9	967.6	994.2	1019.6	1026.8
40°	902.4	921.7	951.9	978.5	986.9
42.5°	855.3	875.8	906.0	935.0	944.7
45°	805.7	825.1	861.3	893.9	901.2
47.5°	755.0	776.7	815.4	848.0	860.1
50°	704.3	727.2	768.3	802.1	809.4
52.5°	653.5	677.7	721.2	757.4	761.0
55°	600.4	627.0	672.9	707.9	715.1
57.5°	552.1	575.0	624.5	660.8	669.2
60°	498.9	524.3	577.4	611.3	622.1
62.5°	448.2	474.7	530.3	564.1	573.8
65°	395.0	425.2	479.6	519.4	529.1
67.5°	349.1	378.1	436.1	474.7	484.4
70°	296.0	328.6	390.2	430.0	439.7
72.5°	250.1	283.9	345.5	384.1	398.6
75°	200.5	239.2	300.8	341.9	351.5
77.5°	152.2	196.9	259.7	291.1	291.1
80°	108.7	155.8	213.8	228.3	230.7
82.5°	71.3	117.2	158.2	157.0	157.0
85°	41.1	76.1	94.2	91.8	91.8
87.5°	15.7	31.4	33.8	33.8	32.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)