

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P389760

Luminaire Tested: **24CZ2-45VHE-S-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P389760
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATIONS CENTER(G3)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-45VHE-S-UNV-L935-CD1-SDWPD1-U
Description: 2x4 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND SMOOTH LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3951.6 lumens
Efficiency: N/A
Efficacy: 133.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 29.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P389760

CATALOG NUMBER: 24CZ2-45VHE-S-UNV-L935-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P389760

CATALOG NUMBER: 24CZ2-45VHE-S-UNV-L935-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1868	1868	1868
5°	1866	1861	1873
10°	1859	1859	1873
15°	1841	1850	1869
20°	1817	1835	1864
25°	1783	1817	1852
30°	1743	1796	1837
35°	1705	1767	1823
40°	1647	1737	1801
45°	1593	1703	1782
50°	1532	1671	1760
55°	1463	1640	1743
60°	1395	1615	1739
65°	1307	1586	1750
70°	1210	1595	1797
75°	1083	1625	1899
80°	876	1722	1857
85°	659	1511	1473



TEST NUMBER: P389760

CATALOG NUMBER: 24CZ2-45VHE-S-UNV-L935-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.4	3.3
10°-20°	375.5	9.5
20°-30°	564.5	14.3
30°-40°	672.4	17.0
40°-50°	688.2	17.4
50°-60°	619.6	15.7
60°-70°	486.6	12.3
70°-80°	315.8	8.0
80°-90°	97.7	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1071.4	27.1
0°-40°	1743.9	44.1
0°-60°	3051.6	77.2
0°-90°	3951.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3951.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1382	1384	1378	1386	1387	131
15°	1322	1326	1328	1339	1342	373
25°	1201	1211	1224	1244	1248	553
35°	1038	1051	1076	1102	1110	648
45°	837	857	895	929	936	645
55°	624	651	699	736	743	559
65°	410	442	498	540	550	409
75°	208	248	312	355	365	221
85°	43	79	98	95	95	52
90°	0	0	0	0	0	



TEST NUMBER: P389760

CATALOG NUMBER: 24CZ2-45VHE-S-UNV-L935-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.2	1388.2	1388.2	1388.2	1388.2
2.5°	1389.5	1389.5	1383.2	1389.5	1390.7
5°	1381.9	1384.5	1378.2	1385.7	1387.0
7.5°	1374.4	1374.4	1370.7	1378.2	1379.4
10°	1360.6	1361.9	1360.6	1369.4	1370.7
12.5°	1343.0	1345.5	1346.8	1355.6	1356.8
15°	1321.7	1325.5	1328.0	1339.3	1341.8
17.5°	1297.9	1301.6	1307.9	1320.4	1323.0
20°	1269.0	1274.0	1281.5	1297.9	1301.6
22.5°	1237.6	1242.6	1255.2	1270.2	1276.5
25°	1201.2	1211.2	1223.8	1243.9	1247.6
27.5°	1164.8	1173.6	1189.9	1211.2	1216.3
30°	1122.1	1135.9	1156.0	1177.4	1182.4
32.5°	1080.7	1094.5	1118.4	1141.0	1147.2
35°	1038.0	1050.6	1075.7	1102.0	1109.6
37.5°	989.1	1005.4	1033.0	1059.4	1066.9
40°	937.6	957.7	989.1	1016.7	1025.5
42.5°	888.7	910.0	941.4	971.5	981.5
45°	837.2	857.3	894.9	928.8	936.4
47.5°	784.5	807.1	847.2	881.1	893.7
50°	731.8	755.6	798.3	833.4	841.0
52.5°	679.0	704.2	749.3	787.0	790.8
55°	623.8	651.4	699.1	735.5	743.1
57.5°	573.6	597.5	648.9	686.6	695.4
60°	518.4	544.7	600.0	635.1	646.4
62.5°	465.7	493.3	551.0	586.2	596.2
65°	410.4	441.8	498.3	539.7	549.8
67.5°	362.7	392.9	453.1	493.3	503.3
70°	307.5	341.4	405.4	446.8	456.9
72.5°	259.8	295.0	359.0	399.1	414.2
75°	208.4	248.5	312.5	355.2	365.3
77.5°	158.2	204.6	269.9	302.5	302.5
80°	113.0	161.9	222.2	237.2	239.7
82.5°	74.1	121.8	164.4	163.2	163.2
85°	42.7	79.1	97.9	95.4	95.4
87.5°	16.3	32.6	35.1	35.1	33.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)