

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P389764

Luminaire Tested: **24CZ2-45VHE-S-UNV-L940-CD1-SWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P389764  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)  
Test Lab: INNOVATIONS CENTER(G3)  
Issue Date: 2/28/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-45VHE-S-UNV-L940-CD1-SWPD1-U  
Description: 2x4 CRUZE LED TROFFER WITH 4000K, 90 LEDS, AND SMOOTH LENS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4041.2 lumens  
Efficiency: N/A  
Efficacy: 136.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 29.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P389764

CATALOG NUMBER: 24CZ2-45VHE-S-UNV-L940-CD1-SWPD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P389764

CATALOG NUMBER: 24CZ2-45VHE-S-UNV-L940-CD1-SWPD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1910	1910	1910
5°	1909	1904	1916
10°	1901	1901	1915
15°	1883	1892	1911
20°	1858	1877	1906
25°	1824	1858	1894
30°	1783	1837	1879
35°	1744	1807	1864
40°	1684	1777	1842
45°	1629	1741	1822
50°	1567	1709	1800
55°	1497	1677	1783
60°	1426	1651	1779
65°	1336	1622	1790
70°	1237	1631	1838
75°	1108	1661	1942
80°	895	1760	1900
85°	673	1545	1507



TEST NUMBER: P389764

CATALOG NUMBER: 24CZ2-45VHE-S-UNV-L940-CD1-SWPD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.4	3.3
10°-20°	384.0	9.5
20°-30°	577.3	14.3
30°-40°	687.6	17.0
40°-50°	703.8	17.4
50°-60°	633.6	15.7
60°-70°	497.6	12.3
70°-80°	322.9	8.0
80°-90°	99.9	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1095.7	27.1
0°-40°	1783.4	44.1
0°-60°	3120.8	77.2
0°-90°	4041.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4041.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1420	1420	1420	1420	1420	
5°	1413	1416	1409	1417	1418	134
15°	1352	1356	1358	1370	1372	381
25°	1228	1239	1252	1272	1276	566
35°	1062	1074	1100	1127	1135	662
45°	856	877	915	950	958	660
55°	638	666	715	752	760	572
65°	420	452	510	552	562	418
75°	213	254	320	363	374	225
85°	44	81	100	98	98	53
90°	0	0	0	0	0	



TEST NUMBER: P389764

CATALOG NUMBER: 24CZ2-45VHE-S-UNV-L940-CD1-SWPD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1419.7	1419.7	1419.7	1419.7	1419.7
2.5°	1421.0	1421.0	1414.6	1421.0	1422.3
5°	1413.3	1415.8	1409.4	1417.1	1418.4
7.5°	1405.6	1405.6	1401.7	1409.4	1410.7
10°	1391.5	1392.7	1391.5	1400.4	1401.7
12.5°	1373.5	1376.1	1377.3	1386.3	1387.6
15°	1351.7	1355.5	1358.1	1369.6	1372.2
17.5°	1327.3	1331.1	1337.5	1350.4	1353.0
20°	1297.8	1302.9	1310.6	1327.3	1331.1
22.5°	1265.7	1270.8	1283.6	1299.0	1305.5
25°	1228.4	1238.7	1251.5	1272.1	1275.9
27.5°	1191.2	1200.2	1216.9	1238.7	1243.8
30°	1147.6	1161.7	1182.2	1204.0	1209.2
32.5°	1105.2	1119.3	1143.7	1166.8	1173.2
35°	1061.6	1074.4	1100.1	1127.0	1134.7
37.5°	1011.5	1028.2	1056.4	1083.4	1091.1
40°	958.9	979.4	1011.5	1039.7	1048.7
42.5°	908.8	930.6	962.7	993.5	1003.8
45°	856.2	876.7	915.2	949.9	957.6
47.5°	802.3	825.4	866.5	901.1	913.9
50°	748.4	772.7	816.4	852.3	860.0
52.5°	694.4	720.1	766.3	804.8	808.7
55°	638.0	666.2	715.0	752.2	759.9
57.5°	586.6	611.0	663.6	702.1	711.1
60°	530.1	557.1	613.6	649.5	661.1
62.5°	476.2	504.5	563.5	599.5	609.7
65°	419.7	451.8	509.6	552.0	562.2
67.5°	371.0	401.8	463.4	504.5	514.7
70°	314.5	349.1	414.6	457.0	467.2
72.5°	265.7	301.7	367.1	408.2	423.6
75°	213.1	254.2	319.6	363.3	373.5
77.5°	161.7	209.2	276.0	309.4	309.4
80°	115.5	165.6	227.2	242.6	245.2
82.5°	75.7	124.5	168.2	166.9	166.9
85°	43.6	80.9	100.1	97.6	97.6
87.5°	16.7	33.4	35.9	35.9	34.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)