

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P388809

Luminaire Tested: **24CZ2-50VHE-SQR-UNV-L950-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P388809
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2002-678-2)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 2/28/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-50VHE-SQR-UNV-L950-CD1-SDWPD1-U
Description: 2x4 CRUZE LED TROFFER WITH 5000K, 90 LEDS, AND SQUARE LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4302.4 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.33 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 32.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P388809

CATALOG NUMBER: 24CZ2-50VHE-SQR-UNV-L950-CD1-SDWPD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P388809

CATALOG NUMBER: 24CZ2-50VHE-SQR-UNV-L950-CD1-SDWPD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	89	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	52	64	57	51	62	55	50	60	54	49	47
5	74	61	51	44	72	60	51	44	57	50	44	55	49	43	54	48	43	41
6	68	55	45	39	66	54	45	38	52	44	38	50	43	38	48	42	37	35
7	63	49	40	34	62	49	40	34	47	39	34	45	39	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	42	35	30	40	34	30	28
9	55	41	33	27	54	41	33	27	39	32	27	38	32	27	37	31	27	25
10	52	38	30	25	50	37	30	24	36	29	24	36	29	24	35	29	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1850	1850	1850
5°	1858	1855	1855
10°	1844	1859	1867
15°	1825	1860	1880
20°	1800	1855	1888
25°	1770	1845	1894
30°	1733	1839	1905
35°	1697	1834	1923
40°	1659	1834	1949
45°	1617	1838	1987
50°	1579	1850	2040
55°	1533	1870	2103
60°	1480	1900	2179
65°	1416	1936	2271
70°	1314	1984	2386
75°	1189	2053	2496
80°	1002	2059	2146
85°	767	1558	1558



TEST NUMBER: P388809

CATALOG NUMBER: 24CZ2-50VHE-SQR-UNV-L950-CD1-SDWPD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.5	3.0
10°-20°	375.6	8.7
20°-30°	570.5	13.3
30°-40°	693.9	16.1
40°-50°	738.8	17.2
50°-60°	703.7	16.4
60°-70°	588.5	13.7
70°-80°	392.3	9.1
80°-90°	108.6	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1076.6	25.0
0°-40°	1770.5	41.2
0°-60°	3213.0	74.7
0°-90°	4302.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4302.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1367	1374	1374	1374	130
15°	1310	1313	1336	1345	1350	369
25°	1192	1208	1243	1264	1276	549
35°	1033	1063	1117	1154	1171	646
45°	850	895	966	1020	1044	657
55°	654	710	797	867	896	584
65°	445	510	608	683	713	439
75°	229	301	395	462	480	242
85°	50	92	101	100	101	60
90°	0	0	0	0	0	



TEST NUMBER: P388809

CATALOG NUMBER: 24CZ2-50VHE-SQR-UNV-L950-CD1-SDWPD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.3	1375.3	1375.3	1375.3	1375.3
2.5°	1380.9	1371.0	1375.3	1375.3	1369.6
5°	1375.3	1366.7	1373.8	1373.8	1373.8
7.5°	1365.3	1358.2	1369.6	1372.4	1372.4
10°	1349.7	1346.8	1361.0	1365.3	1366.7
12.5°	1332.6	1331.2	1351.1	1356.8	1361.0
15°	1309.9	1312.7	1335.5	1345.4	1349.7
17.5°	1285.8	1291.4	1317.0	1331.2	1335.5
20°	1257.3	1265.9	1295.7	1309.9	1318.4
22.5°	1226.1	1238.9	1270.1	1287.2	1297.1
25°	1192.0	1207.6	1243.1	1264.4	1275.8
27.5°	1155.0	1174.9	1216.1	1240.3	1251.7
30°	1115.3	1138.0	1183.5	1211.9	1226.1
32.5°	1074.1	1101.1	1150.8	1182.0	1199.1
35°	1032.9	1062.7	1116.7	1153.6	1170.7
37.5°	991.7	1021.5	1081.2	1120.9	1142.3
40°	944.8	980.3	1044.2	1088.3	1109.6
42.5°	899.3	937.7	1005.9	1054.2	1076.9
45°	849.6	895.1	966.1	1020.1	1044.2
47.5°	804.1	849.6	926.3	983.1	1010.1
50°	754.4	802.7	883.7	946.2	974.6
52.5°	706.1	755.8	841.1	907.8	936.3
55°	653.5	710.4	797.0	866.6	896.5
57.5°	601.0	662.1	751.6	824.0	853.9
60°	549.8	612.3	706.1	778.6	809.8
62.5°	498.7	561.2	659.2	733.1	762.9
65°	444.7	510.0	608.1	683.4	713.2
67.5°	390.7	458.9	556.9	632.2	660.6
70°	333.9	406.3	504.4	578.2	606.6
72.5°	281.3	353.8	450.4	522.8	549.8
75°	228.7	301.2	395.0	461.7	480.2
77.5°	177.6	250.0	333.9	377.9	382.2
80°	129.3	197.5	265.7	278.5	277.0
82.5°	86.7	147.8	183.3	184.7	189.0
85°	49.7	92.3	100.9	99.5	100.9
87.5°	19.9	32.7	28.4	21.3	21.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)