

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P388835

Luminaire Tested: **24CZ2-55-SQR-UNV-L950-CD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P388835  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2002-678-2)  
Test Lab: INNOVATION CENTER (G2)  
Issue Date: 2/28/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-55-SQR-UNV-L950-CD1-U  
Description: 2x4 CRUZE LED TROFFER WITH 5000K, 90 LEDS, AND SQUARE LENS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4851.1 lumens  
Efficiency: N/A  
Efficacy: 96.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.33 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 50.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P388835  
CATALOG NUMBER: 24CZ2-55-SQR-UNV-L950-CD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P388835

CATALOG NUMBER: 24CZ2-55-SQR-UNV-L950-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	89	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	52	64	57	51	62	55	50	60	54	49	47
5	74	61	51	44	72	60	51	44	57	50	44	55	49	43	54	48	43	41
6	68	55	45	39	66	54	45	38	52	44	38	50	43	38	48	42	37	35
7	63	49	40	34	62	49	40	34	47	39	34	45	39	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	42	35	30	40	34	30	28
9	55	41	33	27	54	41	33	27	39	32	27	38	32	27	37	31	27	25
10	52	38	30	25	50	37	30	24	36	29	24	36	29	24	35	29	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2086	2086	2086
5°	2094	2092	2092
10°	2079	2097	2105
15°	2057	2098	2120
20°	2030	2092	2129
25°	1995	2081	2136
30°	1954	2073	2148
35°	1913	2068	2168
40°	1871	2068	2197
45°	1823	2073	2240
50°	1780	2086	2300
55°	1729	2108	2371
60°	1668	2142	2457
65°	1596	2183	2560
70°	1481	2237	2691
75°	1341	2315	2815
80°	1130	2321	2421
85°	866	1755	1755



TEST NUMBER: P388835

CATALOG NUMBER: 24CZ2-55-SQR-UNV-L950-CD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.2	3.0
10°-20°	423.5	8.7
20°-30°	643.2	13.3
30°-40°	782.4	16.1
40°-50°	833.0	17.2
50°-60°	793.4	16.4
60°-70°	663.5	13.7
70°-80°	442.4	9.1
80°-90°	122.4	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1213.9	25.0
0°-40°	1996.3	41.2
0°-60°	3622.8	74.7
0°-90°	4851.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4851.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1551	1551	1551	1551	1551	
5°	1551	1541	1549	1549	1549	147
15°	1477	1480	1506	1517	1522	417
25°	1344	1362	1402	1426	1438	619
35°	1165	1198	1259	1301	1320	729
45°	958	1009	1089	1150	1177	741
55°	737	801	899	977	1011	659
65°	501	575	686	770	804	495
75°	258	340	445	521	541	273
85°	56	104	114	112	114	68
90°	0	0	0	0	0	



TEST NUMBER: P388835

CATALOG NUMBER: 24CZ2-55-SQR-UNV-L950-CD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1550.6	1550.6	1550.6	1550.6	1550.6
2.5°	1557.1	1545.8	1550.6	1550.6	1544.2
5°	1550.6	1541.0	1549.0	1549.0	1549.0
7.5°	1539.4	1531.4	1544.2	1547.4	1547.4
10°	1521.8	1518.6	1534.6	1539.4	1541.0
12.5°	1502.6	1501.0	1523.4	1529.8	1534.6
15°	1477.0	1480.2	1505.8	1517.0	1521.8
17.5°	1449.7	1456.1	1485.0	1501.0	1505.8
20°	1417.7	1427.3	1460.9	1477.0	1486.6
22.5°	1382.4	1396.9	1432.1	1451.3	1462.5
25°	1344.0	1361.6	1401.7	1425.7	1438.5
27.5°	1302.4	1324.8	1371.2	1398.5	1411.3
30°	1257.5	1283.1	1334.4	1366.4	1382.4
32.5°	1211.0	1241.5	1297.5	1332.8	1352.0
35°	1164.6	1198.2	1259.1	1300.7	1320.0
37.5°	1118.1	1151.8	1219.1	1263.9	1287.9
40°	1065.3	1105.3	1177.4	1227.1	1251.1
42.5°	1014.0	1057.3	1134.2	1188.6	1214.2
45°	957.9	1009.2	1089.3	1150.2	1177.4
47.5°	906.7	957.9	1044.4	1108.5	1139.0
50°	850.6	905.1	996.4	1066.9	1098.9
52.5°	796.1	852.2	948.3	1023.6	1055.7
55°	736.9	801.0	898.7	977.2	1010.8
57.5°	677.6	746.5	847.4	929.1	962.7
60°	619.9	690.4	796.1	877.8	913.1
62.5°	562.3	632.8	743.3	826.6	860.2
65°	501.4	575.1	685.6	770.5	804.2
67.5°	440.5	517.4	627.9	712.8	744.9
70°	376.4	458.1	568.7	652.0	684.0
72.5°	317.2	398.9	507.8	589.5	619.9
75°	257.9	339.6	445.3	520.6	541.4
77.5°	200.2	281.9	376.4	426.1	430.9
80°	145.8	222.7	299.6	314.0	312.4
82.5°	97.7	166.6	206.6	208.2	213.1
85°	56.1	104.1	113.7	112.1	113.7
87.5°	22.4	36.8	32.0	24.0	24.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)