

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: METALUX

Report Number: P388923

Luminaire Tested: **24CZ2-60HE-SQR-UNV-L935-CD1-SDWPD1-U**

Issue Date: 2/28/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P388923  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2002-678-2)  
Test Lab: INNOVATION CENTER (G2)  
Issue Date: 2/28/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-60HE-SQR-UNV-L935-CD1-SDWPD1-U  
Description: 2x4 CRUZE LED TROFFER WITH 3500K, 90 LEDS, AND SQUARE LENS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4762.1 lumens  
Efficiency: N/A  
Efficacy: 108.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.33 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 44.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P388923

CATALOG NUMBER: 24CZ2-60HE-SQR-UNV-L935-CD1-SDWPD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P388923

CATALOG NUMBER: 24CZ2-60HE-SQR-UNV-L935-CD1-SDWPD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89	92	89	87	89	86	84	82
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56
4	81	68	59	52	78	67	58	52	64	57	51	62	55	50	60	54	49	47
5	74	61	51	44	72	60	51	44	57	50	44	55	49	43	54	48	43	41
6	68	55	45	39	66	54	45	38	52	44	38	50	43	38	48	42	37	35
7	63	49	40	34	62	49	40	34	47	39	34	45	39	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	42	35	30	40	34	30	28
9	55	41	33	27	54	41	33	27	39	32	27	38	32	27	37	31	27	25
10	52	38	30	25	50	37	30	24	36	29	24	36	29	24	35	29	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2048	2048	2048
5°	2056	2054	2054
10°	2041	2058	2067
15°	2020	2059	2081
20°	1993	2053	2089
25°	1959	2043	2096
30°	1918	2035	2108
35°	1878	2030	2128
40°	1837	2030	2157
45°	1789	2035	2199
50°	1748	2047	2258
55°	1697	2069	2328
60°	1638	2103	2412
65°	1567	2143	2513
70°	1454	2196	2642
75°	1316	2273	2763
80°	1109	2279	2376
85°	849	1723	1723



TEST NUMBER: P388923

CATALOG NUMBER: 24CZ2-60HE-SQR-UNV-L935-CD1-SDWPD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.5	3.0
10°-20°	415.7	8.7
20°-30°	631.4	13.3
30°-40°	768.1	16.1
40°-50°	817.7	17.2
50°-60°	778.9	16.4
60°-70°	651.3	13.7
70°-80°	434.3	9.1
80°-90°	120.2	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1191.7	25.0
0°-40°	1959.7	41.2
0°-60°	3556.3	74.7
0°-90°	4762.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4762.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1522	1522	1522	1522	1522	
5°	1522	1513	1521	1521	1521	144
15°	1450	1453	1478	1489	1494	409
25°	1319	1337	1376	1400	1412	607
35°	1143	1176	1236	1277	1296	715
45°	940	991	1069	1129	1156	727
55°	723	786	882	959	992	647
65°	492	564	673	756	789	486
75°	253	333	437	511	532	268
85°	55	102	112	110	112	66
90°	0	0	0	0	0	



TEST NUMBER: P388923

CATALOG NUMBER: 24CZ2-60HE-SQR-UNV-L935-CD1-SDWPD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1522.2	1522.2	1522.2	1522.2	1522.2
2.5°	1528.5	1517.5	1522.2	1522.2	1515.9
5°	1522.2	1512.8	1520.6	1520.6	1520.6
7.5°	1511.2	1503.3	1515.9	1519.1	1519.1
10°	1493.9	1490.7	1506.5	1511.2	1512.8
12.5°	1475.0	1473.5	1495.5	1501.8	1506.5
15°	1449.9	1453.0	1478.2	1489.2	1493.9
17.5°	1423.1	1429.4	1457.7	1473.5	1478.2
20°	1391.7	1401.1	1434.1	1449.9	1459.3
22.5°	1357.1	1371.2	1405.8	1424.7	1435.7
25°	1319.3	1336.6	1376.0	1399.5	1412.1
27.5°	1278.5	1300.5	1346.1	1372.8	1385.4
30°	1234.4	1259.6	1309.9	1341.4	1357.1
32.5°	1188.8	1218.7	1273.7	1308.3	1327.2
35°	1143.2	1176.2	1236.0	1276.9	1295.8
37.5°	1097.6	1130.6	1196.7	1240.7	1264.3
40°	1045.7	1085.0	1155.8	1204.5	1228.1
42.5°	995.4	1037.9	1113.3	1166.8	1192.0
45°	940.4	990.7	1069.3	1129.1	1155.8
47.5°	890.0	940.4	1025.3	1088.2	1118.1
50°	835.0	888.5	978.1	1047.3	1078.7
52.5°	781.5	836.6	930.9	1004.8	1036.3
55°	723.4	786.3	882.2	959.2	992.3
57.5°	665.2	732.8	831.9	912.1	945.1
60°	608.6	677.8	781.5	861.7	896.3
62.5°	552.0	621.1	729.6	811.4	844.4
65°	492.2	564.5	673.0	756.4	789.4
67.5°	432.4	507.9	616.4	699.8	731.2
70°	369.5	449.7	558.2	640.0	671.5
72.5°	311.4	391.6	498.5	578.7	608.6
75°	253.2	333.4	437.2	511.1	531.5
77.5°	196.6	276.8	369.5	418.3	423.0
80°	143.1	218.6	294.1	308.2	306.6
82.5°	95.9	163.5	202.9	204.4	209.1
85°	55.0	102.2	111.6	110.1	111.6
87.5°	22.0	36.2	31.5	23.6	23.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)