

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P276697

Luminaire Tested: **24CZ2-35-S-UNV-L92765-W2A1-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P276697
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-35-S-UNV-L92765-W2A1-U-3000K
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS
Light Source: (168) 90 CRI LEDS TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2880.6 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 25.761
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P276697

CATALOG NUMBER: 24CZ2-35-S-UNV-L92765-W2A1-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P276697

CATALOG NUMBER: 24CZ2-35-S-UNV-L92765-W2A1-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1362	1362	1362
5°	1361	1357	1366
10°	1355	1355	1365
15°	1342	1349	1362
20°	1324	1338	1359
25°	1300	1324	1350
30°	1271	1309	1339
35°	1243	1288	1328
40°	1201	1266	1313
45°	1161	1241	1299
50°	1117	1218	1283
55°	1067	1195	1271
60°	1017	1177	1268
65°	953	1156	1276
70°	882	1162	1310
75°	790	1184	1384
80°	638	1255	1354
85°	480	1102	1073



TEST NUMBER: P276697

CATALOG NUMBER: 24CZ2-35-S-UNV-L92765-W2A1-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.8	3.3
10°-20°	273.7	9.5
20°-30°	411.5	14.3
30°-40°	490.2	17.0
40°-50°	501.7	17.4
50°-60°	451.6	15.7
60°-70°	354.7	12.3
70°-80°	230.2	8.0
80°-90°	71.2	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	781.1	27.1
0°-40°	1271.2	44.1
0°-60°	2224.5	77.2
0°-90°	2880.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2880.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1007	1009	1005	1010	1011	96
15°	964	966	968	976	978	272
25°	876	883	892	907	910	403
35°	757	766	784	803	809	472
45°	610	625	652	677	683	471
55°	455	475	510	536	542	408
65°	299	322	363	393	401	298
75°	152	181	228	259	266	161
85°	31	58	71	70	70	38
90°	0	0	0	0	0	



TEST NUMBER: P276697

CATALOG NUMBER: 24CZ2-35-S-UNV-L92765-W2A1-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.0	1012.0	1012.0	1012.0	1012.0
2.5°	1012.9	1012.9	1008.3	1012.9	1013.8
5°	1007.4	1009.2	1004.7	1010.1	1011.1
7.5°	1001.9	1001.9	999.2	1004.7	1005.6
10°	991.8	992.8	991.8	998.2	999.2
12.5°	979.0	980.9	981.8	988.2	989.1
15°	963.5	966.2	968.1	976.3	978.1
17.5°	946.1	948.8	953.4	962.6	964.4
20°	925.0	928.7	934.2	946.1	948.8
22.5°	902.2	905.8	915.0	926.0	930.5
25°	875.6	883.0	892.1	906.7	909.5
27.5°	849.1	855.5	867.4	883.0	886.6
30°	818.0	828.1	842.7	858.3	861.9
32.5°	787.8	797.9	815.3	831.7	836.3
35°	756.7	765.8	784.1	803.4	808.8
37.5°	721.0	732.9	753.0	772.2	777.7
40°	683.5	698.1	721.0	741.1	747.5
42.5°	647.8	663.4	686.2	708.2	715.5
45°	610.3	624.9	652.4	677.1	682.6
47.5°	571.9	588.3	617.6	642.3	651.5
50°	533.4	550.8	581.9	607.5	613.0
52.5°	495.0	513.3	546.2	573.7	576.4
55°	454.7	474.9	509.6	536.2	541.7
57.5°	418.1	435.5	473.0	500.5	506.9
60°	377.9	397.1	437.4	463.0	471.2
62.5°	339.5	359.6	401.7	427.3	434.6
65°	299.2	322.1	363.2	393.4	400.8
67.5°	264.4	286.4	330.3	359.6	366.9
70°	224.2	248.9	295.5	325.7	333.1
72.5°	189.4	215.0	261.7	291.0	301.9
75°	151.9	181.2	227.8	258.9	266.3
77.5°	115.3	149.1	196.7	220.5	220.5
80°	82.3	118.0	162.0	172.9	174.8
82.5°	54.0	88.8	119.9	118.9	118.9
85°	31.1	57.6	71.4	69.5	69.5
87.5°	11.9	23.8	25.6	25.6	24.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)