

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: METALUX

Report Number: P276618

Luminaire Tested: **24CZ2-40HE-S-UNV-L92765-W2A1-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
Report Number: P276618  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 24CZ2-40HE-S-UNV-L92765-W2A1-U-4000K  
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS  
Light Source: (336) 90 CRI LEDS TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER  
Luminaire Equipment: Sample No.   Condition   Description

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3575.4 lumens  
Efficiency: N/A  
Efficacy: 124.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 28.644  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P276618

CATALOG NUMBER: 24CZ2-40HE-S-UNV-L92765-W2A1-U-4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P276618

CATALOG NUMBER: 24CZ2-40HE-S-UNV-L92765-W2A1-U-4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1690	1690	1690
5°	1689	1684	1695
10°	1682	1682	1694
15°	1666	1674	1691
20°	1644	1660	1686
25°	1613	1644	1676
30°	1577	1625	1662
35°	1543	1599	1649
40°	1490	1572	1630
45°	1441	1541	1612
50°	1386	1512	1593
55°	1324	1484	1577
60°	1262	1461	1574
65°	1182	1436	1584
70°	1094	1443	1626
75°	980	1470	1718
80°	792	1557	1681
85°	596	1368	1332



TEST NUMBER: P276618

CATALOG NUMBER: 24CZ2-40HE-S-UNV-L92765-W2A1-U-4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.9	3.3
10°-20°	339.8	9.5
20°-30°	510.8	14.3
30°-40°	608.4	17.0
40°-50°	622.7	17.4
50°-60°	560.6	15.7
60°-70°	440.2	12.3
70°-80°	285.7	8.0
80°-90°	88.4	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	969.4	27.1
0°-40°	1577.8	44.1
0°-60°	2761.1	77.2
0°-90°	3575.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3575.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1256	1256	1256	1256	1256	
5°	1250	1253	1247	1254	1255	119
15°	1196	1199	1202	1212	1214	337
25°	1087	1096	1107	1126	1129	501
35°	939	951	973	997	1004	586
45°	758	776	810	840	847	584
55°	564	589	633	666	672	506
65°	371	400	451	488	497	370
75°	188	225	283	321	330	199
85°	39	72	89	86	86	47
90°	0	0	0	0	0	



TEST NUMBER: P276618

CATALOG NUMBER: 24CZ2-40HE-S-UNV-L92765-W2A1-U-4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1256.1	1256.1	1256.1	1256.1	1256.1
2.5°	1257.2	1257.2	1251.5	1257.2	1258.3
5°	1250.4	1252.7	1247.0	1253.8	1254.9
7.5°	1243.6	1243.6	1240.2	1247.0	1248.1
10°	1231.1	1232.2	1231.1	1239.0	1240.2
12.5°	1215.2	1217.4	1218.6	1226.5	1227.7
15°	1195.9	1199.3	1201.5	1211.8	1214.0
17.5°	1174.3	1177.7	1183.4	1194.7	1197.0
20°	1148.2	1152.7	1159.5	1174.3	1177.7
22.5°	1119.8	1124.3	1135.7	1149.3	1155.0
25°	1086.8	1095.9	1107.3	1125.5	1128.9
27.5°	1053.9	1061.9	1076.6	1095.9	1100.5
30°	1015.3	1027.8	1046.0	1065.3	1069.8
32.5°	977.8	990.3	1011.9	1032.3	1038.0
35°	939.2	950.6	973.3	997.1	1003.9
37.5°	894.9	909.7	934.7	958.5	965.3
40°	848.4	866.5	894.9	919.9	927.8
42.5°	804.1	823.4	851.8	879.0	888.1
45°	757.5	775.7	809.7	840.4	847.2
47.5°	709.8	730.2	766.6	797.2	808.6
50°	662.1	683.7	722.3	754.1	760.9
52.5°	614.4	637.1	678.0	712.1	715.5
55°	564.4	589.4	632.6	665.5	672.3
57.5°	519.0	540.6	587.1	621.2	629.2
60°	469.0	492.9	542.9	574.7	584.9
62.5°	421.3	446.3	498.6	530.4	539.4
65°	371.4	399.8	450.9	488.3	497.4
67.5°	328.2	355.5	410.0	446.3	455.4
70°	278.2	308.9	366.8	404.3	413.4
72.5°	235.1	266.9	324.8	361.1	374.8
75°	188.5	224.9	282.8	321.4	330.5
77.5°	143.1	185.1	244.2	273.7	273.7
80°	102.2	146.5	201.0	214.6	216.9
82.5°	67.0	110.2	148.8	147.6	147.6
85°	38.6	71.5	88.6	86.3	86.3
87.5°	14.8	29.5	31.8	31.8	30.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)